

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007513

Luminaire Tested: S123IP-B1195UB2750-4F0-XX-W2A_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1195UB2750-4F0-XX-W2A_3000K
Description: Define 3 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4767.0 lumens
Efficiency: N/A
Efficacy: 136.2 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007513

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007513

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007513

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.1
90°-100°	55.1	1.2
100°-110°	266.4	5.6
110°-120°	652.9	13.7
120°-130°	828.8	17.4
130°-140°	885.4	18.6
140°-150°	827.9	17.4
150°-160°	667.8	14.0
160°-170°	431.0	9.0
170°-180°	148.5	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.1
90°-120°	974.4	20.4
90°-150°	3516.6	73.8
90°-180°	4764.0	99.9
0°-180°	4767.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	13	28	32	35	4
95°	71	23	36	44	44	85
105°	346	359	254	49	51	367
115°	649	656	666	678	683	641
125°	915	924	929	931	933	817
135°	1139	1146	1150	1154	1150	877
145°	1314	1322	1325	1327	1327	823
155°	1448	1445	1447	1452	1445	667
165°	1527	1523	1522	1531	1523	431
175°	1563	1557	1558	1566	1557	149
180°	1563	1563	1563	1563	1563	

TEST NUMBER: P1007513

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	12.8	27.9	32.5	34.8
92.5°	26.7	19.7	30.2	38.3	39.5
95°	70.8	23.2	36.0	44.1	44.1
97.5°	128.9	96.4	37.2	46.4	47.6
100°	196.2	219.4	38.3	47.6	48.8
102.5°	272.8	287.9	85.9	47.6	49.9
105°	346.0	358.7	254.3	48.8	51.1
107.5°	423.8	434.2	451.6	272.8	120.7
110°	501.5	510.8	523.6	485.3	319.3

TEST NUMBER: P1007513

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.8	584.0	596.7	607.2	604.9
115°	649.0	655.9	666.4	678.0	682.6
117.5°	721.0	729.1	734.9	744.2	745.3
120°	787.1	797.6	801.1	810.4	810.4
122.5°	854.5	862.6	867.2	873.0	874.2
125°	914.8	924.1	928.8	931.1	933.4
127.5°	975.2	984.5	990.3	993.8	991.5
130°	1030.9	1040.2	1044.9	1049.5	1047.2
132.5°	1084.3	1093.6	1097.1	1101.8	1098.3
135°	1138.9	1145.9	1150.5	1154.0	1150.5
137.5°	1185.3	1194.6	1197.0	1202.8	1200.4
140°	1231.8	1238.7	1242.2	1246.9	1244.5
142.5°	1274.7	1281.7	1285.2	1288.7	1285.2
145°	1314.2	1322.3	1324.7	1327.0	1327.0
147.5°	1352.5	1358.3	1360.6	1363.0	1357.2
150°	1387.3	1390.8	1393.2	1395.5	1392.0
152.5°	1418.7	1419.9	1421.0	1425.7	1419.9
155°	1447.7	1445.4	1446.6	1452.4	1445.4
157.5°	1470.9	1470.9	1469.8	1476.7	1467.5
160°	1491.8	1490.7	1489.5	1496.5	1488.4
162.5°	1511.6	1508.1	1506.9	1515.1	1508.1
165°	1526.7	1523.2	1522.0	1531.3	1523.2
167.5°	1539.4	1534.8	1534.8	1544.1	1534.8
170°	1549.9	1545.2	1545.2	1554.5	1545.2
172.5°	1556.8	1551.0	1552.2	1561.5	1551.0
175°	1562.7	1556.8	1558.0	1566.1	1556.8
177.5°	1565.0	1559.2	1560.3	1569.6	1558.0
180°	1562.7	1562.7	1562.7	1562.7	1562.7

(END OF REPORT)