

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007514

Luminaire Tested: S123IP-B1195UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007514
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B1195UB2750-4F0-XX-W2A_3500K
Description: Define 3 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4788.0 lumens
Efficiency: N/A
Efficacy: 136.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 35
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007514

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007514

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007514

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	3.1	0.1
90°-100°	55.3	1.2
100°-110°	267.6	5.6
110°-120°	655.8	13.7
120°-130°	832.5	17.4
130°-140°	889.3	18.6
140°-150°	831.6	17.4
150°-160°	670.8	14.0
160°-170°	432.9	9.0
170°-180°	149.2	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	3.1	0.1
90°-120°	978.7	20.4
90°-150°	3532.1	73.8
90°-180°	4785.0	99.9
0°-180°	4788.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	13	28	33	35	4
95°	71	23	36	44	44	85
105°	348	360	255	49	51	368
115°	652	659	669	681	686	644
125°	919	928	933	935	938	821
135°	1144	1151	1156	1159	1156	881
145°	1320	1328	1330	1333	1333	826
155°	1454	1452	1453	1459	1452	670
165°	1533	1530	1529	1538	1530	433
175°	1570	1564	1565	1573	1564	149
180°	1570	1570	1570	1570	1570	

TEST NUMBER: P1007514

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	1.2	12.8	28.0	32.7	35.0
92.5°	26.8	19.8	30.3	38.5	39.6
95°	71.1	23.3	36.1	44.3	44.3
97.5°	129.4	96.8	37.3	46.6	47.8
100°	197.1	220.4	38.5	47.8	49.0
102.5°	274.0	289.2	86.3	47.8	50.1
105°	347.5	360.3	255.4	49.0	51.3
107.5°	425.6	436.1	453.6	274.0	121.3
110°	503.7	513.1	525.9	487.4	320.7

TEST NUMBER: P1007514

CATALOG NUMBER: S123IP-B1195UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	578.4	586.5	599.4	609.9	607.5
115°	651.8	658.8	669.3	681.0	685.7
117.5°	724.1	732.3	738.1	747.5	748.6
120°	790.6	801.1	804.6	813.9	813.9
122.5°	858.2	866.4	871.1	876.9	878.1
125°	918.9	928.2	932.9	935.2	937.5
127.5°	979.5	988.8	994.7	998.2	995.8
130°	1035.5	1044.8	1049.5	1054.1	1051.8
132.5°	1089.1	1098.4	1101.9	1106.6	1103.1
135°	1143.9	1150.9	1155.6	1159.1	1155.6
137.5°	1190.6	1199.9	1202.2	1208.1	1205.7
140°	1237.2	1244.2	1247.7	1252.4	1250.0
142.5°	1280.4	1287.3	1290.8	1294.3	1290.8
145°	1320.0	1328.2	1330.5	1332.8	1332.8
147.5°	1358.5	1364.3	1366.6	1369.0	1363.1
150°	1393.5	1397.0	1399.3	1401.6	1398.1
152.5°	1424.9	1426.1	1427.3	1431.9	1426.1
155°	1454.1	1451.8	1452.9	1458.8	1451.8
157.5°	1477.4	1477.4	1476.3	1483.2	1473.9
160°	1498.4	1497.2	1496.1	1503.1	1494.9
162.5°	1518.2	1514.7	1513.6	1521.7	1514.7
165°	1533.4	1529.9	1528.7	1538.1	1529.9
167.5°	1546.2	1541.6	1541.6	1550.9	1541.6
170°	1556.7	1552.0	1552.0	1561.4	1552.0
172.5°	1563.7	1557.9	1559.0	1568.4	1557.9
175°	1569.5	1563.7	1564.9	1573.0	1563.7
177.5°	1571.9	1566.0	1567.2	1576.5	1564.9
180°	1569.5	1569.5	1569.5	1569.5	1569.5

(END OF REPORT)