

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012377

Luminaire Tested: S123RDIP-B1165D585UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012377
REPORT IS A COMBINATION OF REPORTS P993078 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D585UB50-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6268.7 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012377

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012377

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72
1	102	98	94	91	96	92	89	86	82	80	77	73	71	69	64	63	62
2	93	86	80	75	88	81	76	71	73	68	65	65	61	59	57	55	53
3	85	76	69	63	80	72	65	60	64	59	55	58	54	50	51	48	45
4	78	68	60	54	74	64	57	51	58	52	47	52	47	43	46	42	39
5	72	61	52	46	68	58	50	45	52	46	41	47	42	38	42	38	35
6	67	55	46	41	63	52	44	39	47	41	36	42	37	33	38	34	31
7	62	49	41	36	58	47	40	35	43	37	32	39	34	30	35	31	27
8	58	45	37	32	54	43	36	31	39	33	29	35	30	27	32	28	25
9	54	41	34	29	51	40	33	28	36	30	26	33	28	24	30	25	22
10	50	38	31	26	48	36	30	25	33	28	24	30	25	22	28	23	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20106	20106	20106
5°	20139	19395	19343
10°	19980	18665	18298
15°	19721	17764	17154
20°	19381	16784	15875
25°	19030	15765	14664
30°	18581	14682	13231
35°	18116	13618	11928
40°	17681	12462	10487
45°	17122	11332	9191
50°	16505	10124	7851
55°	15865	8832	6623
60°	15255	7507	5376
65°	14465	6147	4195
70°	13473	4649	2999
75°	12043	3148	2376
80°	10282	2187	1667
85°	7713	1181	873

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17122 cd/sqm

TEST NUMBER: P1012377

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	175.6	2.8
10°-20°	488.5	7.8
20°-30°	703.3	11.2
30°-40°	792.1	12.6
40°-50°	757.6	12.1
50°-60°	620.2	9.9
60°-70°	418.1	6.7
70°-80°	209.7	3.3
80°-90°	56.4	0.9
90°-100°	154.3	2.5
100°-110°	431.3	6.9
110°-120°	420.5	6.7
120°-130°	334.9	5.3
130°-140°	264.3	4.2
140°-150°	197.2	3.1
150°-160°	137.6	2.2
160°-170°	80.8	1.3
170°-180°	26.3	0.4
0°-30°	1367.4	21.8
0°-40°	2159.5	34.4
0°-60°	3537.3	56.4
0°-90°	4221.5	67.3
90°-120°	1006.1	16.0
90°-150°	1802.6	28.8
90°-180°	2047.0	32.7
0°-180°	6268.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1868	1868	1868	1868	1868	
5°	1868	1860	1842	1856	1853	177
15°	1782	1765	1722	1715	1704	502
25°	1621	1583	1513	1482	1465	746
35°	1403	1348	1254	1189	1162	878
45°	1153	1085	968	882	845	890
55°	876	801	673	585	554	785
65°	598	515	397	323	306	592
75°	317	244	161	145	142	337
85°	80	47	42	39	39	88
90°	1	7	14	15	16	6
95°	19	61	326	95	64	20
105°	64	94	442	773	699	68
115°	113	140	338	741	850	112
125°	157	185	316	572	671	139
135°	184	219	311	471	544	142
145°	209	240	307	386	425	131
155°	238	257	297	338	352	109
165°	260	267	285	302	307	73
175°	271	271	273	277	276	26
180°	272	272	272	272	272	

TEST NUMBER: P1012377

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1867.9	1867.9	1867.9	1867.9	1867.9
2.5°	1875.5	1869.5	1851.3	1867.9	1864.9
5°	1867.9	1860.4	1842.2	1855.8	1852.8
7.5°	1854.3	1846.7	1824.0	1833.1	1828.5
10°	1836.1	1825.5	1798.2	1799.8	1792.2
12.5°	1810.4	1798.2	1763.4	1761.9	1752.8
15°	1781.6	1764.9	1722.5	1714.9	1704.3
17.5°	1746.7	1728.6	1675.5	1660.4	1645.2
20°	1707.4	1683.1	1625.5	1605.8	1587.7
22.5°	1663.4	1634.6	1572.5	1546.8	1530.1
25°	1621.0	1583.1	1513.4	1481.6	1465.0
27.5°	1569.5	1528.6	1452.8	1410.4	1384.7
30°	1516.5	1471.0	1386.2	1334.7	1310.4
32.5°	1463.4	1410.4	1319.5	1262.0	1236.2
35°	1402.8	1348.3	1254.4	1189.2	1162.0
37.5°	1342.2	1283.2	1184.7	1112.0	1078.6
40°	1284.7	1218.0	1110.5	1031.7	996.8
42.5°	1219.5	1152.9	1040.8	952.9	922.6
45°	1152.9	1084.7	968.1	881.7	845.3
47.5°	1087.7	1012.0	896.9	802.9	771.1
50°	1015.0	943.8	821.1	727.2	692.3
52.5°	949.9	871.1	749.9	651.4	621.1
55°	875.6	801.4	672.6	584.8	554.5
57.5°	809.0	728.7	598.4	515.1	489.3
60°	739.3	656.0	530.2	448.4	422.7
62.5°	669.6	586.3	460.5	384.8	357.5
65°	598.4	515.1	396.9	322.7	306.0
67.5°	527.2	442.4	327.2	271.2	253.0
70°	457.5	375.7	269.7	216.6	200.0
72.5°	387.8	307.5	213.6	172.7	168.2
75°	316.6	243.9	160.6	145.4	142.4
77.5°	251.5	184.8	125.7	116.7	113.6
80°	189.4	127.3	95.4	90.9	87.9
82.5°	130.3	78.8	68.2	63.6	63.6
85°	80.3	47.0	42.4	39.4	39.4
87.5°	36.4	19.7	19.7	18.2	16.7
90°	1.1	6.6	13.7	15.4	15.9
92.5°	8.2	33.0	102.2	34.9	29.1
95°	18.7	60.8	325.9	95.1	63.8
97.5°	29.7	69.5	501.3	239.1	130.8
100°	40.7	76.7	520.5	500.2	344.6
102.5°	52.2	84.9	484.8	669.8	545.8
105°	63.8	94.2	441.9	772.8	699.2
107.5°	75.9	105.2	404.0	818.2	799.2
110°	89.0	116.5	372.7	819.6	856.4

TEST NUMBER: P1012377

CATALOG NUMBER: S123RDIP-B1165D585UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	101.1	128.4	351.8	788.5	867.9
115°	112.7	140.4	338.0	741.2	850.3
117.5°	124.2	152.0	328.7	690.7	811.8
120°	136.3	163.6	322.7	642.8	761.3
122.5°	146.8	174.5	318.8	605.2	714.0
125°	156.7	185.0	315.5	571.7	670.6
127.5°	164.3	194.9	313.9	544.2	633.2
130°	171.5	203.6	312.2	518.9	602.4
132.5°	177.0	211.6	311.7	495.2	572.2
135°	183.6	219.0	311.1	470.8	543.6
137.5°	189.6	225.1	310.0	447.7	513.4
140°	195.7	230.6	309.5	425.2	481.5
142.5°	202.3	235.6	308.4	404.5	451.8
145°	209.4	239.9	307.3	386.2	424.9
147.5°	216.6	244.6	305.6	371.8	401.8
150°	223.7	248.4	303.4	359.2	382.0
152.5°	230.9	252.6	300.7	348.2	365.5
155°	238.0	256.6	297.4	338.0	352.3
157.5°	243.5	260.2	294.6	328.2	339.7
160°	250.1	263.2	291.3	319.1	327.6
162.5°	255.0	265.5	288.0	310.5	316.6
165°	260.0	267.4	284.7	302.0	307.3
167.5°	263.8	269.0	281.4	294.6	297.9
170°	267.1	269.8	278.1	288.0	289.7
172.5°	269.3	270.7	275.4	282.2	282.0
175°	271.0	271.2	273.2	277.0	276.5
177.5°	272.1	271.5	271.5	273.7	272.6
180°	271.5	271.5	271.5	271.5	271.5

(END OF REPORT)