

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007532

Luminaire Tested: S123IP-B365UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007532
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B365UB2750-4F0-XX-W2A-1_2700K
Description: Define 3 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1244.0 lumens
Efficiency: N/A
Efficacy: 133.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007532

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1007532

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007532

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	28.9	2.3
100°-110°	87.4	7.0
110°-120°	148.8	12.0
120°-130°	195.8	15.7
130°-140°	220.0	17.7
140°-150°	216.3	17.4
150°-160°	182.1	14.6
160°-170°	121.2	9.7
170°-180°	42.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	265.1	21.3
90°-150°	897.2	72.1
90°-180°	1243.0	99.9
0°-180°	1244.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	8	10	11	2
95°	21	23	26	28	28	23
105°	79	80	83	83	84	85
115°	150	151	150	150	150	148
125°	219	220	220	218	217	195
135°	284	286	286	285	284	219
145°	345	346	347	346	345	216
155°	395	395	395	397	394	182
165°	430	429	429	431	429	121
175°	448	446	446	448	446	43
180°	449	449	449	449	449	

TEST NUMBER: P1007532

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	3.9	8.5	9.9	10.6
92.5°	10.6	12.7	14.8	15.9	15.2
95°	20.8	23.3	26.1	27.5	27.5
97.5°	34.2	35.9	38.1	39.8	39.5
100°	47.9	50.0	51.8	52.9	53.6
102.5°	63.8	64.8	67.3	68.4	68.0
105°	79.3	80.0	83.2	83.2	83.9
107.5°	97.6	98.0	99.4	100.4	100.1
110°	114.5	115.2	115.9	117.4	116.6

TEST NUMBER: P1007532

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	132.2	132.5	132.5	134.3	134.3
115°	149.8	150.8	150.1	150.5	150.1
117.5°	167.7	168.1	167.4	167.4	166.3
120°	184.3	186.4	184.7	184.3	183.6
122.5°	201.6	203.0	202.3	201.2	200.2
125°	219.2	220.3	219.6	218.1	216.7
127.5°	235.4	237.5	236.8	234.7	233.3
130°	251.6	254.4	253.4	252.0	249.5
132.5°	267.8	270.7	269.9	268.2	266.4
135°	284.4	286.5	286.2	284.8	284.0
137.5°	299.6	301.3	302.4	300.6	299.6
140°	315.4	317.2	317.5	317.2	314.7
142.5°	329.9	331.6	332.3	332.0	330.2
145°	345.0	345.7	346.8	346.4	345.0
147.5°	358.1	359.5	360.5	360.5	358.4
150°	371.8	372.5	373.2	373.2	371.1
152.5°	383.1	384.1	384.5	385.2	383.4
155°	395.1	395.1	395.4	396.8	394.4
157.5°	405.3	404.9	405.3	406.7	404.6
160°	414.8	414.1	414.1	415.8	414.4
162.5°	423.2	422.2	422.5	424.3	421.8
165°	430.3	429.2	429.2	431.4	428.9
167.5°	436.3	434.9	435.2	437.3	435.2
170°	441.2	439.8	439.8	442.3	439.8
172.5°	445.1	443.7	443.7	445.8	443.3
175°	447.6	446.2	446.2	448.3	445.8
177.5°	449.0	447.6	447.6	449.7	447.2
180°	448.6	448.6	448.6	448.6	448.6

(END OF REPORT)