

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012382

Luminaire Tested: S123RDIP-B1165D805UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012382
REPORT IS A COMBINATION OF REPORTS P993083 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D805UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7023.0 lumens
Efficiency: N/A
Efficacy: 85.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012382

CATALOG NUMBER: S123RDIP-B1165D805UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012382

CATALOG NUMBER: S123RDIP-B1165D805UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	89	94	91	87	84	80	77	75	69	68	66	60	59	58
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32
6	66	54	46	40	62	51	43	38	45	39	35	40	35	32	35	31	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21
10	50	37	30	25	46	36	29	24	32	26	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20730	20730	20730
5°	20764	19997	19943
10°	20601	19245	18866
15°	20334	18316	17686
20°	19983	17305	16368
25°	19621	16255	15119
30°	19156	15137	13642
35°	18679	14040	12298
40°	18230	12848	10813
45°	17654	11683	9477
50°	17017	10438	8094
55°	16358	9106	6828
60°	15727	7740	5542
65°	14915	6338	4325
70°	13891	4792	3092
75°	12420	3246	2449
80°	10597	2255	1718
85°	7953	1217	900

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17654 cd/sqm

TEST NUMBER: P1012382

CATALOG NUMBER: S123RDIP-B1165D805UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	181.0	2.6
10°-20°	503.7	7.2
20°-30°	725.2	10.3
30°-40°	816.6	11.6
40°-50°	781.2	11.1
50°-60°	639.4	9.1
60°-70°	431.1	6.1
70°-80°	216.2	3.1
80°-90°	58.6	0.8
90°-100°	62.0	0.9
100°-110°	187.7	2.7
110°-120°	319.6	4.6
120°-130°	420.5	6.0
130°-140°	472.6	6.7
140°-150°	464.7	6.6
150°-160°	391.2	5.6
160°-170°	260.4	3.7
170°-180°	91.2	1.3
0°-30°	1409.9	20.1
0°-40°	2226.5	31.7
0°-60°	3647.1	51.9
0°-90°	4353.0	62.0
90°-120°	569.4	8.1
90°-150°	1927.2	27.4
90°-180°	2670.0	38.0
0°-180°	7023.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1926	1926	1926	1926	1926	
5°	1926	1918	1899	1913	1910	183
15°	1837	1820	1776	1768	1757	518
25°	1671	1632	1560	1528	1510	769
35°	1446	1390	1293	1226	1198	905
45°	1189	1118	998	909	872	917
55°	903	826	694	603	572	810
65°	617	531	409	333	316	611
75°	326	252	166	150	147	348
85°	83	48	44	41	41	91
90°	1	8	18	21	23	8
95°	45	50	56	59	59	49
105°	170	172	179	179	180	182
115°	322	324	322	323	322	318
125°	471	473	472	469	466	420
135°	611	615	615	612	610	471
145°	741	743	745	744	741	463
155°	848	848	849	852	847	391
165°	924	922	922	926	921	261
175°	961	958	958	963	958	91
180°	964	964	964	964	964	

TEST NUMBER: P1012382

CATALOG NUMBER: S123RDIP-B1165D805UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1925.9	1925.9	1925.9	1925.9	1925.9
2.5°	1933.7	1927.5	1908.7	1925.9	1922.8
5°	1925.9	1918.1	1899.4	1913.4	1910.3
7.5°	1911.9	1904.1	1880.6	1890.0	1885.3
10°	1893.1	1882.2	1854.1	1855.6	1847.8
12.5°	1866.6	1854.1	1818.1	1816.6	1807.2
15°	1836.9	1819.7	1776.0	1768.2	1757.2
17.5°	1801.0	1782.2	1727.6	1711.9	1696.3
20°	1760.4	1735.4	1676.0	1655.7	1637.0
22.5°	1715.1	1685.4	1621.3	1594.8	1577.6
25°	1671.3	1632.3	1560.4	1527.6	1510.4
27.5°	1618.2	1576.0	1497.9	1454.2	1427.7
30°	1563.5	1516.7	1429.2	1376.1	1351.1
32.5°	1508.9	1454.2	1360.5	1301.1	1274.6
35°	1446.4	1390.2	1293.3	1226.2	1198.0
37.5°	1383.9	1323.0	1221.5	1146.5	1112.1
40°	1324.6	1255.8	1144.9	1063.7	1027.8
42.5°	1257.4	1188.7	1073.1	982.5	951.2
45°	1188.7	1118.4	998.1	909.1	871.6
47.5°	1121.5	1043.4	924.7	827.8	795.0
50°	1046.5	973.1	846.6	749.8	713.8
52.5°	979.4	898.1	773.2	671.7	640.4
55°	902.8	826.3	693.5	602.9	571.7
57.5°	834.1	751.3	617.0	531.1	504.5
60°	762.2	676.3	546.7	462.3	435.8
62.5°	690.4	604.5	474.8	396.7	368.6
65°	617.0	531.1	409.2	332.7	315.5
67.5°	543.6	456.1	337.4	279.6	260.9
70°	471.7	387.4	278.0	223.4	206.2
72.5°	399.9	317.1	220.2	178.1	173.4
75°	326.5	251.5	165.6	150.0	146.8
77.5°	259.3	190.6	129.6	120.3	117.1
80°	195.2	131.2	98.4	93.7	90.6
82.5°	134.3	81.2	70.3	65.6	65.6
85°	82.8	48.4	43.7	40.6	40.6
87.5°	37.5	20.3	20.3	18.7	17.2
90°	0.8	8.3	18.2	21.2	22.7
92.5°	22.7	27.3	31.8	34.1	32.5
95°	44.7	50.0	56.0	59.0	59.0
97.5°	73.4	77.2	81.8	85.5	84.8
100°	102.9	107.5	111.3	113.5	115.1
102.5°	137.0	139.3	144.6	146.8	146.1
105°	170.3	171.8	178.6	178.6	180.2
107.5°	209.7	210.4	213.5	215.7	215.0
110°	246.0	247.5	249.0	252.1	250.6

TEST NUMBER: P1012382

CATALOG NUMBER: S123RDIP-B1165D805UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.9	284.6	284.6	288.4	288.4
115°	321.7	324.0	322.5	323.2	322.5
117.5°	360.3	361.1	359.6	359.6	357.3
120°	395.9	400.4	396.6	395.9	394.4
122.5°	433.0	436.0	434.5	432.2	429.9
125°	470.8	473.1	471.6	468.6	465.5
127.5°	505.6	510.2	508.7	504.1	501.1
130°	540.5	546.5	544.2	541.2	535.9
132.5°	575.3	581.3	579.8	576.0	572.3
135°	610.9	615.4	614.6	611.6	610.1
137.5°	643.4	647.2	649.5	645.7	643.4
140°	677.5	681.3	682.0	681.3	676.0
142.5°	708.5	712.3	713.8	713.0	709.3
145°	741.1	742.6	744.8	744.1	741.1
147.5°	769.1	772.1	774.4	774.4	769.8
150°	798.6	800.1	801.6	801.6	797.1
152.5°	822.8	825.1	825.8	827.3	823.6
155°	848.5	848.5	849.3	852.3	847.0
157.5°	870.5	869.7	870.5	873.5	869.0
160°	890.9	889.4	889.4	893.2	890.2
162.5°	909.1	906.8	907.6	911.4	906.1
165°	924.2	922.0	922.0	926.5	921.2
167.5°	937.1	934.1	934.8	939.4	934.8
170°	947.7	944.7	944.7	950.0	944.7
172.5°	956.0	953.0	953.0	957.5	952.2
175°	961.3	958.3	958.3	962.8	957.5
177.5°	964.4	961.3	961.3	965.9	960.6
180°	963.6	963.6	963.6	963.6	963.6

(END OF REPORT)