

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012388

Luminaire Tested: S123RDIP-B1165D805UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012388
REPORT IS A COMBINATION OF REPORTS P993099 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B1165D805UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7083.0 lumens
Efficiency: N/A
Efficacy: 86.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012388

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012388

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	89	94	91	87	84	80	77	75	69	68	66	60	59	58
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49
3	84	75	68	62	79	71	64	59	62	57	53	55	51	48	48	45	42
4	77	67	59	53	72	63	56	50	56	50	46	49	45	41	43	39	37
5	71	60	52	46	67	56	49	44	50	44	40	44	40	36	39	35	32
6	66	54	46	40	62	51	43	38	45	39	35	40	35	32	35	31	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	32	28	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	25	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	28	24	21
10	50	37	30	25	46	36	29	24	32	26	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20907	20907	20907
5°	20941	20167	20112
10°	20776	19408	19026
15°	20506	18472	17837
20°	20152	17453	16507
25°	19787	16393	15248
30°	19319	15266	13759
35°	18838	14159	12402
40°	18384	12958	10904
45°	17804	11782	9558
50°	17162	10527	8164
55°	16498	9184	6885
60°	15862	7805	5589
65°	15041	6392	4362
70°	14009	4834	3117
75°	12523	3274	2471
80°	10690	2274	1733
85°	8021	1228	909

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 17804 cd/sqm

TEST NUMBER: P1012388

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	182.6	2.6
10°-20°	507.9	7.2
20°-30°	731.3	10.3
30°-40°	823.6	11.6
40°-50°	787.8	11.1
50°-60°	644.9	9.1
60°-70°	434.8	6.1
70°-80°	218.1	3.1
80°-90°	59.1	0.8
90°-100°	62.6	0.9
100°-110°	189.4	2.7
110°-120°	322.4	4.6
120°-130°	424.1	6.0
130°-140°	476.7	6.7
140°-150°	468.7	6.6
150°-160°	394.6	5.6
160°-170°	262.7	3.7
170°-180°	92.0	1.3
0°-30°	1421.8	20.1
0°-40°	2245.4	31.7
0°-60°	3678.1	51.9
0°-90°	4390.1	62.0
90°-120°	574.3	8.1
90°-150°	1943.8	27.4
90°-180°	2693.0	38.0
0°-180°	7083.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1942	1942	1942	1942	1942	
5°	1942	1934	1916	1930	1926	184
15°	1852	1835	1791	1783	1772	522
25°	1686	1646	1574	1541	1523	775
35°	1459	1402	1304	1237	1208	913
45°	1199	1128	1007	917	879	925
55°	910	833	699	608	576	817
65°	622	536	413	336	318	616
75°	329	254	167	151	148	351
85°	84	49	44	41	41	91
90°	1	8	18	21	23	9
95°	45	50	56	60	60	50
105°	172	173	180	180	182	184
115°	324	327	325	326	325	321
125°	475	477	476	473	470	424
135°	616	621	620	617	615	475
145°	747	749	751	750	747	467
155°	856	856	857	860	854	394
165°	932	930	930	934	929	263
175°	970	967	967	971	966	92
180°	972	972	972	972	972	

TEST NUMBER: P1012388

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1942.3	1942.3	1942.3	1942.3	1942.3
2.5°	1950.2	1943.9	1925.0	1942.3	1939.1
5°	1942.3	1934.4	1915.5	1929.7	1926.5
7.5°	1928.1	1920.2	1896.6	1906.1	1901.3
10°	1909.2	1898.2	1869.8	1871.4	1863.5
12.5°	1882.4	1869.8	1833.6	1832.0	1822.6
15°	1852.5	1835.2	1791.1	1783.2	1772.2
17.5°	1816.3	1797.4	1742.2	1726.5	1710.7
20°	1775.3	1750.1	1690.3	1669.8	1650.9
22.5°	1729.6	1699.7	1635.1	1608.3	1591.0
25°	1685.5	1646.2	1573.7	1540.6	1523.3
27.5°	1632.0	1589.4	1510.7	1466.6	1439.8
30°	1576.8	1529.6	1441.4	1387.8	1362.6
32.5°	1521.7	1466.6	1372.1	1312.2	1285.4
35°	1458.7	1402.0	1304.3	1236.6	1208.2
37.5°	1395.7	1334.2	1231.9	1156.2	1121.6
40°	1335.8	1266.5	1154.7	1072.8	1036.5
42.5°	1268.1	1198.8	1082.2	990.8	959.3
45°	1198.8	1127.9	1006.6	916.8	879.0
47.5°	1131.0	1052.3	932.6	834.9	801.8
50°	1055.4	981.4	853.8	756.1	719.9
52.5°	987.7	905.8	779.8	677.4	645.9
55°	910.5	833.3	699.4	608.1	576.5
57.5°	841.2	757.7	622.2	535.6	508.8
60°	768.7	682.1	551.3	466.3	439.5
62.5°	696.3	609.6	478.9	400.1	371.8
65°	622.2	535.6	412.7	335.5	318.2
67.5°	548.2	460.0	340.3	282.0	263.1
70°	475.7	390.7	280.4	225.3	207.9
72.5°	403.3	319.8	222.1	179.6	174.9
75°	329.2	253.6	167.0	151.2	148.1
77.5°	261.5	192.2	130.7	121.3	118.1
80°	196.9	132.3	99.2	94.5	91.4
82.5°	135.5	81.9	70.9	66.2	66.2
85°	83.5	48.8	44.1	41.0	41.0
87.5°	37.8	20.5	20.5	18.9	17.3
90°	0.8	8.4	18.3	21.4	22.9
92.5°	22.9	27.5	32.1	34.4	32.8
95°	45.0	50.4	56.5	59.6	59.6
97.5°	74.1	77.9	82.5	86.3	85.5
100°	103.8	108.4	112.2	114.5	116.0
102.5°	138.2	140.5	145.8	148.1	147.3
105°	171.8	173.3	180.2	180.2	181.7
107.5°	211.5	212.2	215.3	217.6	216.8
110°	248.1	249.7	251.2	254.2	252.7

TEST NUMBER: P1012388

CATALOG NUMBER: S123RDIP-B1165D805UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	286.3	287.1	287.1	290.9	290.9
115°	324.5	326.8	325.2	326.0	325.2
117.5°	363.4	364.2	362.6	362.6	360.4
120°	399.3	403.9	400.1	399.3	397.8
122.5°	436.7	439.8	438.2	435.9	433.7
125°	474.9	477.2	475.6	472.6	469.5
127.5°	510.0	514.6	513.1	508.5	505.4
130°	545.1	551.2	548.9	545.9	540.5
132.5°	580.2	586.3	584.8	581.0	577.2
135°	616.1	620.7	619.9	616.9	615.4
137.5°	648.9	652.8	655.1	651.2	648.9
140°	683.3	687.1	687.9	687.1	681.8
142.5°	714.6	718.4	720.0	719.2	715.4
145°	747.4	749.0	751.3	750.5	747.4
147.5°	775.7	778.7	781.0	781.0	776.4
150°	805.5	807.0	808.5	808.5	803.9
152.5°	829.9	832.2	832.9	834.5	830.7
155°	855.8	855.8	856.6	859.7	854.3
157.5°	878.0	877.2	878.0	881.0	876.5
160°	898.6	897.1	897.1	900.9	897.8
162.5°	916.9	914.6	915.4	919.2	913.9
165°	932.2	929.9	929.9	934.5	929.1
167.5°	945.2	942.1	942.9	947.5	942.9
170°	955.9	952.8	952.8	958.2	952.8
172.5°	964.3	961.2	961.2	965.8	960.4
175°	969.6	966.6	966.6	971.1	965.8
177.5°	972.7	969.6	969.6	974.2	968.8
180°	971.9	971.9	971.9	971.9	971.9

(END OF REPORT)