

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007544

Luminaire Tested: S123IP-B365UB2750-4F0-XX-W2A_3500K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007544
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B365UB2750-4F0-XX-W2A_3500K
Description: Define 3 Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1466.0 lumens
Efficiency: N/A
Efficacy: 157.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 9.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007544

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1007544

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007544

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.0	0.1
90°-100°	16.9	1.2
100°-110°	81.9	5.6
110°-120°	200.8	13.7
120°-130°	254.9	17.4
130°-140°	272.3	18.6
140°-150°	254.6	17.4
150°-160°	205.4	14.0
160°-170°	132.5	9.0
170°-180°	45.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.0	0.1
90°-120°	299.6	20.4
90°-150°	1081.4	73.8
90°-180°	1465.0	99.9
0°-180°	1466.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	4	9	10	11	1
95°	22	7	11	14	14	26
105°	106	110	78	15	16	113
115°	200	202	205	208	210	197
125°	281	284	286	286	287	251
135°	350	352	354	355	354	270
145°	404	407	407	408	408	253
155°	445	444	445	447	444	205
165°	470	468	468	471	468	133
175°	481	479	479	482	479	46
180°	481	481	481	481	481	

TEST NUMBER: P1007544

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.4	3.9	8.6	10.0	10.7
92.5°	8.2	6.1	9.3	11.8	12.1
95°	21.8	7.1	11.1	13.6	13.6
97.5°	39.6	29.6	11.4	14.3	14.6
100°	60.3	67.5	11.8	14.6	15.0
102.5°	83.9	88.5	26.4	14.6	15.4
105°	106.4	110.3	78.2	15.0	15.7
107.5°	130.3	133.5	138.9	83.9	37.1
110°	154.2	157.1	161.0	149.2	98.2

TEST NUMBER: P1007544

CATALOG NUMBER: S123IP-B365UB2750-4F0-XX-W2A_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	177.1	179.6	183.5	186.7	186.0
115°	199.6	201.7	204.9	208.5	209.9
117.5°	221.7	224.2	226.0	228.9	229.2
120°	242.1	245.3	246.4	249.2	249.2
122.5°	262.8	265.3	266.7	268.5	268.8
125°	281.3	284.2	285.6	286.3	287.1
127.5°	299.9	302.8	304.5	305.6	304.9
130°	317.0	319.9	321.3	322.8	322.0
132.5°	333.5	336.3	337.4	338.8	337.8
135°	350.2	352.4	353.8	354.9	353.8
137.5°	364.5	367.4	368.1	369.9	369.2
140°	378.8	381.0	382.0	383.5	382.7
142.5°	392.0	394.2	395.2	396.3	395.2
145°	404.2	406.7	407.4	408.1	408.1
147.5°	415.9	417.7	418.4	419.2	417.4
150°	426.7	427.7	428.4	429.2	428.1
152.5°	436.3	436.6	437.0	438.4	436.6
155°	445.2	444.5	444.9	446.6	444.5
157.5°	452.4	452.4	452.0	454.1	451.3
160°	458.8	458.4	458.1	460.2	457.7
162.5°	464.9	463.8	463.4	465.9	463.8
165°	469.5	468.4	468.1	470.9	468.4
167.5°	473.4	472.0	472.0	474.9	472.0
170°	476.6	475.2	475.2	478.1	475.2
172.5°	478.8	477.0	477.4	480.2	477.0
175°	480.6	478.8	479.1	481.6	478.8
177.5°	481.3	479.5	479.8	482.7	479.1
180°	480.6	480.6	480.6	480.6	480.6

(END OF REPORT)