

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007566

Luminaire Tested: S123IP-B585UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007566
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B585UB2750-4F0-XX-W2A-1_5000K
Description: Define 3 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1940.0 lumens
Efficiency: N/A
Efficacy: 126.0 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 15.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007566

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007566

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007566

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	1.5	0.1
90°-100°	45.0	2.3
100°-110°	136.3	7.0
110°-120°	232.1	12.0
120°-130°	305.3	15.7
130°-140°	343.2	17.7
140°-150°	337.4	17.4
150°-160°	284.0	14.6
160°-170°	189.1	9.7
170°-180°	66.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	1.5	0.1
90°-120°	413.4	21.3
90°-150°	1399.2	72.1
90°-180°	1939.0	99.9
0°-180°	1940.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	6	13	15	16	2
95°	32	36	41	43	43	36
105°	124	125	130	130	131	132
115°	234	235	234	235	234	231
125°	342	344	342	340	338	305
135°	444	447	446	444	443	342
145°	538	539	541	540	538	336
155°	616	616	617	619	615	284
165°	671	669	669	673	669	189
175°	698	696	696	699	695	66
180°	700	700	700	700	700	

TEST NUMBER: P1007566

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.5	6.0	13.2	15.4	16.5
92.5°	16.5	19.8	23.1	24.7	23.6
95°	32.4	36.3	40.7	42.9	42.9
97.5°	53.3	56.1	59.4	62.1	61.6
100°	74.7	78.0	80.8	82.4	83.5
102.5°	99.5	101.1	105.0	106.6	106.1
105°	123.7	124.8	129.7	129.7	130.8
107.5°	152.2	152.8	155.0	156.6	156.1
110°	178.6	179.7	180.8	183.0	181.9

TEST NUMBER: P1007566

CATALOG NUMBER: S123IP-B585UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	206.1	206.6	206.6	209.4	209.4
115°	233.6	235.2	234.1	234.7	234.1
117.5°	261.6	262.2	261.1	261.1	259.4
120°	287.4	290.7	288.0	287.4	286.3
122.5°	314.4	316.6	315.5	313.8	312.2
125°	341.8	343.5	342.4	340.2	338.0
127.5°	367.1	370.4	369.3	366.0	363.8
130°	392.4	396.8	395.2	393.0	389.1
132.5°	417.7	422.1	421.0	418.2	415.5
135°	443.5	446.8	446.3	444.1	443.0
137.5°	467.1	469.9	471.5	468.8	467.1
140°	491.9	494.6	495.2	494.6	490.8
142.5°	514.4	517.2	518.3	517.7	515.0
145°	538.0	539.1	540.8	540.2	538.0
147.5°	558.4	560.6	562.2	562.2	558.9
150°	579.8	580.9	582.0	582.0	578.7
152.5°	597.4	599.0	599.6	600.7	597.9
155°	616.1	616.1	616.6	618.8	615.0
157.5°	632.0	631.5	632.0	634.2	630.9
160°	646.9	645.8	645.8	648.5	646.3
162.5°	660.1	658.4	659.0	661.7	657.9
165°	671.0	669.4	669.4	672.7	668.8
167.5°	680.4	678.2	678.7	682.0	678.7
170°	688.1	685.9	685.9	689.7	685.9
172.5°	694.1	691.9	691.9	695.2	691.4
175°	698.0	695.8	695.8	699.1	695.2
177.5°	700.2	698.0	698.0	701.3	697.4
180°	699.6	699.6	699.6	699.6	699.6

(END OF REPORT)