

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012429

Luminaire Tested: S123RDIP-B340D1025UB40-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012429
REPORT IS A COMBINATION OF REPORTS P993152 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1025UB40-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4918.5 lumens
Efficiency: N/A
Efficacy: 118.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 41.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012429

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012429

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	101	101	101	101		90	90	90	90		70	70	70		51	51	51		34	34	34
1	92	88	85	81		82	79	76	73		61	59	57		45	44	43		30	29	29
2	84	77	72	67		75	69	64	60		54	51	48		40	38	36		27	25	24
3	77	68	61	56		68	61	55	50		48	44	40		35	33	30		24	22	21
4	70	60	53	47		62	54	48	43		42	38	34		31	28	26		21	20	18
5	65	53	46	40		57	48	41	37		38	33	29		28	25	23		19	17	16
6	59	48	40	35		53	43	36	32		34	29	26		25	22	20		17	15	14
7	55	43	36	30		49	39	32	28		31	26	22		23	20	17		16	14	12
8	51	39	32	27		45	35	29	24		28	23	20		21	18	15		15	13	11
9	47	35	28	24		42	32	26	22		25	21	18		19	16	14		13	12	10
10	44	32	26	21		39	29	23	19		23	19	16		18	15	12		12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5985	5985	5985
5°	5994	5773	5756
10°	5947	5555	5446
15°	5870	5288	5106
20°	5769	4995	4725
25°	5664	4692	4364
30°	5529	4370	3938
35°	5392	4053	3550
40°	5263	3709	3121
45°	5095	3372	2736
50°	4913	3013	2337
55°	4722	2629	1971
60°	4540	2234	1600
65°	4305	1829	1249
70°	4011	1384	892
75°	3583	937	707
80°	3062	651	497
85°	2296	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5095 cd/sqm

TEST NUMBER: P1012429

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	1.1
10°-20°	145.4	3.0
20°-30°	209.3	4.3
30°-40°	235.7	4.8
40°-50°	225.5	4.6
50°-60°	184.6	3.8
60°-70°	124.4	2.5
70°-80°	62.4	1.3
80°-90°	19.0	0.4
90°-100°	275.8	5.6
100°-110°	771.0	15.7
110°-120°	751.8	15.3
120°-130°	598.6	12.2
130°-140°	472.5	9.6
140°-150°	352.5	7.2
150°-160°	246.0	5.0
160°-170°	144.5	2.9
170°-180°	47.0	1.0
0°-30°	407.0	8.3
0°-40°	642.7	13.1
0°-60°	1052.8	21.4
0°-90°	1258.7	25.6
90°-120°	1798.6	36.6
90°-150°	3222.4	65.5
90°-180°	3660.0	74.4
0°-180°	4918.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	556	556	556	556	556	
5°	556	554	548	552	551	53
15°	530	525	513	510	507	149
25°	482	471	450	441	436	222
35°	418	401	373	354	346	261
45°	343	323	288	262	252	265
55°	261	238	200	174	165	234
65°	178	153	118	96	91	176
75°	94	73	48	43	42	100
85°	24	14	13	12	12	26
90°	2	12	25	28	28	4
95°	33	109	583	170	114	35
105°	114	168	790	1382	1250	121
115°	201	251	604	1325	1520	199
125°	280	331	564	1022	1199	249
135°	328	392	556	842	972	254
145°	374	429	549	690	760	235
155°	426	459	532	604	630	196
165°	465	478	509	540	549	131
175°	484	485	488	495	494	46
180°	485	485	485	485	485	

TEST NUMBER: P1012429

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	556.0	556.0	556.0	556.0	556.0
2.5°	558.2	556.4	551.0	556.0	555.1
5°	556.0	553.7	548.3	552.3	551.4
7.5°	551.9	549.6	542.9	545.6	544.2
10°	546.5	543.3	535.2	535.7	533.4
12.5°	538.8	535.2	524.8	524.4	521.7
15°	530.3	525.3	512.7	510.4	507.3
17.5°	519.9	514.5	498.7	494.2	489.7
20°	508.2	500.9	483.8	477.9	472.5
22.5°	495.1	486.5	468.0	460.4	455.4
25°	482.5	471.2	450.4	441.0	436.0
27.5°	467.1	455.0	432.4	419.8	412.1
30°	451.3	437.8	412.6	397.2	390.0
32.5°	435.6	419.8	392.7	375.6	367.9
35°	417.5	401.3	373.3	354.0	345.8
37.5°	399.5	381.9	352.6	331.0	321.0
40°	382.4	362.5	330.5	307.1	296.7
42.5°	363.0	343.1	309.8	283.6	274.6
45°	343.1	322.8	288.1	262.4	251.6
47.5°	323.7	301.2	266.9	239.0	229.5
50°	302.1	280.9	244.4	216.4	206.1
52.5°	282.7	259.3	223.2	193.9	184.9
55°	260.6	238.5	200.2	174.0	165.0
57.5°	240.8	216.9	178.1	153.3	145.6
60°	220.0	195.2	157.8	133.5	125.8
62.5°	199.3	174.5	137.1	114.5	106.4
65°	178.1	153.3	118.1	96.0	91.1
67.5°	156.9	131.7	97.4	80.7	75.3
70°	136.2	111.8	80.3	64.5	59.5
72.5°	115.4	91.5	63.6	51.4	50.0
75°	94.2	72.6	47.8	43.3	42.4
77.5°	74.8	55.0	37.4	34.7	33.8
80°	56.4	37.9	28.4	27.1	26.2
82.5°	38.8	23.4	20.3	18.9	18.9
85°	23.9	14.0	12.6	11.7	11.7
87.5°	10.8	5.9	5.9	5.4	5.0
90°	2.0	11.8	24.6	27.5	28.5
92.5°	14.7	59.0	182.8	62.4	52.1
95°	33.4	108.6	582.7	170.0	114.0
97.5°	53.1	124.3	896.1	427.4	233.9
100°	72.7	137.0	930.5	894.2	616.1
102.5°	93.3	151.8	866.7	1197.3	975.7
105°	114.0	168.5	790.0	1381.6	1249.9
107.5°	135.6	188.2	722.2	1462.6	1428.7
110°	159.2	208.4	666.2	1465.1	1530.9

TEST NUMBER: P1012429

CATALOG NUMBER: S123RDIP-B340D1025UB40-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	180.8	229.4	628.9	1409.6	1551.5
115°	201.4	251.0	604.3	1325.0	1520.1
117.5°	222.1	271.7	587.6	1234.6	1451.3
120°	243.7	292.3	576.8	1149.2	1360.9
122.5°	262.4	312.0	569.9	1081.9	1276.4
125°	280.0	330.6	564.0	1021.9	1198.8
127.5°	293.8	348.4	561.1	972.8	1132.0
130°	306.6	364.0	558.1	927.6	1076.9
132.5°	316.4	378.3	557.1	885.4	1022.9
135°	328.2	391.6	556.2	841.6	971.8
137.5°	339.0	402.4	554.2	800.3	917.8
140°	349.8	412.2	553.2	760.0	860.8
142.5°	361.6	421.0	551.2	723.2	807.7
145°	374.4	428.9	549.3	690.2	759.6
147.5°	387.1	437.2	546.3	664.8	718.3
150°	399.9	444.2	542.4	642.2	682.9
152.5°	412.7	451.6	537.5	622.5	653.4
155°	425.5	458.9	531.6	604.3	629.9
157.5°	435.3	465.3	526.7	586.6	607.3
160°	447.1	470.7	520.8	570.4	585.6
162.5°	455.9	474.6	514.9	555.2	566.0
165°	464.8	478.0	509.0	540.0	549.3
167.5°	471.7	481.0	503.1	526.7	532.6
170°	477.6	482.4	497.2	514.9	517.8
172.5°	481.5	483.9	492.3	504.6	504.1
175°	484.4	484.9	488.4	495.2	494.3
177.5°	486.4	485.4	485.4	489.3	487.4
180°	485.4	485.4	485.4	485.4	485.4

(END OF REPORT)