

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007592

Luminaire Tested: S123IP-B805UB2750-4F0-XX-W2A-1_2700K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B805UB2750-4F0-XX-W2A-1_2700K
Description: Define 3 Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2672.0 lumens
Efficiency: N/A
Efficacy: 126.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007592

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1007592

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007592

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	62.0	2.3
100°-110°	187.7	7.0
110°-120°	319.6	12.0
120°-130°	420.5	15.7
130°-140°	472.6	17.7
140°-150°	464.7	17.4
150°-160°	391.2	14.6
160°-170°	260.4	9.7
170°-180°	91.2	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	569.4	21.3
90°-150°	1927.2	72.1
90°-180°	2670.0	99.9
0°-180°	2672.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	18	21	23	3
95°	45	50	56	59	59	49
105°	170	172	179	179	180	182
115°	322	324	322	323	322	318
125°	471	473	472	469	466	420
135°	611	615	615	612	610	471
145°	741	743	745	744	741	463
155°	848	848	849	852	847	391
165°	924	922	922	926	921	261
175°	961	958	958	963	958	91
180°	964	964	964	964	964	

TEST NUMBER: P1007592

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	8.3	18.2	21.2	22.7
92.5°	22.7	27.3	31.8	34.1	32.5
95°	44.7	50.0	56.0	59.0	59.0
97.5°	73.4	77.2	81.8	85.5	84.8
100°	102.9	107.5	111.3	113.5	115.1
102.5°	137.0	139.3	144.6	146.8	146.1
105°	170.3	171.8	178.6	178.6	180.2
107.5°	209.7	210.4	213.5	215.7	215.0
110°	246.0	247.5	249.0	252.1	250.6

TEST NUMBER: P1007592

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	283.9	284.6	284.6	288.4	288.4
115°	321.7	324.0	322.5	323.2	322.5
117.5°	360.3	361.1	359.6	359.6	357.3
120°	395.9	400.4	396.6	395.9	394.4
122.5°	433.0	436.0	434.5	432.2	429.9
125°	470.8	473.1	471.6	468.6	465.5
127.5°	505.6	510.2	508.7	504.1	501.1
130°	540.5	546.5	544.2	541.2	535.9
132.5°	575.3	581.3	579.8	576.0	572.3
135°	610.9	615.4	614.6	611.6	610.1
137.5°	643.4	647.2	649.5	645.7	643.4
140°	677.5	681.3	682.0	681.3	676.0
142.5°	708.5	712.3	713.8	713.0	709.3
145°	741.1	742.6	744.8	744.1	741.1
147.5°	769.1	772.1	774.4	774.4	769.8
150°	798.6	800.1	801.6	801.6	797.1
152.5°	822.8	825.1	825.8	827.3	823.6
155°	848.5	848.5	849.3	852.3	847.0
157.5°	870.5	869.7	870.5	873.5	869.0
160°	890.9	889.4	889.4	893.2	890.2
162.5°	909.1	906.8	907.6	911.4	906.1
165°	924.2	922.0	922.0	926.5	921.2
167.5°	937.1	934.1	934.8	939.4	934.8
170°	947.7	944.7	944.7	950.0	944.7
172.5°	956.0	953.0	953.0	957.5	952.2
175°	961.3	958.3	958.3	962.8	957.5
177.5°	964.4	961.3	961.3	965.9	960.6
180°	963.6	963.6	963.6	963.6	963.6

(END OF REPORT)