

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007593

Luminaire Tested: S123IP-B805UB2750-4F0-XX-W2A-1_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B805UB2750-4F0-XX-W2A-1_3000K
Description: Define 3 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2695.0 lumens
Efficiency: N/A
Efficacy: 127.7 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007593

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007593

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007593

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	62.6	2.3
100°-110°	189.4	7.0
110°-120°	322.4	12.0
120°-130°	424.1	15.7
130°-140°	476.7	17.7
140°-150°	468.7	17.4
150°-160°	394.6	14.6
160°-170°	262.7	9.7
170°-180°	92.0	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	574.3	21.3
90°-150°	1943.8	72.1
90°-180°	2693.0	99.9
0°-180°	2695.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	18	21	23	3
95°	45	50	56	60	60	50
105°	172	173	180	180	182	184
115°	324	327	325	326	325	321
125°	475	477	476	473	470	424
135°	616	621	620	617	615	475
145°	747	749	751	750	747	467
155°	856	856	857	860	854	394
165°	932	930	930	934	929	263
175°	970	967	967	971	966	92
180°	972	972	972	972	972	

TEST NUMBER: P1007593

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	8.4	18.3	21.4	22.9
92.5°	22.9	27.5	32.1	34.4	32.8
95°	45.0	50.4	56.5	59.6	59.6
97.5°	74.1	77.9	82.5	86.3	85.5
100°	103.8	108.4	112.2	114.5	116.0
102.5°	138.2	140.5	145.8	148.1	147.3
105°	171.8	173.3	180.2	180.2	181.7
107.5°	211.5	212.2	215.3	217.6	216.8
110°	248.1	249.7	251.2	254.2	252.7

TEST NUMBER: P1007593

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	286.3	287.1	287.1	290.9	290.9
115°	324.5	326.8	325.2	326.0	325.2
117.5°	363.4	364.2	362.6	362.6	360.4
120°	399.3	403.9	400.1	399.3	397.8
122.5°	436.7	439.8	438.2	435.9	433.7
125°	474.9	477.2	475.6	472.6	469.5
127.5°	510.0	514.6	513.1	508.5	505.4
130°	545.1	551.2	548.9	545.9	540.5
132.5°	580.2	586.3	584.8	581.0	577.2
135°	616.1	620.7	619.9	616.9	615.4
137.5°	648.9	652.8	655.1	651.2	648.9
140°	683.3	687.1	687.9	687.1	681.8
142.5°	714.6	718.4	720.0	719.2	715.4
145°	747.4	749.0	751.3	750.5	747.4
147.5°	775.7	778.7	781.0	781.0	776.4
150°	805.5	807.0	808.5	808.5	803.9
152.5°	829.9	832.2	832.9	834.5	830.7
155°	855.8	855.8	856.6	859.7	854.3
157.5°	878.0	877.2	878.0	881.0	876.5
160°	898.6	897.1	897.1	900.9	897.8
162.5°	916.9	914.6	915.4	919.2	913.9
165°	932.2	929.9	929.9	934.5	929.1
167.5°	945.2	942.1	942.9	947.5	942.9
170°	955.9	952.8	952.8	958.2	952.8
172.5°	964.3	961.2	961.2	965.8	960.4
175°	969.6	966.6	966.6	971.1	965.8
177.5°	972.7	969.6	969.6	974.2	968.8
180°	971.9	971.9	971.9	971.9	971.9

(END OF REPORT)