

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007596

Luminaire Tested: S123IP-B805UB2750-4F0-XX-W2A-1_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-9)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B805UB2750-4F0-XX-W2A-1_5000K
Description: Define 3 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2592.0 lumens
Efficiency: N/A
Efficacy: 122.8 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007596

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007596

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007596

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	60.2	2.3
100°-110°	182.1	7.0
110°-120°	310.1	12.0
120°-130°	407.9	15.7
130°-140°	458.5	17.7
140°-150°	450.7	17.4
150°-160°	379.5	14.6
160°-170°	252.6	9.7
170°-180°	88.5	3.4
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	552.3	21.3
90°-150°	1869.5	72.1
90°-180°	2590.0	99.9
0°-180°	2592.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	18	21	22	3
95°	43	48	54	57	57	48
105°	165	167	173	173	175	177
115°	312	314	313	314	313	309
125°	457	459	458	454	452	407
135°	593	597	596	593	592	457
145°	719	720	722	722	719	449
155°	823	823	824	827	822	379
165°	897	894	894	899	894	253
175°	932	930	930	934	929	89
180°	935	935	935	935	935	

TEST NUMBER: P1007596

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.7	8.1	17.6	20.6	22.0
92.5°	22.0	26.4	30.8	33.0	31.6
95°	43.3	48.5	54.3	57.3	57.3
97.5°	71.2	74.9	79.3	83.0	82.2
100°	99.9	104.3	107.9	110.1	111.6
102.5°	132.9	135.1	140.2	142.5	141.7
105°	165.2	166.7	173.3	173.3	174.8
107.5°	203.4	204.1	207.1	209.3	208.5
110°	238.6	240.1	241.6	244.5	243.0

TEST NUMBER: P1007596

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A-1_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	275.4	276.1	276.1	279.8	279.8
115°	312.1	314.3	312.8	313.5	312.8
117.5°	349.5	350.3	348.8	348.8	346.6
120°	384.0	388.4	384.8	384.0	382.6
122.5°	420.0	423.0	421.5	419.3	417.1
125°	456.7	458.9	457.5	454.5	451.6
127.5°	490.5	494.9	493.4	489.0	486.1
130°	524.3	530.2	528.0	525.0	519.9
132.5°	558.1	563.9	562.5	558.8	555.1
135°	592.6	597.0	596.2	593.3	591.8
137.5°	624.1	627.8	630.0	626.3	624.1
140°	657.2	660.9	661.6	660.9	655.7
142.5°	687.3	691.0	692.4	691.7	688.0
145°	718.9	720.3	722.5	721.8	718.9
147.5°	746.0	749.0	751.2	751.2	746.8
150°	774.7	776.1	777.6	777.6	773.2
152.5°	798.2	800.4	801.1	802.6	798.9
155°	823.1	823.1	823.9	826.8	821.7
157.5°	844.4	843.7	844.4	847.4	843.0
160°	864.3	862.8	862.8	866.5	863.5
162.5°	881.9	879.7	880.4	884.1	878.9
165°	896.6	894.4	894.4	898.8	893.6
167.5°	909.1	906.1	906.8	911.3	906.8
170°	919.3	916.4	916.4	921.5	916.4
172.5°	927.4	924.5	924.5	928.9	923.7
175°	932.5	929.6	929.6	934.0	928.9
177.5°	935.5	932.5	932.5	937.0	931.8
180°	934.8	934.8	934.8	934.8	934.8

(END OF REPORT)