

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012439

Luminaire Tested: S123RDIP-B340D1195UB27-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012439
REPORT IS A COMBINATION OF REPORTS P993162 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB27-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5979.0 lumens
Efficiency: N/A
Efficacy: 124.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012439

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1012439

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	100	100	100	100	89	89	89	89	67	67	67	48	48	48	29	29	29
1	91	87	84	80	81	77	74	72	59	57	55	42	41	40	26	26	25
2	83	76	71	66	74	68	63	59	52	49	46	37	35	33	23	22	21
3	76	67	60	55	67	60	54	49	46	42	39	33	30	28	21	19	18
4	69	59	52	46	61	53	47	42	41	36	33	29	26	24	19	17	16
5	64	53	45	39	56	47	41	36	36	32	28	26	23	21	17	15	14
6	59	47	40	34	52	42	36	31	32	28	24	24	21	18	15	13	12
7	54	42	35	30	48	38	31	27	29	25	21	21	18	16	14	12	11
8	50	38	31	26	44	34	28	24	27	22	19	19	16	14	13	11	10
9	46	35	28	23	41	31	25	21	24	20	17	18	15	13	12	10	9
10	43	32	25	20	38	29	23	19	22	18	15	16	13	11	11	9	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5970	5970	5970
5°	5979	5759	5743
10°	5933	5542	5433
15°	5856	5274	5093
20°	5754	4984	4714
25°	5650	4681	4354
30°	5517	4359	3929
35°	5379	4043	3541
40°	5249	3700	3114
45°	5084	3364	2729
50°	4901	3006	2331
55°	4711	2622	1966
60°	4529	2229	1596
65°	4296	1826	1246
70°	3999	1381	891
75°	3576	935	706
80°	3051	649	495
85°	2286	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 5084 cd/sqm

TEST NUMBER: P1012439

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	0.9
10°-20°	145.0	2.4
20°-30°	208.8	3.5
30°-40°	235.2	3.9
40°-50°	225.0	3.8
50°-60°	184.1	3.1
60°-70°	124.2	2.1
70°-80°	62.3	1.0
80°-90°	19.4	0.3
90°-100°	54.6	0.9
100°-110°	264.1	4.4
110°-120°	647.3	10.8
120°-130°	821.7	13.7
130°-140°	877.8	14.7
140°-150°	820.8	13.7
150°-160°	662.1	11.1
160°-170°	427.3	7.1
170°-180°	147.2	2.5
0°-30°	406.0	6.8
0°-40°	641.2	10.7
0°-60°	1050.3	17.6
0°-90°	1256.1	21.0
90°-120°	966.0	16.2
90°-150°	3486.3	58.3
90°-180°	4723.0	79.0
0°-180°	5979.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	555	555	555	555	555	
5°	555	552	547	551	550	53
15°	529	524	511	509	506	149
25°	481	470	449	440	435	221
35°	416	400	372	353	345	261
45°	342	322	287	262	251	264
55°	260	238	200	174	165	233
65°	178	153	118	96	91	176
75°	94	72	48	43	42	100
85°	24	14	13	12	12	26
90°	1	13	28	32	34	5
95°	70	23	36	44	44	84
105°	343	356	252	48	51	364
115°	643	650	661	672	677	635
125°	907	916	921	923	925	810
135°	1129	1136	1141	1144	1141	869
145°	1303	1311	1313	1316	1316	816
155°	1435	1433	1434	1440	1433	661
165°	1514	1510	1509	1518	1510	428
175°	1549	1544	1545	1553	1544	147
180°	1549	1549	1549	1549	1549	

TEST NUMBER: P1012439

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	554.6	554.6	554.6	554.6	554.6
2.5°	556.9	555.1	549.7	554.6	553.7
5°	554.6	552.4	547.0	551.0	550.1
7.5°	550.6	548.3	541.6	544.3	542.9
10°	545.2	542.0	533.9	534.4	532.1
12.5°	537.5	533.9	523.6	523.1	520.4
15°	529.0	524.0	511.4	509.2	506.0
17.5°	518.6	513.2	497.5	493.0	488.5
20°	506.9	499.7	482.7	476.8	471.4
22.5°	493.9	485.4	466.9	459.3	454.3
25°	481.3	470.1	449.4	439.9	435.0
27.5°	466.0	453.9	431.4	418.8	411.1
30°	450.3	436.8	411.6	396.3	389.1
32.5°	434.5	418.8	391.8	374.7	367.1
35°	416.5	400.3	372.4	353.1	345.0
37.5°	398.5	381.0	351.8	330.2	320.3
40°	381.4	361.7	329.7	306.3	296.0
42.5°	362.1	342.3	309.0	282.9	273.9
45°	342.3	322.1	287.4	261.8	251.0
47.5°	323.0	300.5	266.3	238.4	229.0
50°	301.4	280.2	243.8	215.9	205.6
52.5°	282.0	258.6	222.7	193.4	184.4
55°	260.0	238.0	199.7	173.6	164.6
57.5°	240.2	216.4	177.7	152.9	145.3
60°	219.5	194.8	157.4	133.1	125.5
62.5°	198.8	174.1	136.7	114.3	106.2
65°	177.7	152.9	117.9	95.8	90.9
67.5°	156.5	131.3	97.2	80.5	75.1
70°	135.8	111.6	80.1	64.3	59.4
72.5°	115.2	91.3	63.4	51.3	49.9
75°	94.0	72.4	47.7	43.2	42.3
77.5°	74.7	54.9	37.3	34.6	33.7
80°	56.2	37.8	28.3	27.0	26.1
82.5°	38.7	23.4	20.2	18.9	18.9
85°	23.8	13.9	12.6	11.7	11.7
87.5°	10.8	5.8	5.8	5.4	4.9
90°	1.2	12.7	27.6	32.2	34.5
92.5°	26.5	19.6	29.9	38.0	39.1
95°	70.2	23.0	35.7	43.7	43.7
97.5°	127.8	95.5	36.8	46.0	47.2
100°	194.5	217.5	38.0	47.2	48.3
102.5°	270.5	285.4	85.2	47.2	49.5
105°	343.0	355.7	252.1	48.3	50.6
107.5°	420.1	430.5	447.7	270.5	119.7
110°	497.2	506.4	519.1	481.1	316.5

TEST NUMBER: P1012439

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	570.9	578.9	591.6	602.0	599.7
115°	643.4	650.3	660.7	672.2	676.8
117.5°	714.8	722.8	728.6	737.8	738.9
120°	780.4	790.7	794.2	803.4	803.4
122.5°	847.1	855.2	859.8	865.5	866.7
125°	907.0	916.2	920.8	923.1	925.4
127.5°	966.8	976.0	981.8	985.2	982.9
130°	1022.1	1031.3	1035.9	1040.5	1038.2
132.5°	1075.0	1084.2	1087.7	1092.3	1088.8
135°	1129.1	1136.0	1140.6	1144.1	1140.6
137.5°	1175.1	1184.4	1186.7	1192.4	1190.1
140°	1221.2	1228.1	1231.5	1236.1	1233.8
142.5°	1263.8	1270.7	1274.1	1277.6	1274.1
145°	1302.9	1311.0	1313.3	1315.6	1315.6
147.5°	1340.9	1346.6	1348.9	1351.2	1345.5
150°	1375.4	1378.9	1381.2	1383.5	1380.0
152.5°	1406.5	1407.6	1408.8	1413.4	1407.6
155°	1435.3	1433.0	1434.1	1439.9	1433.0
157.5°	1458.3	1458.3	1457.1	1464.0	1454.8
160°	1479.0	1477.9	1476.7	1483.6	1475.6
162.5°	1498.6	1495.1	1494.0	1502.0	1495.1
165°	1513.5	1510.1	1508.9	1518.1	1510.1
167.5°	1526.2	1521.6	1521.6	1530.8	1521.6
170°	1536.6	1531.9	1531.9	1541.2	1531.9
172.5°	1543.5	1537.7	1538.9	1548.1	1537.7
175°	1549.2	1543.5	1544.6	1552.7	1543.5
177.5°	1551.5	1545.8	1546.9	1556.1	1544.6
180°	1549.2	1549.2	1549.2	1549.2	1549.2

(END OF REPORT)