

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012441

Luminaire Tested: S123RDIP-B340D1195UB27-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012441
REPORT IS A COMBINATION OF REPORTS P993164 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB27-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5543.9 lumens
Efficiency: N/A
Efficacy: 115.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012441

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012441

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31			23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	26			19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22			16
3	76	67	61	55	67	60	54	50	46	42	39	34	31	29	22	20	19			14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	17			12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15			11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13			9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11			8
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10			8
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	11	9			7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5970	5970	5970
5°	5979	5759	5743
10°	5933	5542	5433
15°	5856	5274	5093
20°	5754	4984	4714
25°	5650	4681	4354
30°	5517	4359	3929
35°	5379	4043	3541
40°	5249	3700	3114
45°	5084	3364	2729
50°	4901	3006	2331
55°	4711	2622	1966
60°	4529	2229	1596
65°	4296	1826	1246
70°	3999	1381	891
75°	3576	935	706
80°	3051	649	495
85°	2286	351	259

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5084 cd/sqm

TEST NUMBER: P1012441

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.1	0.9
10°-20°	145.0	2.6
20°-30°	208.8	3.8
30°-40°	235.2	4.2
40°-50°	225.0	4.1
50°-60°	184.1	3.3
60°-70°	124.2	2.2
70°-80°	62.3	1.1
80°-90°	19.4	0.4
90°-100°	323.2	5.8
100°-110°	903.3	16.3
110°-120°	880.8	15.9
120°-130°	701.4	12.7
130°-140°	553.6	10.0
140°-150°	413.0	7.5
150°-160°	288.1	5.2
160°-170°	169.3	3.1
170°-180°	55.1	1.0
0°-30°	406.0	7.3
0°-40°	641.2	11.6
0°-60°	1050.3	18.9
0°-90°	1256.2	22.7
90°-120°	2107.3	38.0
90°-150°	3775.3	68.1
90°-180°	4288.0	77.3
0°-180°	5543.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	555	555	555	555	555	
5°	555	552	547	551	550	53
15°	529	524	511	509	506	149
25°	481	470	449	440	435	221
35°	416	400	372	353	345	261
45°	342	322	287	262	251	264
55°	260	238	200	174	165	233
65°	178	153	118	96	91	176
75°	94	72	48	43	42	100
85°	24	14	13	12	12	26
90°	2	14	29	32	33	4
95°	39	127	683	199	134	41
105°	134	197	926	1619	1464	142
115°	236	294	708	1552	1781	234
125°	328	387	661	1197	1404	291
135°	384	459	652	986	1139	297
145°	439	502	644	809	890	275
155°	498	538	623	708	738	229
165°	544	560	596	633	644	153
175°	568	568	572	580	579	54
180°	569	569	569	569	569	

TEST NUMBER: P1012441

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	554.6	554.6	554.6	554.6	554.6
2.5°	556.9	555.1	549.7	554.6	553.7
5°	554.6	552.4	547.0	551.0	550.1
7.5°	550.6	548.3	541.6	544.3	542.9
10°	545.2	542.0	533.9	534.4	532.1
12.5°	537.5	533.9	523.6	523.1	520.4
15°	529.0	524.0	511.4	509.2	506.0
17.5°	518.6	513.2	497.5	493.0	488.5
20°	506.9	499.7	482.7	476.8	471.4
22.5°	493.9	485.4	466.9	459.3	454.3
25°	481.3	470.1	449.4	439.9	435.0
27.5°	466.0	453.9	431.4	418.8	411.1
30°	450.3	436.8	411.6	396.3	389.1
32.5°	434.5	418.8	391.8	374.7	367.1
35°	416.5	400.3	372.4	353.1	345.0
37.5°	398.5	381.0	351.8	330.2	320.3
40°	381.4	361.7	329.7	306.3	296.0
42.5°	362.1	342.3	309.0	282.9	273.9
45°	342.3	322.1	287.4	261.8	251.0
47.5°	323.0	300.5	266.3	238.4	229.0
50°	301.4	280.2	243.8	215.9	205.6
52.5°	282.0	258.6	222.7	193.4	184.4
55°	260.0	238.0	199.7	173.6	164.6
57.5°	240.2	216.4	177.7	152.9	145.3
60°	219.5	194.8	157.4	133.1	125.5
62.5°	198.8	174.1	136.7	114.3	106.2
65°	177.7	152.9	117.9	95.8	90.9
67.5°	156.5	131.3	97.2	80.5	75.1
70°	135.8	111.6	80.1	64.3	59.4
72.5°	115.2	91.3	63.4	51.3	49.9
75°	94.0	72.4	47.7	43.2	42.3
77.5°	74.7	54.9	37.3	34.6	33.7
80°	56.2	37.8	28.3	27.0	26.1
82.5°	38.7	23.4	20.2	18.9	18.9
85°	23.8	13.9	12.6	11.7	11.7
87.5°	10.8	5.8	5.8	5.4	4.9
90°	2.3	13.8	28.8	32.2	33.4
92.5°	17.3	69.1	214.1	73.1	61.0
95°	39.1	127.2	682.7	199.2	133.5
97.5°	62.2	145.6	1049.9	500.8	274.0
100°	85.2	160.6	1090.2	1047.6	721.8
102.5°	109.4	177.8	1015.4	1402.8	1143.2
105°	133.5	197.4	925.6	1618.6	1464.4
107.5°	158.9	220.5	846.1	1713.6	1673.9
110°	186.5	244.0	780.5	1716.5	1793.6

TEST NUMBER: P1012441

CATALOG NUMBER: S123RDIP-B340D1195UB27-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	211.8	268.8	736.8	1651.4	1817.8
115°	236.0	294.2	708.0	1552.4	1780.9
117.5°	260.2	318.3	688.4	1446.6	1700.4
120°	285.5	342.5	675.8	1346.4	1594.4
122.5°	307.4	365.6	667.7	1267.5	1495.4
125°	328.1	387.4	660.8	1197.2	1404.5
127.5°	344.2	408.2	657.3	1139.7	1326.2
130°	359.2	426.6	653.9	1086.8	1261.7
132.5°	370.7	443.2	652.7	1037.2	1198.4
135°	384.5	458.8	651.6	986.0	1138.6
137.5°	397.2	471.4	649.3	937.6	1075.2
140°	409.8	482.9	648.1	890.4	1008.5
142.5°	423.7	493.3	645.8	847.3	946.3
145°	438.6	502.5	643.5	808.7	889.9
147.5°	453.6	512.3	640.1	778.8	841.5
150°	468.5	520.4	635.5	752.3	800.1
152.5°	483.5	529.0	629.7	729.3	765.6
155°	498.5	537.7	622.8	708.0	737.9
157.5°	510.0	545.1	617.1	687.2	711.5
160°	523.8	551.4	610.1	668.3	686.1
162.5°	534.2	556.0	603.2	650.4	663.1
165°	544.5	560.0	596.3	632.6	643.5
167.5°	552.6	563.5	589.4	617.1	624.0
170°	559.5	565.2	582.5	603.2	606.7
172.5°	564.1	567.0	576.8	591.2	590.6
175°	567.6	568.2	572.2	580.2	579.1
177.5°	569.9	568.7	568.7	573.3	571.0
180°	568.7	568.7	568.7	568.7	568.7

(END OF REPORT)