

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012446

Luminaire Tested: S123RDIP-B340D1195UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012446
REPORT IS A COMBINATION OF REPORTS P993179 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5362.0 lumens
Efficiency: N/A
Efficacy: 111.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012446

CATALOG NUMBER: S123RDIP-B340D1195UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012446

CATALOG NUMBER: S123RDIP-B340D1195UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	49	49	49	32	32	32
1	92	88	84	81	82	78	75	72	60	58	56	44	42	41	28	28	27
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	32	29	22	21	20
4	70	60	52	47	62	53	47	42	41	37	34	30	28	25	20	18	17
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15
6	59	48	40	34	52	43	36	31	33	29	25	25	21	19	16	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	13	11	9
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1012446

CATALOG NUMBER: S123RDIP-B340D1195UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	1.0
10°-20°	146.2	2.7
20°-30°	210.5	3.9
30°-40°	237.1	4.4
40°-50°	226.7	4.2
50°-60°	185.6	3.5
60°-70°	125.1	2.3
70°-80°	62.8	1.2
80°-90°	19.5	0.4
90°-100°	95.2	1.8
100°-110°	288.0	5.4
110°-120°	490.3	9.1
120°-130°	645.0	12.0
130°-140°	725.0	13.5
140°-150°	712.8	13.3
150°-160°	600.1	11.2
160°-170°	399.5	7.5
170°-180°	139.9	2.6
0°-30°	409.2	7.6
0°-40°	646.3	12.1
0°-60°	1058.7	19.7
0°-90°	1266.1	23.6
90°-120°	873.5	16.3
90°-150°	2956.4	55.1
90°-180°	4096.0	76.4
0°-180°	5362.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	13	28	32	35	7
95°	68	77	86	91	91	75
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	722	726	723	719	714	644
135°	937	944	943	938	936	722
145°	1137	1139	1143	1142	1137	710
155°	1302	1302	1303	1308	1299	599
165°	1418	1414	1414	1421	1413	400
175°	1475	1470	1470	1477	1469	140
180°	1478	1478	1478	1478	1478	

TEST NUMBER: P1012446

CATALOG NUMBER: S123RDIP-B340D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	1.2	12.8	27.9	32.5	34.8
92.5°	34.8	41.8	48.8	52.3	49.9
95°	68.5	76.6	85.9	90.6	90.6
97.5°	112.6	118.4	125.4	131.2	130.1
100°	157.9	164.9	170.7	174.2	176.5
102.5°	210.2	213.7	221.8	225.3	224.1
105°	261.3	263.6	274.0	274.0	276.4
107.5°	321.7	322.8	327.5	330.9	329.8
110°	377.4	379.7	382.0	386.7	384.4

TEST NUMBER: P1012446

CATALOG NUMBER: S123RDIP-B340D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.5	436.6	436.6	442.4	442.4
115°	493.5	497.0	494.7	495.8	494.7
117.5°	552.7	553.9	551.6	551.6	548.1
120°	607.3	614.3	608.5	607.3	605.0
122.5°	664.2	668.9	666.5	663.1	659.6
125°	722.3	725.8	723.4	718.8	714.1
127.5°	775.7	782.7	780.3	773.4	768.7
130°	829.1	838.4	834.9	830.3	822.1
132.5°	882.5	891.8	889.5	883.7	877.9
135°	937.1	944.1	942.9	938.3	935.9
137.5°	987.0	992.8	996.3	990.5	987.0
140°	1039.3	1045.1	1046.2	1045.1	1037.0
142.5°	1086.9	1092.7	1095.0	1093.9	1088.1
145°	1136.8	1139.1	1142.6	1141.5	1136.8
147.5°	1179.8	1184.4	1187.9	1187.9	1180.9
150°	1225.1	1227.4	1229.7	1229.7	1222.8
152.5°	1262.2	1265.7	1266.9	1269.2	1263.4
155°	1301.7	1301.7	1302.9	1307.5	1299.4
157.5°	1335.4	1334.2	1335.4	1340.0	1333.1
160°	1366.7	1364.4	1364.4	1370.2	1365.6
162.5°	1394.6	1391.1	1392.3	1398.1	1390.0
165°	1417.8	1414.4	1414.4	1421.3	1413.2
167.5°	1437.6	1432.9	1434.1	1441.1	1434.1
170°	1453.8	1449.2	1449.2	1457.3	1449.2
172.5°	1466.6	1462.0	1462.0	1468.9	1460.8
175°	1474.7	1470.1	1470.1	1477.1	1468.9
177.5°	1479.4	1474.7	1474.7	1481.7	1473.6
180°	1478.2	1478.2	1478.2	1478.2	1478.2

(END OF REPORT)