

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007603

Luminaire Tested: S123IP-B805UB2750-4F0-XX-W2A_3000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B805UB2750-4F0-XX-W2A_3000K
Description: Define 3 Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3135.0 lumens
Efficiency: N/A
Efficacy: 148.6 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007603

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007603

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007603

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.1	0.1
90°-100°	36.2	1.2
100°-110°	175.2	5.6
110°-120°	429.3	13.7
120°-130°	545.1	17.4
130°-140°	582.3	18.6
140°-150°	544.5	17.4
150°-160°	439.2	14.0
160°-170°	283.4	9.0
170°-180°	97.7	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.1	0.1
90°-120°	640.8	20.4
90°-150°	2312.6	73.8
90°-180°	3133.0	99.9
0°-180°	3135.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	18	21	23	3
95°	47	15	24	29	29	56
105°	228	236	167	32	34	241
115°	427	431	438	446	449	422
125°	602	608	611	612	614	538
135°	749	754	757	759	757	577
145°	864	870	871	873	873	541
155°	952	951	951	955	951	439
165°	1004	1002	1001	1007	1002	284
175°	1028	1024	1025	1030	1024	98
180°	1028	1028	1028	1028	1028	

TEST NUMBER: P1007603

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.8	8.4	18.3	21.4	22.9
92.5°	17.6	13.0	19.9	25.2	26.0
95°	46.6	15.3	23.7	29.0	29.0
97.5°	84.7	63.4	24.4	30.5	31.3
100°	129.0	144.3	25.2	31.3	32.1
102.5°	179.4	189.3	56.5	31.3	32.8
105°	227.5	235.9	167.2	32.1	33.6
107.5°	278.7	285.5	297.0	179.4	79.4
110°	329.8	335.9	344.3	319.1	210.0

TEST NUMBER: P1007603

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	384.0	392.4	399.3	397.8
115°	426.8	431.4	438.2	445.9	448.9
117.5°	474.1	479.5	483.3	489.4	490.2
120°	517.7	524.5	526.8	532.9	532.9
122.5°	561.9	567.3	570.3	574.2	574.9
125°	601.6	607.7	610.8	612.3	613.9
127.5°	641.3	647.4	651.3	653.6	652.0
130°	678.0	684.1	687.2	690.2	688.7
132.5°	713.1	719.2	721.5	724.6	722.3
135°	749.0	753.6	756.6	758.9	756.6
137.5°	779.5	785.6	787.2	791.0	789.5
140°	810.1	814.7	816.9	820.0	818.5
142.5°	838.3	842.9	845.2	847.5	845.2
145°	864.3	869.6	871.2	872.7	872.7
147.5°	889.5	893.3	894.8	896.4	892.5
150°	912.4	914.7	916.2	917.7	915.4
152.5°	933.0	933.8	934.5	937.6	933.8
155°	952.1	950.6	951.3	955.1	950.6
157.5°	967.4	967.4	966.6	971.2	965.1
160°	981.1	980.3	979.6	984.2	978.8
162.5°	994.1	991.8	991.0	996.4	991.8
165°	1004.0	1001.7	1001.0	1007.1	1001.7
167.5°	1012.4	1009.3	1009.3	1015.5	1009.3
170°	1019.3	1016.2	1016.2	1022.3	1016.2
172.5°	1023.9	1020.0	1020.8	1026.9	1020.0
175°	1027.7	1023.9	1024.6	1030.0	1023.9
177.5°	1029.2	1025.4	1026.1	1032.3	1024.6
180°	1027.7	1027.7	1027.7	1027.7	1027.7

(END OF REPORT)