

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1007606

Luminaire Tested: S123IP-B805UB2750-4F0-XX-W2A_5000K

Issue Date: 5/5/2025

Test Information

Test Method: LM-79-2019
Report Number: P1007606
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-5)
Test Lab: INNOVATION CENTER
Issue Date: 5/5/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123IP-B805UB2750-4F0-XX-W2A_5000K
Description: Define 3 Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015} {m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3015.0 lumens
Efficiency: N/A
Efficacy: 142.9 lumens/watt
Spacing Criteria (0/90/45): - / - / -
Luminous Opening: Rectangular (W 0.25' x L: 4' x H: 0')
CIE Type: Indirect

Input Watts (W): 21.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1007606

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1007606

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	95	95	95	95	81	81	81	81	56	56	56	32	32	32	10	10	10	10	10	10	0
1	87	83	79	76	74	71	68	65	48	47	45	28	27	26	9	9	8	8	8	8	0
2	79	72	66	62	67	62	57	53	42	40	37	24	23	22	8	7	7	7	7	7	0
3	72	63	56	51	61	54	49	44	37	34	31	21	20	18	7	6	6	6	6	6	0
4	65	56	48	43	56	48	42	37	33	29	26	19	17	16	6	6	5	5	5	5	0
5	60	49	42	36	51	42	36	32	29	25	22	17	15	13	5	5	4	4	4	4	0
6	55	44	36	31	47	38	32	27	26	22	19	15	13	11	5	4	4	4	4	4	0
7	50	39	32	27	43	34	28	23	23	19	17	14	11	10	4	4	3	3	3	3	0
8	47	35	28	23	40	30	24	20	21	17	14	12	10	9	4	3	3	3	3	3	0
9	43	32	25	20	37	27	22	18	19	15	13	11	9	8	4	3	3	3	3	3	0
10	40	29	22	18	34	25	19	16	17	14	11	10	8	7	3	3	2	2	2	2	0

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	0	0	0
5°	0	0	0
10°	0	0	0
15°	0	0	0
20°	0	0	0
25°	0	0	0
30°	0	0	0
35°	0	0	0
40°	0	0	0
45°	0	0	0
50°	0	0	0
55°	0	0	0
60°	0	0	0
65°	0	0	0
70°	0	0	0
75°	0	0	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 0°
Luminance: 0 cd/sqm

TEST NUMBER: P1007606

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.0	0.0
20°-30°	0.0	0.0
30°-40°	0.0	0.0
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	2.0	0.1
90°-100°	34.9	1.2
100°-110°	168.5	5.6
110°-120°	412.9	13.7
120°-130°	524.2	17.4
130°-140°	560.0	18.6
140°-150°	523.6	17.4
150°-160°	422.4	14.0
160°-170°	272.6	9.0
170°-180°	93.9	3.1
0°-30°	0.0	0.0
0°-40°	0.0	0.0
0°-60°	0.0	0.0
0°-90°	2.0	0.1
90°-120°	616.3	20.4
90°-150°	2224.1	73.8
90°-180°	3013.0	99.9
0°-180°	3015.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	0	0	0	0	0	
5°	0	0	0	0	0	0
15°	0	0	0	0	0	0
25°	0	0	0	0	0	0
35°	0	0	0	0	0	0
45°	0	0	0	0	0	0
55°	0	0	0	0	0	0
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	1	8	18	21	22	3
95°	45	15	23	28	28	54
105°	219	227	161	31	32	232
115°	410	415	422	429	432	405
125°	579	584	587	589	590	517
135°	720	725	728	730	728	555
145°	831	836	838	839	839	520
155°	916	914	915	919	914	422
165°	966	963	963	968	963	273
175°	988	985	985	990	985	94
180°	988	988	988	988	988	

TEST NUMBER: P1007606

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0
52.5°	0.0	0.0	0.0	0.0	0.0
55°	0.0	0.0	0.0	0.0	0.0
57.5°	0.0	0.0	0.0	0.0	0.0
60°	0.0	0.0	0.0	0.0	0.0
62.5°	0.0	0.0	0.0	0.0	0.0
65°	0.0	0.0	0.0	0.0	0.0
67.5°	0.0	0.0	0.0	0.0	0.0
70°	0.0	0.0	0.0	0.0	0.0
72.5°	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.7	8.1	17.6	20.6	22.0
92.5°	16.9	12.5	19.1	24.2	25.0
95°	44.8	14.7	22.8	27.9	27.9
97.5°	81.5	60.9	23.5	29.4	30.1
100°	124.1	138.8	24.2	30.1	30.8
102.5°	172.6	182.1	54.3	30.1	31.6
105°	218.8	226.9	160.8	30.8	32.3
107.5°	268.0	274.6	285.6	172.6	76.4
110°	317.2	323.1	331.2	306.9	201.9

TEST NUMBER: P1007606

CATALOG NUMBER: S123IP-B805UB2750-4F0-XX-W2A_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	364.2	369.3	377.4	384.0	382.6
115°	410.5	414.9	421.5	428.8	431.8
117.5°	456.0	461.1	464.8	470.7	471.4
120°	497.8	504.4	506.7	512.5	512.5
122.5°	540.4	545.6	548.5	552.2	552.9
125°	578.6	584.5	587.4	588.9	590.4
127.5°	616.8	622.7	626.3	628.5	627.1
130°	652.0	657.9	660.8	663.8	662.3
132.5°	685.8	691.7	693.9	696.8	694.6
135°	720.3	724.7	727.7	729.9	727.7
137.5°	749.7	755.6	757.0	760.7	759.2
140°	779.1	783.5	785.7	788.6	787.1
142.5°	806.2	810.6	812.8	815.0	812.8
145°	831.2	836.3	837.8	839.3	839.3
147.5°	855.4	859.1	860.6	862.0	858.4
150°	877.5	879.7	881.1	882.6	880.4
152.5°	897.3	898.0	898.8	901.7	898.0
155°	915.6	914.2	914.9	918.6	914.2
157.5°	930.3	930.3	929.6	934.0	928.1
160°	943.5	942.8	942.1	946.5	941.3
162.5°	956.0	953.8	953.1	958.2	953.8
165°	965.6	963.4	962.6	968.5	963.4
167.5°	973.7	970.7	970.7	976.6	970.7
170°	980.3	977.3	977.3	983.2	977.3
172.5°	984.7	981.0	981.7	987.6	981.0
175°	988.3	984.7	985.4	990.5	984.7
177.5°	989.8	986.1	986.9	992.7	985.4
180°	988.3	988.3	988.3	988.3	988.3

(END OF REPORT)