

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012464

Luminaire Tested: S123RDIP-B340D1195UB50-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012464
REPORT IS A COMBINATION OF REPORTS P993197 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB50-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5156.0 lumens
Efficiency: N/A
Efficacy: 107.4 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012464

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012464

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	32	32	32
1	92	88	84	81	82	78	75	73	60	58	56	44	42	41	28	28	27
2	84	77	71	66	74	69	64	60	53	50	47	38	36	35	25	24	23
3	77	68	61	55	68	60	55	50	47	43	40	34	32	29	22	21	20
4	70	60	52	47	62	53	47	42	42	37	34	30	28	25	20	18	17
5	64	53	45	40	57	48	41	36	37	32	29	27	24	22	18	16	15
6	59	48	40	34	52	43	36	31	33	29	25	25	21	19	16	15	13
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	12
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	14	12	11
9	47	35	28	23	42	32	26	21	25	20	17	19	16	13	13	11	9
10	44	32	25	21	39	29	23	19	23	19	15	17	14	12	12	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1012464

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	1.0
10°-20°	140.6	2.7
20°-30°	202.5	3.9
30°-40°	228.0	4.4
40°-50°	218.1	4.2
50°-60°	178.6	3.5
60°-70°	120.4	2.3
70°-80°	60.4	1.2
80°-90°	18.8	0.4
90°-100°	91.5	1.8
100°-110°	276.9	5.4
110°-120°	471.4	9.1
120°-130°	620.2	12.0
130°-140°	697.1	13.5
140°-150°	685.3	13.3
150°-160°	577.0	11.2
160°-170°	384.1	7.4
170°-180°	134.5	2.6
0°-30°	393.7	7.6
0°-40°	621.7	12.1
0°-60°	1018.4	19.8
0°-90°	1218.0	23.6
90°-120°	839.8	16.3
90°-150°	2842.4	55.1
90°-180°	3938.0	76.4
0°-180°	5156.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	1	12	27	31	34	6
95°	66	74	83	87	87	73
105°	251	253	264	264	266	269
115°	474	478	476	477	476	470
125°	694	698	696	691	687	619
135°	901	908	907	902	900	694
145°	1093	1095	1099	1098	1093	683
155°	1252	1252	1253	1257	1249	576
165°	1363	1360	1360	1366	1359	384
175°	1418	1413	1413	1420	1412	135
180°	1421	1421	1421	1421	1421	

TEST NUMBER: P1012464

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	1.1	12.3	26.8	31.3	33.5
92.5°	33.5	40.2	46.9	50.2	48.0
95°	65.9	73.7	82.6	87.1	87.1
97.5°	108.3	113.9	120.6	126.2	125.0
100°	151.8	158.5	164.1	167.5	169.7
102.5°	202.1	205.4	213.2	216.6	215.5
105°	251.2	253.4	263.5	263.5	265.7
107.5°	309.3	310.4	314.8	318.2	317.1
110°	362.8	365.1	367.3	371.8	369.5

TEST NUMBER: P1012464

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	418.7	419.8	419.8	425.4	425.4
115°	474.5	477.8	475.6	476.7	475.6
117.5°	531.4	532.5	530.3	530.3	527.0
120°	583.9	590.6	585.0	583.9	581.7
122.5°	638.6	643.1	640.8	637.5	634.1
125°	694.4	697.8	695.5	691.1	686.6
127.5°	745.8	752.5	750.3	743.6	739.1
130°	797.1	806.1	802.7	798.3	790.4
132.5°	848.5	857.4	855.2	849.6	844.0
135°	901.0	907.7	906.6	902.1	899.9
137.5°	949.0	954.6	957.9	952.3	949.0
140°	999.2	1004.8	1005.9	1004.8	997.0
142.5°	1045.0	1050.6	1052.8	1051.7	1046.1
145°	1093.0	1095.2	1098.6	1097.5	1093.0
147.5°	1134.3	1138.8	1142.1	1142.1	1135.4
150°	1177.9	1180.1	1182.3	1182.3	1175.6
152.5°	1213.6	1216.9	1218.0	1220.3	1214.7
155°	1251.5	1251.5	1252.7	1257.1	1249.3
157.5°	1283.9	1282.8	1283.9	1288.4	1281.7
160°	1314.1	1311.8	1311.8	1317.4	1312.9
162.5°	1340.9	1337.5	1338.6	1344.2	1336.4
165°	1363.2	1359.8	1359.8	1366.5	1358.7
167.5°	1382.2	1377.7	1378.8	1385.5	1378.8
170°	1397.8	1393.3	1393.3	1401.1	1393.3
172.5°	1410.1	1405.6	1405.6	1412.3	1404.5
175°	1417.9	1413.4	1413.4	1420.1	1412.3
177.5°	1422.4	1417.9	1417.9	1424.6	1416.8
180°	1421.2	1421.2	1421.2	1421.2	1421.2

(END OF REPORT)