

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012465

Luminaire Tested: S123RDIP-B340D1195UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012465
REPORT IS A COMBINATION OF REPORTS P993198 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D1195UB50-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5376.6 lumens
Efficiency: N/A
Efficacy: 112.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 48
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012465

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012465

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	26	26	26	19
2	84	77	71	66	74	68	63	59	52	49	46	38	36	34	24	23	22	22	22	16
3	76	67	61	55	67	60	54	50	46	42	39	34	31	29	22	20	19	19	19	14
4	70	60	52	47	62	53	47	42	41	37	33	30	27	25	19	18	17	17	17	12
5	64	53	45	40	57	47	41	36	37	32	29	27	24	22	18	16	15	15	15	11
6	59	47	40	34	52	42	36	31	33	28	25	24	21	19	16	14	13	13	13	9
7	54	43	35	30	48	38	32	27	30	25	22	22	19	17	15	13	11	11	11	8
8	50	39	31	26	45	35	28	24	27	23	19	20	17	15	13	12	10	10	10	8
9	47	35	28	23	41	32	25	21	25	20	17	18	15	13	12	11	9	9	9	7
10	43	32	25	21	39	29	23	19	23	18	15	17	14	12	11	10	8	8	8	6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5789	5789	5789
5°	5798	5584	5569
10°	5752	5374	5268
15°	5678	5114	4939
20°	5580	4832	4571
25°	5479	4539	4222
30°	5349	4227	3810
35°	5216	3921	3434
40°	5091	3588	3019
45°	4929	3262	2647
50°	4752	2915	2260
55°	4568	2543	1906
60°	4393	2162	1548
65°	4165	1770	1208
70°	3878	1338	864
75°	3469	906	684
80°	2959	630	480
85°	2219	340	250

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4929 cd/sqm

TEST NUMBER: P1012465

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.6	0.9
10°-20°	140.6	2.6
20°-30°	202.5	3.8
30°-40°	228.0	4.2
40°-50°	218.1	4.1
50°-60°	178.6	3.3
60°-70°	120.4	2.2
70°-80°	60.4	1.1
80°-90°	18.9	0.4
90°-100°	313.4	5.8
100°-110°	876.1	16.3
110°-120°	854.3	15.9
120°-130°	680.2	12.7
130°-140°	536.9	10.0
140°-150°	400.6	7.5
150°-160°	279.5	5.2
160°-170°	164.2	3.1
170°-180°	53.4	1.0
0°-30°	393.7	7.3
0°-40°	621.7	11.6
0°-60°	1018.4	18.9
0°-90°	1218.1	22.7
90°-120°	2043.8	38.0
90°-150°	3661.5	68.1
90°-180°	4159.0	77.4
0°-180°	5376.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	538	538	538	538	538	
5°	538	536	530	534	533	51
15°	513	508	496	494	491	145
25°	467	456	436	427	422	215
35°	404	388	361	342	334	253
45°	332	312	279	254	243	256
55°	252	231	194	168	160	226
65°	172	148	114	93	88	171
75°	91	70	46	42	41	97
85°	23	14	12	11	11	25
90°	2	13	28	31	32	4
95°	38	123	662	193	130	40
105°	130	192	898	1570	1420	138
115°	229	285	687	1506	1727	227
125°	318	376	641	1161	1362	283
135°	373	445	632	956	1104	288
145°	425	487	624	784	863	267
155°	484	521	604	687	716	222
165°	528	543	578	614	624	149
175°	550	551	555	563	562	52
180°	552	552	552	552	552	

TEST NUMBER: P1012465

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	537.8	537.8	537.8	537.8	537.8
2.5°	540.0	538.2	533.0	537.8	536.9
5°	537.8	535.6	530.4	534.3	533.4
7.5°	533.9	531.7	525.2	527.8	526.5
10°	528.6	525.6	517.7	518.2	516.0
12.5°	521.2	517.7	507.7	507.3	504.7
15°	512.9	508.1	495.9	493.8	490.7
17.5°	502.9	497.7	482.4	478.1	473.7
20°	491.6	484.6	468.0	462.3	457.1
22.5°	478.9	470.6	452.8	445.3	440.5
25°	466.7	455.8	435.7	426.6	421.8
27.5°	451.9	440.1	418.3	406.1	398.7
30°	436.6	423.5	399.1	384.3	377.3
32.5°	421.3	406.1	379.9	363.3	355.9
35°	403.9	388.2	361.2	342.4	334.5
37.5°	386.5	369.4	341.1	320.2	310.6
40°	369.9	350.7	319.7	297.0	287.0
42.5°	351.1	331.9	299.7	274.4	265.6
45°	331.9	312.3	278.7	253.9	243.4
47.5°	313.2	291.4	258.2	231.2	222.0
50°	292.2	271.7	236.4	209.4	199.3
52.5°	273.5	250.8	215.9	187.6	178.8
55°	252.1	230.7	193.7	168.4	159.6
57.5°	232.9	209.8	172.3	148.3	140.9
60°	212.9	188.9	152.7	129.1	121.7
62.5°	192.8	168.8	132.6	110.8	102.9
65°	172.3	148.3	114.3	92.9	88.1
67.5°	151.8	127.4	94.2	78.1	72.8
70°	131.7	108.2	77.6	62.4	57.6
72.5°	111.7	88.5	61.5	49.7	48.4
75°	91.2	70.2	46.2	41.9	41.0
77.5°	72.4	53.2	36.2	33.6	32.7
80°	54.5	36.6	27.5	26.2	25.3
82.5°	37.5	22.7	19.6	18.3	18.3
85°	23.1	13.5	12.2	11.3	11.3
87.5°	10.5	5.7	5.7	5.2	4.8
90°	2.2	13.4	27.9	31.2	32.4
92.5°	16.7	67.0	207.7	70.9	59.2
95°	38.0	123.4	662.1	193.2	129.5
97.5°	60.3	141.2	1018.3	485.6	265.7
100°	82.6	155.8	1057.4	1016.0	700.1
102.5°	106.1	172.5	984.8	1360.5	1108.7
105°	129.5	191.5	897.7	1569.8	1420.2
107.5°	154.1	213.8	820.7	1662.0	1623.4
110°	180.9	236.7	757.0	1664.8	1739.6

TEST NUMBER: P1012465

CATALOG NUMBER: S123RDIP-B340D1195UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	205.4	260.7	714.6	1601.6	1763.0
115°	228.9	285.2	686.7	1505.6	1727.3
117.5°	252.3	308.8	667.7	1402.9	1649.1
120°	276.9	332.2	655.4	1305.8	1546.4
122.5°	298.1	354.5	647.6	1229.3	1450.4
125°	318.2	375.7	640.9	1161.2	1362.2
127.5°	333.8	395.8	637.5	1105.4	1286.2
130°	348.4	413.6	634.2	1054.0	1223.7
132.5°	359.5	429.9	633.1	1006.0	1162.3
135°	372.9	445.0	632.0	956.3	1104.3
137.5°	385.2	457.2	629.7	909.4	1042.8
140°	397.5	468.4	628.6	863.6	978.1
142.5°	410.9	478.4	626.4	821.8	917.8
145°	425.4	487.4	624.1	784.4	863.1
147.5°	439.9	496.8	620.8	755.4	816.2
150°	454.4	504.6	616.3	729.6	776.0
152.5°	468.9	513.0	610.7	707.3	742.5
155°	483.5	521.4	604.0	686.7	715.7
157.5°	494.6	528.6	598.5	666.6	690.0
160°	508.0	534.8	591.8	648.2	665.5
162.5°	518.1	539.3	585.1	630.8	643.1
165°	528.1	543.2	578.4	613.5	624.1
167.5°	535.9	546.6	571.7	598.4	605.2
170°	542.6	548.2	565.0	585.0	588.4
172.5°	547.1	549.9	559.4	573.3	572.8
175°	550.5	551.0	554.9	562.7	561.6
177.5°	552.7	551.6	551.6	556.0	553.8
180°	551.6	551.6	551.6	551.6	551.6

(END OF REPORT)