

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012477

Luminaire Tested: S123RDIP-B340D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012477
REPORT IS A COMBINATION OF REPORTS P993220 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D365UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2588.1 lumens
Efficiency: N/A
Efficacy: 116.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012477

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012477

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6018	6018	6018
5°	6028	5804	5789
10°	5980	5586	5477
15°	5902	5316	5134
20°	5801	5023	4752
25°	5695	4719	4388
30°	5561	4394	3960
35°	5423	4075	3570
40°	5292	3729	3138
45°	5124	3391	2751
50°	4940	3029	2350
55°	4749	2643	1981
60°	4566	2247	1609
65°	4329	1840	1256
70°	4032	1391	897
75°	3606	943	711
80°	3078	656	499
85°	2305	354	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5124 cd/sqm

TEST NUMBER: P1012477

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.6	2.0
10°-20°	146.2	5.6
20°-30°	210.5	8.1
30°-40°	237.1	9.2
40°-50°	226.7	8.8
50°-60°	185.6	7.2
60°-70°	125.1	4.8
70°-80°	62.8	2.4
80°-90°	17.4	0.7
90°-100°	99.8	3.9
100°-110°	278.9	10.8
110°-120°	272.0	10.5
120°-130°	216.6	8.4
130°-140°	171.0	6.6
140°-150°	127.6	4.9
150°-160°	89.0	3.4
160°-170°	52.3	2.0
170°-180°	17.0	0.7
0°-30°	409.2	15.8
0°-40°	646.3	25.0
0°-60°	1058.7	40.9
0°-90°	1264.0	48.8
90°-120°	650.7	25.1
90°-150°	1165.8	45.0
90°-180°	1324.0	51.2
0°-180°	2588.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	559	559	559	559	559	
5°	559	557	551	555	554	53
15°	533	528	516	513	510	150
25°	485	474	453	443	438	223
35°	420	404	375	356	348	263
45°	345	325	290	264	253	266
55°	262	240	201	175	166	235
65°	179	154	119	97	92	177
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	4	9	10	10	2
95°	12	39	211	62	41	13
105°	41	61	286	500	452	44
115°	73	91	219	479	550	72
125°	101	120	204	370	434	90
135°	119	142	201	304	352	92
145°	135	155	199	250	275	85
155°	154	166	192	219	228	71
165°	168	173	184	195	199	47
175°	175	175	177	179	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1012477

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	559.1	559.1	559.1	559.1	559.1
2.5°	561.3	559.5	554.1	559.1	558.1
5°	559.1	556.8	551.3	555.4	554.5
7.5°	555.0	552.7	545.9	548.6	547.3
10°	549.5	546.4	538.2	538.6	536.4
12.5°	541.8	538.2	527.8	527.3	524.6
15°	533.2	528.2	515.5	513.3	510.1
17.5°	522.8	517.3	501.5	496.9	492.4
20°	511.0	503.7	486.5	480.6	475.2
22.5°	497.8	489.2	470.6	462.9	457.9
25°	485.1	473.8	453.0	443.4	438.4
27.5°	469.7	457.5	434.8	422.1	414.4
30°	453.9	440.3	414.9	399.5	392.2
32.5°	438.0	422.1	394.9	377.7	370.0
35°	419.9	403.5	375.4	355.9	347.8
37.5°	401.7	384.0	354.6	332.8	322.8
40°	384.5	364.5	332.3	308.8	298.3
42.5°	365.0	345.0	311.5	285.2	276.1
45°	345.0	324.6	289.7	263.9	253.0
47.5°	325.5	302.9	268.4	240.3	230.8
50°	303.8	282.5	245.7	217.6	207.2
52.5°	284.3	260.7	224.4	195.0	185.9
55°	262.1	239.9	201.3	175.0	165.9
57.5°	242.1	218.1	179.1	154.2	146.5
60°	221.3	196.3	158.7	134.2	126.5
62.5°	200.4	175.5	137.8	115.2	107.0
65°	179.1	154.2	118.8	96.6	91.6
67.5°	157.8	132.4	97.9	81.2	75.7
70°	136.9	112.4	80.7	64.8	59.8
72.5°	116.1	92.0	63.9	51.7	50.3
75°	94.8	73.0	48.1	43.5	42.6
77.5°	75.3	55.3	37.6	34.9	34.0
80°	56.7	38.1	28.6	27.2	26.3
82.5°	39.0	23.6	20.4	19.0	19.0
85°	24.0	14.1	12.7	11.8	11.8
87.5°	10.9	5.9	5.9	5.4	5.0
90°	0.7	4.2	8.9	10.0	10.3
92.5°	5.3	21.3	66.1	22.6	18.8
95°	12.1	39.3	210.8	61.5	41.2
97.5°	19.2	45.0	324.2	154.6	84.6
100°	26.3	49.6	336.7	323.6	222.9
102.5°	33.8	54.9	313.6	433.2	353.0
105°	41.2	61.0	285.8	499.8	452.2
107.5°	49.1	68.0	261.3	529.2	516.9
110°	57.6	75.4	241.0	530.0	553.9

TEST NUMBER: P1012477

CATALOG NUMBER: S123RDIP-B340D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.0	227.5	510.0	561.3
115°	72.9	90.8	218.6	479.4	550.0
117.5°	80.3	98.3	212.6	446.7	525.1
120°	88.2	105.8	208.7	415.8	492.4
122.5°	94.9	112.9	206.2	391.5	461.8
125°	101.3	119.6	204.1	369.7	433.7
127.5°	106.3	126.0	203.0	352.0	409.5
130°	110.9	131.7	201.9	335.6	389.6
132.5°	114.5	136.8	201.6	320.3	370.1
135°	118.7	141.7	201.2	304.5	351.6
137.5°	122.6	145.6	200.5	289.6	332.0
140°	126.6	149.1	200.1	275.0	311.4
142.5°	130.8	152.3	199.4	261.7	292.2
145°	135.4	155.2	198.7	249.8	274.8
147.5°	140.1	158.2	197.7	240.5	259.9
150°	144.7	160.7	196.2	232.3	247.1
152.5°	149.3	163.4	194.5	225.2	236.4
155°	153.9	166.0	192.3	218.6	227.9
157.5°	157.5	168.4	190.6	212.2	219.7
160°	161.8	170.3	188.4	206.4	211.9
162.5°	165.0	171.7	186.3	200.9	204.8
165°	168.2	173.0	184.2	195.4	198.7
167.5°	170.6	174.0	182.0	190.6	192.7
170°	172.8	174.6	179.9	186.2	187.4
172.5°	174.2	175.1	178.1	182.6	182.4
175°	175.3	175.4	176.7	179.2	178.8
177.5°	176.0	175.6	175.6	177.0	176.3
180°	175.6	175.6	175.6	175.6	175.6

(END OF REPORT)