

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012483

Luminaire Tested: S123RDIP-B340D365UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012483
REPORT IS A COMBINATION OF REPORTS P993226 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B340D365UB35-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2600.1 lumens
Efficiency: N/A
Efficacy: 116.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012483

CATALOG NUMBER: S123RDIP-B340D365UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012483

CATALOG NUMBER: S123RDIP-B340D365UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	86	83	80	73	71	69	61	59	58	49	48	47
2	89	82	76	71	82	76	71	66	64	61	57	54	51	49	44	42	40
3	82	72	65	60	75	67	61	56	57	52	48	48	44	41	39	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	35	32	30
5	69	57	49	44	63	53	46	41	46	40	36	38	34	31	32	29	26
6	63	52	44	38	58	48	41	36	41	36	32	35	31	27	29	26	23
7	59	47	39	33	54	43	36	32	37	32	28	32	27	24	26	23	21
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	22	19	17
10	47	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6046	6046	6046
5°	6056	5833	5817
10°	6008	5613	5502
15°	5930	5342	5158
20°	5828	5047	4774
25°	5723	4741	4409
30°	5587	4415	3979
35°	5449	4095	3587
40°	5316	3747	3154
45°	5149	3407	2764
50°	4963	3044	2361
55°	4771	2656	1991
60°	4587	2257	1616
65°	4349	1849	1261
70°	4052	1398	901
75°	3621	947	714
80°	3089	658	501
85°	2315	356	262

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 5149 cd/sqm

TEST NUMBER: P1012483

CATALOG NUMBER: S123RDIP-B340D365UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	2.0
10°-20°	146.9	5.6
20°-30°	211.5	8.1
30°-40°	238.2	9.2
40°-50°	227.8	8.8
50°-60°	186.5	7.2
60°-70°	125.7	4.8
70°-80°	63.1	2.4
80°-90°	17.5	0.7
90°-100°	100.2	3.9
100°-110°	280.2	10.8
110°-120°	273.2	10.5
120°-130°	217.6	8.4
130°-140°	171.7	6.6
140°-150°	128.1	4.9
150°-160°	89.4	3.4
160°-170°	52.5	2.0
170°-180°	17.1	0.7
0°-30°	411.2	15.8
0°-40°	649.4	25.0
0°-60°	1063.7	40.9
0°-90°	1269.9	48.8
90°-120°	653.7	25.1
90°-150°	1171.1	45.0
90°-180°	1330.0	51.2
0°-180°	2600.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	562	562	562	562	562	
5°	562	559	554	558	557	53
15°	536	531	518	516	512	151
25°	488	476	455	446	440	224
35°	422	406	377	358	349	264
45°	347	326	291	265	254	268
55°	263	241	202	176	167	236
65°	180	155	119	97	92	178
75°	95	73	48	44	43	101
85°	24	14	13	12	12	26
90°	1	4	9	10	10	2
95°	12	39	212	62	41	13
105°	41	61	287	502	454	44
115°	73	91	220	482	552	72
125°	102	120	205	371	436	90
135°	119	142	202	306	353	92
145°	136	156	200	251	276	85
155°	155	167	193	220	229	71
165°	169	174	185	196	200	48
175°	176	176	178	180	180	17
180°	176	176	176	176	176	

TEST NUMBER: P1012483

CATALOG NUMBER: S123RDIP-B340D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	561.7	561.7	561.7	561.7	561.7
2.5°	564.0	562.2	556.7	561.7	560.8
5°	561.7	559.4	554.0	558.1	557.2
7.5°	557.6	555.3	548.5	551.2	549.9
10°	552.1	549.0	540.8	541.2	538.9
12.5°	544.4	540.8	530.3	529.8	527.1
15°	535.7	530.7	518.0	515.7	512.5
17.5°	525.3	519.8	503.9	499.3	494.7
20°	513.4	506.1	488.8	482.9	477.4
22.5°	500.2	491.6	472.9	465.1	460.1
25°	487.5	476.1	455.1	445.5	440.5
27.5°	472.0	459.7	436.9	424.1	416.4
30°	456.0	442.4	416.8	401.4	394.1
32.5°	440.1	424.1	396.8	379.5	371.7
35°	421.9	405.5	377.2	357.6	349.4
37.5°	403.6	385.9	356.3	334.4	324.4
40°	386.3	366.3	333.9	310.2	299.8
42.5°	366.7	346.7	313.0	286.5	277.4
45°	346.7	326.2	291.1	265.1	254.2
47.5°	327.1	304.3	269.7	241.4	231.9
50°	305.2	283.8	246.9	218.7	208.2
52.5°	285.6	261.9	225.5	195.9	186.8
55°	263.3	241.0	202.3	175.8	166.7
57.5°	243.3	219.1	179.9	154.9	147.1
60°	222.3	197.3	159.4	134.8	127.1
62.5°	201.4	176.3	138.5	115.7	107.5
65°	179.9	154.9	119.4	97.0	92.0
67.5°	158.5	133.0	98.4	81.5	76.1
70°	137.6	113.0	81.1	65.1	60.1
72.5°	116.6	92.5	64.2	51.9	50.6
75°	95.2	73.3	48.3	43.7	42.8
77.5°	75.6	55.6	37.8	35.1	34.2
80°	56.9	38.3	28.7	27.3	26.4
82.5°	39.2	23.7	20.5	19.1	19.1
85°	24.1	14.1	12.8	11.8	11.8
87.5°	10.9	5.9	5.9	5.5	5.0
90°	0.7	4.2	8.9	10.0	10.4
92.5°	5.4	21.4	66.4	22.6	18.9
95°	12.1	39.4	211.8	61.8	41.4
97.5°	19.3	45.2	325.7	155.4	85.0
100°	26.4	49.8	338.2	325.0	223.9
102.5°	33.9	55.2	315.0	435.2	354.6
105°	41.4	61.2	287.1	502.2	454.3
107.5°	49.3	68.4	262.5	531.6	519.3
110°	57.9	75.7	242.1	532.5	556.4

TEST NUMBER: P1012483

CATALOG NUMBER: S123RDIP-B340D365UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.7	83.4	228.6	512.2	563.9
115°	73.2	91.2	219.6	481.6	552.5
117.5°	80.7	98.8	213.6	448.7	527.5
120°	88.6	106.2	209.6	417.6	494.6
122.5°	95.4	113.4	207.1	393.2	463.9
125°	101.8	120.2	205.0	371.4	435.7
127.5°	106.8	126.6	203.9	353.6	411.4
130°	111.4	132.3	202.8	337.2	391.4
132.5°	115.0	137.4	202.5	321.8	371.8
135°	119.3	142.3	202.1	305.8	353.2
137.5°	123.2	146.2	201.4	290.9	333.5
140°	127.1	149.8	201.1	276.2	312.8
142.5°	131.4	153.0	200.3	262.8	293.6
145°	136.1	155.9	199.6	250.9	276.1
147.5°	140.7	158.9	198.6	241.6	261.1
150°	145.3	161.4	197.1	233.4	248.2
152.5°	150.0	164.1	195.3	226.2	237.5
155°	154.6	166.8	193.2	219.6	228.9
157.5°	158.2	169.1	191.4	213.2	220.7
160°	162.5	171.0	189.3	207.4	212.8
162.5°	165.7	172.5	187.1	201.8	205.7
165°	168.9	173.8	185.0	196.2	199.6
167.5°	171.4	174.8	182.8	191.4	193.6
170°	173.6	175.4	180.7	187.2	188.2
172.5°	175.0	175.9	178.9	183.4	183.2
175°	176.1	176.2	177.5	180.0	179.6
177.5°	176.8	176.4	176.4	177.8	177.1
180°	176.4	176.4	176.4	176.4	176.4

(END OF REPORT)