

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012914

Luminaire Tested: S124DIP-B1020D810UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012914
REPORT IS A COMBINATION OF REPORTS P995381 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1020D810UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7520.0 lumens
Efficiency: N/A
Efficacy: 110.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 67.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012914

CATALOG NUMBER: S124DIP-B1020D810UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1012914

CATALOG NUMBER: S124DIP-B1020D810UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	109	109	109	109	102	102	102	102	88	88	88	75	75	75	64	64	64
1	100	95	91	88	93	89	85	82	77	75	72	66	64	63	56	55	54
2	91	83	77	72	84	78	72	68	68	63	60	58	55	52	49	47	45
3	83	73	66	60	77	68	62	56	60	54	50	51	48	44	44	41	38
4	76	65	57	51	70	61	53	48	53	47	43	46	41	38	39	36	33
5	70	58	49	43	65	54	47	41	47	42	37	41	37	33	35	32	29
6	64	52	44	38	60	49	41	36	43	37	32	37	33	29	32	28	25
7	59	47	39	33	55	44	37	32	39	33	29	34	29	26	29	26	23
8	55	43	35	29	51	40	33	28	35	30	25	31	26	23	27	23	20
9	51	39	31	26	48	37	30	25	33	27	23	29	24	21	25	21	18
10	48	36	28	24	45	34	27	23	30	24	21	26	22	19	23	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13906	13906	13906
5°	13917	13506	13522
10°	13800	13130	13039
15°	13602	12685	12494
20°	13349	12203	11929
25°	13064	11693	11321
30°	12721	11142	10654
35°	12365	10579	10010
40°	11995	9972	9324
45°	11608	9363	8683
50°	11177	8773	7973
55°	10710	8084	7267
60°	10231	7329	6533
65°	9684	6550	5705
70°	9053	5611	4818
75°	8112	4522	3859
80°	6914	3269	2714
85°	5370	1822	1461

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11608 cd/sqm

TEST NUMBER: P1012914

CATALOG NUMBER: S124DIP-B1020D810UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	160.7	2.1
10°-20°	452.8	6.0
20°-30°	666.4	8.9
30°-40°	774.7	10.3
40°-50°	774.6	10.3
50°-60°	677.5	9.0
60°-70°	503.0	6.7
70°-80°	285.4	3.8
80°-90°	83.8	1.1
90°-100°	33.7	0.4
100°-110°	221.9	3.0
110°-120°	423.7	5.6
120°-130°	537.9	7.2
130°-140°	575.4	7.7
140°-150°	538.1	7.2
150°-160°	433.9	5.8
160°-170°	279.8	3.7
170°-180°	96.4	1.3
0°-30°	1280.0	17.0
0°-40°	2054.7	27.3
0°-60°	3506.8	46.6
0°-90°	4379.1	58.2
90°-120°	679.3	9.0
90°-150°	2330.7	31.0
90°-180°	3141.0	41.8
0°-180°	7520.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1705	1705	1705	1705	1705	
5°	1704	1698	1683	1698	1696	162
15°	1622	1616	1596	1604	1600	457
25°	1469	1459	1440	1442	1436	676
35°	1264	1254	1235	1226	1219	790
45°	1032	1022	1000	985	981	795
55°	780	776	757	741	732	699
65°	529	522	508	495	488	523
75°	282	275	268	262	261	299
85°	74	74	71	71	70	79
90°	2	11	17	21	23	7
95°	42	16	17	21	22	51
105°	228	233	237	244	216	239
115°	427	429	428	430	430	420
125°	600	603	601	604	604	536
135°	744	743	746	748	749	573
145°	858	860	860	861	862	536
155°	941	941	939	942	940	434
165°	992	988	988	994	988	280
175°	1015	1010	1011	1018	1009	97
180°	1015	1015	1015	1015	1015	

TEST NUMBER: P1012914

CATALOG NUMBER: S124DIP-B1020D810UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1705.3	1705.3	1705.3	1705.3	1705.3
2.5°	1710.8	1706.7	1691.6	1705.3	1703.9
5°	1703.9	1698.5	1683.4	1698.5	1695.7
7.5°	1691.6	1686.2	1669.8	1682.1	1680.7
10°	1673.9	1668.4	1650.6	1661.6	1658.8
12.5°	1650.6	1645.2	1626.1	1638.4	1634.3
15°	1622.0	1616.5	1596.0	1604.2	1600.1
17.5°	1589.2	1582.3	1563.2	1568.7	1565.9
20°	1552.3	1545.4	1524.9	1529.0	1526.3
22.5°	1512.6	1503.1	1482.6	1490.8	1485.3
25°	1468.9	1459.3	1440.2	1441.6	1436.1
27.5°	1419.7	1410.2	1392.4	1389.7	1382.8
30°	1370.5	1359.6	1341.8	1336.4	1329.5
32.5°	1318.6	1309.0	1289.9	1283.1	1276.2
35°	1263.9	1254.4	1235.3	1225.7	1218.9
37.5°	1206.6	1198.4	1177.9	1168.3	1158.7
40°	1150.5	1139.6	1119.1	1105.4	1098.6
42.5°	1090.4	1084.9	1061.7	1045.3	1041.2
45°	1031.7	1022.1	1000.2	985.2	981.1
47.5°	970.2	963.3	942.8	926.4	915.5
50°	907.3	901.8	882.7	863.6	855.4
52.5°	845.8	839.0	818.5	802.1	791.2
55°	780.2	776.1	757.0	740.6	732.4
57.5°	718.7	714.6	695.5	679.1	670.9
60°	654.5	647.7	629.9	617.6	610.8
62.5°	591.7	586.2	567.1	556.1	549.3
65°	528.8	522.0	508.3	494.6	487.8
67.5°	464.6	459.1	445.5	431.8	430.4
70°	405.8	396.3	385.3	374.4	370.3
72.5°	343.0	333.4	325.2	317.0	312.9
75°	281.5	274.7	267.8	262.4	261.0
77.5°	221.4	218.6	211.8	210.4	206.3
80°	168.1	164.0	161.2	158.5	157.1
82.5°	116.1	114.8	114.8	113.4	112.0
85°	73.8	73.8	71.1	71.1	69.7
87.5°	35.5	34.2	32.8	32.8	32.8
90°	2.3	10.6	16.7	21.3	22.8
92.5°	11.4	9.9	15.9	20.5	20.5
95°	41.8	15.9	16.7	21.3	22.0
97.5°	79.7	96.4	16.7	20.5	21.3
100°	124.5	138.2	33.4	20.5	21.3
102.5°	174.6	183.7	192.8	22.0	22.0
105°	228.5	233.1	236.9	243.7	216.4
107.5°	277.9	280.1	285.5	289.3	292.3
110°	328.0	330.2	334.8	336.3	338.6



TEST NUMBER: P1012914

CATALOG NUMBER: S124DIP-B1020D810UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	376.6	381.1	382.6	381.9	384.9
115°	426.7	428.9	428.2	429.7	429.7
117.5°	471.5	474.5	476.8	476.0	476.0
120°	517.0	520.0	519.3	520.8	519.3
122.5°	559.5	561.0	562.6	563.3	561.8
125°	599.8	602.8	601.3	603.6	604.3
127.5°	638.5	639.2	643.0	642.3	641.5
130°	675.7	676.4	678.7	679.5	679.5
132.5°	709.8	711.4	714.4	715.2	714.4
135°	744.0	743.3	746.3	747.8	749.3
137.5°	774.4	774.4	778.2	779.7	778.9
140°	804.0	805.5	807.0	809.3	810.1
142.5°	830.6	833.6	834.4	835.9	835.9
145°	857.9	860.2	860.2	860.9	862.4
147.5°	879.1	883.7	882.9	883.7	884.5
150°	902.7	905.7	905.0	905.0	905.7
152.5°	922.4	924.7	923.2	924.7	923.9
155°	940.6	941.4	939.1	942.2	939.9
157.5°	956.6	956.6	953.5	957.3	953.5
160°	970.3	968.0	967.2	971.8	967.2
162.5°	982.4	979.4	978.6	983.2	977.8
165°	992.3	988.5	988.5	994.5	987.7
167.5°	1000.6	996.8	996.1	1002.9	995.3
170°	1007.5	1002.9	1003.7	1009.7	1002.1
172.5°	1012.0	1007.5	1008.2	1014.3	1005.9
175°	1015.0	1010.5	1011.2	1018.1	1009.0
177.5°	1017.3	1012.0	1013.5	1019.6	1010.5
180°	1015.0	1015.0	1015.0	1015.0	1015.0

(END OF REPORT)