

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012944

Luminaire Tested: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012944
REPORT IS A COMBINATION OF REPORTS P995501 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9877.0 lumens
Efficiency: N/A
Efficacy: 102.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012944

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1012944

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	99	99	99	99	84	84	84	70	70	70	58	58	58
1	98	94	90	86	91	87	83	80	74	71	69	62	60	59	51	50	49
2	89	82	76	70	82	76	71	66	65	61	57	54	51	49	45	43	41
3	81	72	65	59	75	67	60	55	57	52	48	48	44	41	40	37	35
4	75	64	56	50	69	59	52	47	51	45	41	43	39	35	35	32	30
5	68	57	49	43	63	53	46	40	45	40	35	38	34	31	32	29	26
6	63	51	43	37	58	47	40	35	41	35	31	35	30	27	29	26	23
7	58	46	38	32	54	43	36	31	37	31	27	32	27	24	26	23	20
8	54	42	34	29	50	39	32	27	34	28	24	29	24	21	24	21	18
9	50	38	31	26	47	36	29	24	31	26	22	27	22	19	22	19	17
10	47	35	28	23	44	33	26	22	29	23	20	25	20	17	21	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16193	16193	16193
5°	16206	15728	15747
10°	16069	15291	15184
15°	15839	14772	14549
20°	15545	14210	13892
25°	15213	13617	13184
30°	14814	12976	12407
35°	14400	12318	11656
40°	13969	11612	10857
45°	13517	10904	10111
50°	13016	10216	9284
55°	12472	9414	8463
60°	11915	8534	7608
65°	11277	7627	6644
70°	10544	6534	5610
75°	9446	5267	4493
80°	8049	3809	3161
85°	6251	2119	1702

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13517 cd/sqm

TEST NUMBER: P1012944

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.2	1.9
10°-20°	527.3	5.3
20°-30°	776.1	7.9
30°-40°	902.1	9.1
40°-50°	902.1	9.1
50°-60°	789.0	8.0
60°-70°	585.7	5.9
70°-80°	332.3	3.4
80°-90°	98.4	1.0
90°-100°	51.2	0.5
100°-110°	337.5	3.4
110°-120°	644.4	6.5
120°-130°	818.1	8.3
130°-140°	875.1	8.9
140°-150°	818.3	8.3
150°-160°	659.9	6.7
160°-170°	425.6	4.3
170°-180°	146.7	1.5
0°-30°	1490.6	15.1
0°-40°	2392.7	24.2
0°-60°	4083.7	41.3
0°-90°	5100.2	51.6
90°-120°	1033.1	10.5
90°-150°	3544.6	35.9
90°-180°	4777.0	48.4
0°-180°	9877.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1986	1986	1986	1986	1986	
5°	1984	1978	1960	1978	1975	188
15°	1889	1882	1858	1868	1863	532
25°	1710	1699	1677	1679	1672	787
35°	1472	1461	1438	1427	1419	920
45°	1201	1190	1165	1147	1142	926
55°	909	904	882	862	853	814
65°	616	608	592	576	568	609
75°	328	320	312	306	304	348
85°	86	86	83	83	81	92
90°	4	16	25	32	35	9
95°	64	24	25	32	34	78
105°	348	354	360	371	329	364
115°	649	652	651	654	654	639
125°	912	917	914	918	919	815
135°	1132	1130	1135	1137	1140	872
145°	1305	1308	1308	1309	1312	815
155°	1431	1432	1428	1433	1429	660
165°	1509	1503	1503	1512	1502	426
175°	1544	1537	1538	1548	1534	147
180°	1544	1544	1544	1544	1544	

TEST NUMBER: P1012944

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1985.8	1985.8	1985.8	1985.8	1985.8
2.5°	1992.2	1987.4	1969.9	1985.8	1984.2
5°	1984.2	1977.9	1960.4	1977.9	1974.7
7.5°	1969.9	1963.5	1944.5	1958.8	1957.2
10°	1949.2	1942.9	1922.2	1934.9	1931.7
12.5°	1922.2	1915.8	1893.5	1907.9	1903.1
15°	1888.8	1882.4	1858.5	1868.1	1863.3
17.5°	1850.6	1842.6	1820.3	1826.7	1823.5
20°	1807.6	1799.7	1775.8	1780.6	1777.4
22.5°	1761.5	1750.3	1726.5	1736.0	1729.6
25°	1710.5	1699.4	1677.1	1678.7	1672.4
27.5°	1653.3	1642.1	1621.4	1618.3	1610.3
30°	1596.0	1583.2	1562.6	1556.2	1548.2
32.5°	1535.5	1524.4	1502.1	1494.1	1486.2
35°	1471.9	1460.7	1438.4	1427.3	1419.4
37.5°	1405.0	1395.5	1371.6	1360.5	1349.3
40°	1339.8	1327.1	1303.2	1287.3	1279.3
42.5°	1269.8	1263.4	1236.4	1217.3	1212.5
45°	1201.4	1190.2	1164.8	1147.3	1142.5
47.5°	1129.8	1121.8	1097.9	1078.8	1066.1
50°	1056.6	1050.2	1027.9	1005.6	996.1
52.5°	985.0	977.0	953.1	934.0	921.3
55°	908.6	903.8	881.5	862.4	852.9
57.5°	837.0	832.2	809.9	790.8	781.3
60°	762.2	754.2	733.5	719.2	711.3
62.5°	689.0	682.6	660.3	647.6	639.7
65°	615.8	607.8	591.9	576.0	568.1
67.5°	541.0	534.6	518.7	502.8	501.2
70°	472.6	461.4	448.7	436.0	431.2
72.5°	399.4	388.3	378.7	369.2	364.4
75°	327.8	319.8	311.9	305.5	303.9
77.5°	257.8	254.6	246.6	245.0	240.3
80°	195.7	190.9	187.8	184.6	183.0
82.5°	135.3	133.7	133.7	132.1	130.5
85°	85.9	85.9	82.7	82.7	81.2
87.5°	41.4	39.8	38.2	38.2	38.2
90°	3.5	16.2	25.4	32.3	34.6
92.5°	17.3	15.0	24.2	31.2	31.2
95°	63.5	24.2	25.4	32.3	33.5
97.5°	121.2	146.6	25.4	31.2	32.3
100°	189.4	210.1	50.8	31.2	32.3
102.5°	265.6	279.4	293.3	33.5	33.5
105°	347.5	354.5	360.2	370.6	329.1
107.5°	422.6	426.1	434.1	439.9	444.5
110°	498.8	502.3	509.2	511.5	515.0



TEST NUMBER: P1012944

CATALOG NUMBER: S124DIP-B1195D1205UB2750-4F0-XX-W2A-F_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.7	579.6	581.9	580.8	585.4
115°	648.9	652.4	651.2	653.5	653.5
117.5°	717.0	721.6	725.1	723.9	723.9
120°	786.3	790.9	789.8	792.1	789.8
122.5°	851.0	853.3	855.6	856.7	854.4
125°	912.1	916.8	914.5	917.9	919.1
127.5°	971.0	972.2	978.0	976.8	975.6
130°	1027.6	1028.8	1032.2	1033.4	1033.4
132.5°	1079.6	1081.9	1086.5	1087.6	1086.5
135°	1131.5	1130.4	1135.0	1137.3	1139.6
137.5°	1177.7	1177.7	1183.5	1185.8	1184.6
140°	1222.7	1225.0	1227.4	1230.8	1232.0
142.5°	1263.1	1267.8	1268.9	1271.2	1271.2
145°	1304.7	1308.2	1308.2	1309.3	1311.6
147.5°	1337.0	1344.0	1342.8	1344.0	1345.1
150°	1372.8	1377.5	1376.3	1376.3	1377.5
152.5°	1402.9	1406.3	1404.0	1406.3	1405.2
155°	1430.6	1431.7	1428.3	1432.9	1429.4
157.5°	1454.8	1454.8	1450.2	1456.0	1450.2
160°	1475.6	1472.1	1471.0	1477.9	1471.0
162.5°	1494.1	1489.5	1488.3	1495.2	1487.1
165°	1509.1	1503.3	1503.3	1512.5	1502.2
167.5°	1521.8	1516.0	1514.9	1525.2	1513.7
170°	1532.2	1525.2	1526.4	1535.6	1524.1
172.5°	1539.1	1532.2	1533.3	1542.6	1529.9
175°	1543.7	1536.8	1537.9	1548.3	1534.5
177.5°	1547.2	1539.1	1541.4	1550.6	1536.8
180°	1543.7	1543.7	1543.7	1543.7	1543.7

(END OF REPORT)