

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012948

Luminaire Tested: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012948
REPORT IS A COMBINATION OF REPORTS P995550 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6831.0 lumens
Efficiency: N/A
Efficacy: 96.8 lumens/watt
Spacing Criteria (0/90/45): 1.22 / 1.3 / 1.41
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 70.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	114	114	114	114	109	109	109	109	99	99	99	90	90	90	82	82	82	78		
1	104	100	96	93	100	96	92	89	88	85	82	80	78	76	73	72	70	67		
2	95	88	82	76	91	84	79	74	77	73	69	71	67	64	65	62	60	56		
3	87	78	70	64	83	74	68	62	69	63	58	63	58	55	58	54	51	48		
4	80	69	61	55	76	66	59	53	61	55	50	56	51	47	52	48	44	42		
5	74	62	54	47	70	60	52	46	55	49	44	51	46	41	47	43	39	36		
6	68	56	47	41	65	54	46	40	50	43	38	46	41	36	43	38	35	32		
7	63	51	42	37	60	49	41	36	45	39	34	42	37	32	39	34	31	29		
8	59	46	38	33	56	45	37	32	42	35	31	39	33	29	36	31	28	26		
9	55	42	35	29	53	41	34	29	38	32	28	36	30	26	33	29	25	23		
10	52	39	32	27	49	38	31	26	35	29	25	33	28	24	31	26	23	21		

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	15819	15819	15819	15819
5°	15779	18148	15871	13637
10°	15661	21173	15781	11963
15°	15473	24408	15580	10704
20°	15273	26467	15383	9597
25°	14980	26165	15123	8781
30°	14694	21626	14873	8359
35°	14293	16116	14450	8104
40°	13824	12140	13959	7979
45°	13110	9743	13273	7809
50°	12256	8208	12434	7729
55°	11252	7144	11428	7639
60°	10275	6291	10577	7511
65°	9360	5414	9448	7199
70°	8284	4453	8462	6629
75°	7225	3421	7179	5632
80°	5684	2249	5618	4275
85°	3740	1010	3507	2492

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 145°

Vertical Angle: 45°

Luminance: 20455 cd/sqm

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	188.8	2.8
10°-20°	582.7	8.5
20°-30°	925.8	13.6
30°-40°	1028.7	15.1
40°-50°	935.5	13.7
50°-60°	764.5	11.2
60°-70°	545.7	8.0
70°-80°	300.3	4.4
80°-90°	82.1	1.2
90°-100°	15.8	0.2
100°-110°	104.3	1.5
110°-120°	199.2	2.9
120°-130°	252.9	3.7
130°-140°	270.6	4.0
140°-150°	253.0	3.7
150°-160°	204.0	3.0
160°-170°	131.6	1.9
170°-180°	45.4	0.7
0°-30°	1697.3	24.8
0°-40°	2726.0	39.9
0°-60°	4425.9	64.8
0°-90°	5354.0	78.4
90°-120°	319.4	4.7
90°-150°	1096.0	16.0
90°-180°	1477.0	21.6
0°-180°	6831.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1940	1940	1940	1940	1940	
5°	1932	2276	1943	1710	1932	183
15°	1845	3126	1858	1371	1845	521
25°	1684	3319	1700	1114	1684	776
35°	1461	1962	1477	987	1461	913
45°	1165	1101	1180	882	1165	899
55°	820	720	832	770	820	737
65°	511	463	516	616	511	505
75°	251	231	249	381	251	263
85°	51	48	48	119	51	60
90°	1	11	1	11	1	4
95°	20	10	20	10	20	24
105°	108	102	108	102	108	112
115°	201	202	201	202	201	197
125°	282	284	282	284	282	252
135°	350	352	350	352	350	270
145°	403	406	403	406	403	252
155°	442	442	442	442	442	204
165°	467	464	467	464	467	132
175°	477	474	477	474	477	45
180°	477	477	477	477	477	

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	1939.9	1959.2	1967.2	1973.6	1994.5	2001.0	2002.6	2012.2	2020.3	2021.9	2021.9
5°	1931.9	1962.4	1986.5	2009.0	2042.8	2057.2	2074.9	2094.2	2119.9	2136.0	2144.0
7.5°	1919.0	1964.0	2001.0	2039.5	2086.2	2115.1	2131.2	2182.6	2217.9	2246.9	2282.2
10°	1899.7	1957.6	2010.6	2066.9	2132.8	2168.1	2203.5	2266.2	2316.0	2372.2	2417.2
12.5°	1870.8	1946.3	2010.6	2089.4	2171.3	2213.1	2254.9	2364.2	2422.1	2471.9	2552.2
15°	1845.1	1920.6	2012.2	2092.6	2193.8	2256.5	2317.6	2388.3	2479.9	2587.6	2664.7
17.5°	1816.1	1911.0	1996.1	2108.7	2221.2	2280.6	2330.4	2439.7	2568.3	2674.4	2745.1
20°	1776.0	1872.4	1984.9	2103.8	2237.2	2283.8	2349.7	2496.0	2611.7	2716.2	2831.9
22.5°	1729.4	1841.9	1960.8	2074.9	2213.1	2311.2	2383.5	2512.1	2651.9	2772.4	2902.6
25°	1684.3	1806.5	1911.0	2066.9	2213.1	2279.0	2361.0	2513.7	2666.4	2812.6	2946.0
27.5°	1636.1	1750.2	1891.7	2015.4	2181.0	2253.3	2341.7	2508.8	2671.2	2817.4	2960.5
30°	1583.1	1705.2	1822.6	1968.8	2129.5	2222.8	2304.7	2486.3	2651.9	2804.6	2938.0
32.5°	1523.6	1639.3	1764.7	1902.9	2071.7	2166.5	2269.4	2455.8	2632.6	2764.4	2867.3
35°	1460.9	1578.3	1687.6	1829.0	2002.6	2097.4	2197.0	2402.8	2578.0	2685.6	2745.1
37.5°	1391.8	1502.7	1610.4	1750.2	1923.8	2025.1	2126.3	2325.6	2491.2	2581.2	2565.1
40°	1325.9	1425.6	1525.2	1657.0	1838.6	1946.3	2034.7	2235.6	2380.3	2418.8	2365.8
42.5°	1250.4	1335.6	1432.0	1567.0	1743.8	1845.1	1956.0	2139.2	2246.9	2230.8	2140.8
45°	1165.2	1240.8	1337.2	1464.2	1644.2	1748.6	1841.9	2015.4	2094.2	2054.0	1890.1
47.5°	1083.3	1157.2	1235.9	1362.9	1538.1	1626.5	1721.3	1877.2	1922.2	1837.0	1673.1
50°	994.9	1055.9	1137.9	1258.4	1422.4	1515.6	1594.3	1719.7	1735.8	1631.3	1460.9
52.5°	909.7	961.1	1039.9	1158.8	1311.5	1385.4	1462.6	1573.5	1560.6	1452.9	1289.0
55°	819.7	867.9	940.2	1049.5	1184.5	1255.2	1321.1	1419.2	1391.8	1280.9	1137.9
57.5°	744.1	777.9	848.6	949.9	1060.8	1137.9	1194.2	1271.3	1229.5	1118.6	985.2
60°	657.3	699.1	758.6	840.6	949.9	1001.3	1051.1	1102.5	1073.6	967.5	848.6
62.5°	578.6	610.7	662.2	740.9	826.1	872.7	925.7	957.9	929.0	830.9	731.3
65°	511.1	536.8	577.0	641.3	723.2	761.8	792.4	822.9	798.8	707.2	634.8
67.5°	437.2	459.7	493.4	544.8	614.0	641.3	670.2	691.1	663.8	602.7	532.0
70°	371.3	387.3	419.5	458.1	506.3	532.0	556.1	577.0	552.9	501.4	448.4
72.5°	303.8	316.6	345.5	372.9	416.3	433.9	451.6	467.7	459.7	411.4	368.0
75°	250.7	255.5	274.8	297.3	324.7	343.9	356.8	366.4	360.0	321.4	294.1
77.5°	189.7	196.1	210.5	228.2	252.3	263.6	271.6	281.3	273.2	242.7	223.4
80°	138.2	139.8	147.9	163.9	180.0	181.6	189.7	202.5	197.7	176.8	162.3
82.5°	88.4	93.2	96.4	106.1	117.3	120.5	125.4	128.6	127.0	114.1	109.3
85°	51.4	51.4	54.6	61.1	64.3	69.1	70.7	72.3	75.5	67.5	62.7
87.5°	22.5	24.1	24.1	25.7	28.9	28.9	30.5	32.1	33.8	32.1	27.3
90°	1.1	2.0	2.8	3.7	4.6	5.0	5.3	6.0	6.6	7.3	7.9
92.5°	5.4	5.2	5.0	4.9	4.7	4.6	4.9	5.6	6.2	6.9	7.5
95°	19.6	16.9	14.2	11.5	8.8	7.5	7.5	7.6	7.7	7.8	7.9
97.5°	37.5	39.2	41.0	42.7	44.4	45.3	41.1	32.8	24.5	16.2	7.9
100°	58.6	60.0	61.4	62.9	64.3	65.0	59.5	48.6	37.6	26.7	15.7
102.5°	82.1	83.1	84.0	85.0	85.9	86.4	86.9	87.8	88.8	89.7	90.7
105°	107.5	108.0	108.4	108.9	109.4	109.6	109.8	110.2	110.6	111.0	111.4
107.5°	130.7	130.9	131.1	131.4	131.6	131.7	132.0	132.5	133.1	133.6	134.2
110°	154.2	154.4	154.7	154.9	155.2	155.3	155.5	156.0	156.5	156.9	157.4

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
112.5°	177.1	177.6	178.0	178.5	179.0	179.2	179.3	179.4	179.6	179.7	179.9
115°	200.6	200.8	201.1	201.3	201.6	201.7	201.7	201.6	201.5	201.5	201.4
117.5°	221.7	222.0	222.3	222.6	222.9	223.1	223.2	223.5	223.7	224.0	224.2
120°	243.1	243.4	243.8	244.1	244.4	244.6	244.6	244.5	244.4	244.3	244.2
122.5°	263.1	263.3	263.4	263.6	263.7	263.8	263.9	264.0	264.2	264.3	264.5
125°	282.0	282.3	282.7	283.0	283.3	283.5	283.4	283.3	283.1	283.0	282.8
127.5°	300.2	300.3	300.4	300.5	300.6	300.6	300.8	301.2	301.6	302.0	302.4
130°	317.7	317.8	317.9	318.0	318.1	318.1	318.2	318.5	318.7	319.0	319.2
132.5°	333.8	334.0	334.1	334.3	334.4	334.5	334.7	335.0	335.3	335.6	335.9
135°	349.9	349.8	349.7	349.6	349.5	349.5	349.7	350.0	350.3	350.6	350.9
137.5°	364.2	364.2	364.2	364.2	364.2	364.2	364.4	364.8	365.1	365.5	365.9
140°	378.1	378.3	378.4	378.6	378.7	378.8	378.9	379.0	379.2	379.3	379.5
142.5°	390.6	390.9	391.2	391.5	391.8	392.0	392.0	392.1	392.2	392.3	392.4
145°	403.4	403.6	403.9	404.1	404.4	404.5	404.5	404.5	404.5	404.5	404.5
147.5°	413.4	413.9	414.4	414.9	415.4	415.6	415.6	415.5	415.4	415.3	415.2
150°	424.5	424.8	425.1	425.4	425.7	425.9	425.9	425.8	425.7	425.7	425.6
152.5°	433.8	434.0	434.2	434.5	434.7	434.8	434.7	434.6	434.4	434.3	434.1
155°	442.3	442.4	442.5	442.6	442.7	442.7	442.6	442.3	442.1	441.8	441.6
157.5°	449.8	449.8	449.8	449.8	449.8	449.8	449.6	449.3	449.0	448.7	448.4
160°	456.3	456.1	455.8	455.6	455.3	455.2	455.2	455.1	455.0	454.9	454.8
162.5°	462.0	461.7	461.3	461.0	460.7	460.5	460.5	460.4	460.3	460.3	460.2
165°	466.6	466.2	465.8	465.4	465.0	464.8	464.8	464.8	464.8	464.8	464.8
167.5°	470.5	470.1	469.7	469.4	469.0	468.8	468.8	468.7	468.6	468.5	468.4
170°	473.8	473.3	472.8	472.3	471.8	471.6	471.6	471.7	471.8	471.9	472.0
172.5°	475.9	475.4	475.0	474.5	474.0	473.8	473.8	473.9	474.0	474.0	474.1
175°	477.3	476.8	476.4	475.9	475.4	475.2	475.2	475.3	475.4	475.4	475.5
177.5°	478.4	477.8	477.3	476.7	476.2	475.9	476.0	476.1	476.3	476.4	476.6
180°	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	2026.7	2055.6	2068.5	2071.7	2089.4	2078.1	2082.9	2081.3	2094.2	2095.8	2095.8
5°	2174.5	2208.3	2219.5	2235.6	2259.7	2266.2	2261.3	2271.0	2288.7	2275.8	2295.1
7.5°	2330.4	2367.4	2393.1	2428.5	2436.5	2457.4	2470.3	2481.5	2484.7	2486.3	2489.6
10°	2475.1	2521.7	2557.1	2616.5	2629.4	2640.6	2696.9	2674.4	2703.3	2693.7	2696.9
12.5°	2592.4	2684.0	2713.0	2812.6	2822.2	2860.8	2857.6	2893.0	2899.4	2912.3	2899.4
15°	2746.7	2852.8	2899.4	2955.6	2987.8	3032.8	3040.8	3089.0	3108.3	3126.0	3108.3
17.5°	2888.1	2944.4	3063.3	3108.3	3129.2	3153.3	3214.4	3232.1	3261.0	3249.8	3281.9
20°	2958.9	3039.2	3164.6	3241.7	3273.9	3296.4	3347.8	3375.1	3386.4	3386.4	3389.6
22.5°	3021.5	3137.3	3230.5	3318.9	3347.8	3363.9	3394.4	3415.3	3420.1	3423.3	3426.6
25°	3077.8	3182.3	3257.8	3307.6	3318.9	3318.9	3336.6	3323.7	3302.8	3318.9	3328.5
27.5°	3077.8	3151.7	3185.5	3203.2	3203.2	3159.8	3134.0	3081.0	3036.0	3023.2	3052.1
30°	3026.4	3060.1	3013.5	2970.1	2936.4	2907.4	2806.2	2725.8	2709.7	2698.5	2741.9
32.5°	2907.4	2864.0	2772.4	2647.1	2597.2	2531.3	2452.6	2391.5	2354.6	2341.7	2332.1
35°	2696.9	2584.4	2465.5	2296.7	2261.3	2177.8	2070.1	2025.1	1964.0	1962.4	1983.3
37.5°	2467.1	2293.5	2164.9	2004.2	1954.4	1866.0	1764.7	1718.1	1676.3	1644.2	1682.7
40°	2198.7	2047.6	1851.5	1719.7	1649.0	1602.4	1517.2	1465.8	1446.5	1430.4	1454.5
42.5°	1947.9	1782.4	1629.7	1494.7	1436.8	1383.8	1327.6	1277.7	1263.3	1261.7	1279.3
45°	1698.8	1536.5	1395.1	1279.3	1242.4	1210.2	1155.6	1141.1	1117.0	1100.9	1109.0
47.5°	1499.5	1332.4	1215.0	1126.6	1094.5	1067.2	1031.8	1007.7	986.8	980.4	990.0
50°	1303.4	1190.9	1070.4	996.5	972.4	946.6	919.3	896.8	887.2	880.7	887.2
52.5°	1145.9	1025.4	943.4	884.0	859.9	840.6	821.3	811.6	798.8	802.0	808.4
55°	1004.5	898.4	829.3	785.9	771.5	763.4	739.3	728.1	723.2	720.0	723.2
57.5°	871.1	794.0	742.5	705.6	686.3	681.5	662.2	662.2	657.3	652.5	654.1
60°	765.0	699.1	649.3	620.4	617.2	609.1	596.3	594.7	583.4	588.2	589.8
62.5°	657.3	604.3	570.6	552.9	541.6	538.4	530.4	528.8	523.9	525.6	522.3
65°	572.2	528.8	495.0	480.6	475.7	474.1	467.7	462.9	459.7	462.9	459.7
67.5°	487.0	458.1	432.3	417.9	411.4	409.8	405.0	401.8	403.4	398.6	401.8
70°	406.6	377.7	361.6	353.6	350.4	345.5	345.5	345.5	345.5	342.3	340.7
72.5°	342.3	313.4	302.2	297.3	294.1	292.5	287.7	289.3	287.7	286.1	292.5
75°	271.6	253.9	242.7	237.9	241.1	236.3	231.4	234.7	229.8	231.4	237.9
77.5°	205.7	197.7	191.3	188.0	184.8	181.6	181.6	178.4	178.4	178.4	178.4
80°	149.5	147.9	136.6	135.0	135.0	131.8	131.8	131.8	131.8	130.2	131.8
82.5°	99.6	98.0	94.8	93.2	90.0	91.6	91.6	88.4	88.4	86.8	88.4
85°	57.9	57.9	54.6	53.0	51.4	53.0	49.8	48.2	49.8	48.2	49.8
87.5°	27.3	24.1	25.7	24.1	20.9	22.5	19.3	20.9	19.3	17.7	20.9
90°	8.4	8.8	9.3	9.8	10.0	10.1	10.2	10.4	10.5	10.7	10.5
92.5°	8.0	8.4	8.9	9.4	9.6	9.6	9.6	9.6	9.6	9.6	9.6
95°	8.4	8.8	9.3	9.8	10.0	10.0	10.1	10.2	10.3	10.4	10.3
97.5°	8.3	8.7	9.0	9.4	9.6	9.6	9.7	9.8	9.9	10.0	9.9
100°	14.3	13.0	11.6	10.3	9.6	9.6	9.7	9.8	9.9	10.0	9.9
102.5°	72.9	55.0	37.2	19.3	10.4	10.4	10.4	10.4	10.4	10.4	10.4
105°	112.1	112.8	113.5	114.2	114.6	113.2	110.3	107.4	104.6	101.7	104.6
107.5°	134.6	135.0	135.4	135.8	136.0	136.2	136.5	136.8	137.1	137.4	137.1
110°	157.6	157.8	157.9	158.1	158.2	158.3	158.5	158.8	159.0	159.2	159.0

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
112.5°	179.8	179.8	179.7	179.6	179.6	179.8	180.1	180.4	180.7	181.0	180.7
115°	201.6	201.7	201.9	202.0	202.1	202.1	202.1	202.1	202.1	202.1	202.1
117.5°	224.1	224.0	223.9	223.8	223.8	223.8	223.8	223.8	223.8	223.8	223.8
120°	244.4	244.5	244.7	244.8	244.9	244.8	244.7	244.5	244.4	244.2	244.4
122.5°	264.6	264.7	264.8	264.9	264.9	264.8	264.7	264.5	264.4	264.2	264.4
125°	283.0	283.2	283.5	283.7	283.8	283.8	283.9	284.0	284.1	284.2	284.1
127.5°	302.3	302.2	302.1	302.0	302.0	302.0	301.9	301.8	301.8	301.7	301.8
130°	319.3	319.3	319.4	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5
132.5°	336.0	336.1	336.2	336.3	336.3	336.3	336.2	336.1	336.0	335.9	336.0
135°	351.1	351.3	351.4	351.6	351.7	351.8	351.9	352.1	352.2	352.4	352.2
137.5°	366.1	366.3	366.4	366.6	366.7	366.7	366.6	366.5	366.4	366.3	366.4
140°	379.7	380.0	380.2	380.5	380.6	380.6	380.7	380.8	380.8	380.9	380.8
142.5°	392.6	392.7	392.9	393.0	393.1	393.1	393.1	393.1	393.1	393.1	393.1
145°	404.6	404.7	404.8	404.9	404.9	405.0	405.1	405.3	405.4	405.6	405.4
147.5°	415.3	415.4	415.5	415.6	415.6	415.6	415.7	415.8	415.8	415.9	415.8
150°	425.6	425.6	425.6	425.6	425.6	425.6	425.7	425.8	425.8	425.9	425.8
152.5°	434.3	434.4	434.6	434.7	434.8	434.8	434.7	434.6	434.6	434.5	434.6
155°	441.9	442.3	442.6	442.9	443.1	443.0	442.7	442.5	442.2	442.0	442.2
157.5°	448.8	449.2	449.6	450.0	450.2	450.0	449.6	449.2	448.8	448.4	448.8
160°	455.3	455.8	456.3	456.8	457.0	456.8	456.3	455.8	455.3	454.8	455.3
162.5°	460.7	461.1	461.6	462.1	462.3	462.0	461.5	460.9	460.4	459.8	460.4
165°	465.4	466.1	466.7	467.4	467.7	467.3	466.6	465.9	465.2	464.5	465.2
167.5°	469.1	469.8	470.5	471.2	471.6	471.2	470.4	469.6	468.8	468.0	468.8
170°	472.6	473.2	473.9	474.5	474.8	474.4	473.6	472.9	472.1	471.3	472.1
172.5°	474.7	475.4	476.0	476.7	477.0	476.6	475.7	474.8	473.9	473.0	473.9
175°	476.2	477.0	477.7	478.4	478.8	478.3	477.4	476.4	475.5	474.5	475.5
177.5°	477.2	477.9	478.5	479.2	479.5	479.0	478.1	477.1	476.2	475.2	476.2
180°	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	2092.6	2087.8	2081.3	2081.3	2073.3	2073.3	2060.4	2037.9	2018.6	2012.2	2015.4
5°	2271.0	2272.6	2262.9	2254.9	2240.4	2229.2	2208.3	2168.1	2155.3	2129.5	2111.9
7.5°	2475.1	2468.7	2451.0	2438.1	2434.9	2409.2	2364.2	2316.0	2277.4	2251.7	2214.7
10°	2704.9	2679.2	2653.5	2645.5	2626.2	2582.8	2531.3	2478.3	2425.3	2369.0	2306.3
12.5°	2897.8	2848.0	2846.4	2827.1	2790.1	2766.0	2704.9	2629.4	2537.8	2475.1	2404.4
15°	3105.1	3058.5	3019.9	2984.6	2966.9	2896.2	2844.8	2749.9	2640.6	2573.1	2524.9
17.5°	3253.0	3232.1	3166.2	3150.1	3126.0	3044.0	2962.1	2868.9	2774.0	2679.2	2549.0
20°	3371.9	3359.1	3315.7	3293.2	3254.6	3190.3	3090.7	2983.0	2873.7	2738.7	2616.5
22.5°	3423.3	3407.3	3371.9	3352.6	3328.5	3273.9	3188.7	3066.5	2923.5	2803.0	2672.8
25°	3322.1	3351.0	3341.4	3333.3	3323.7	3291.6	3227.3	3119.6	2979.8	2843.1	2680.8
27.5°	3093.9	3143.7	3191.9	3198.3	3214.4	3227.3	3201.5	3124.4	3007.1	2862.4	2684.0
30°	2786.9	2809.4	2907.4	2936.4	2958.9	3040.8	3089.0	3069.8	2979.8	2849.6	2685.6
32.5°	2393.1	2452.6	2552.2	2621.3	2682.4	2774.0	2899.4	2949.2	2917.1	2811.0	2648.7
35°	2020.3	2091.0	2206.7	2295.1	2356.2	2486.3	2634.2	2741.9	2782.1	2729.0	2584.4
37.5°	1714.9	1800.1	1902.9	1936.7	2007.4	2168.1	2372.2	2521.7	2619.7	2624.6	2512.1
40°	1485.1	1528.5	1610.4	1661.8	1731.0	1866.0	2065.3	2262.9	2410.8	2460.6	2401.2
42.5°	1290.6	1324.3	1385.4	1448.1	1510.8	1613.6	1796.9	1981.7	2181.0	2280.6	2279.0
45°	1136.3	1171.7	1213.4	1264.9	1308.3	1419.2	1563.8	1753.5	1925.4	2079.7	2118.3
47.5°	1001.3	1031.8	1083.3	1105.8	1134.7	1239.2	1364.5	1541.3	1719.7	1896.5	1941.5
50°	901.6	927.4	962.7	977.2	1009.3	1086.5	1189.3	1332.4	1530.1	1692.4	1776.0
52.5°	811.6	830.9	858.2	869.5	892.0	949.9	1043.1	1155.6	1319.5	1486.7	1604.0
55°	734.5	747.3	766.6	779.5	795.6	847.0	916.1	1017.4	1158.8	1303.4	1417.6
57.5°	662.2	671.8	691.1	697.5	710.4	750.6	798.8	884.0	1014.1	1142.7	1253.6
60°	594.7	601.1	612.3	626.8	636.5	663.8	708.8	779.5	884.0	1001.3	1091.3
62.5°	530.4	540.0	543.2	549.7	557.7	583.4	618.8	670.2	761.8	858.2	953.1
65°	464.5	472.5	478.9	480.6	488.6	507.9	540.0	585.0	644.5	728.1	816.5
67.5°	403.4	408.2	411.4	417.9	425.9	435.6	461.3	495.0	549.7	617.2	687.9
70°	347.2	347.2	352.0	353.6	363.2	374.5	385.7	417.9	466.1	520.7	569.0
72.5°	286.1	294.1	292.5	300.5	298.9	307.0	321.4	342.3	377.7	421.1	467.7
75°	233.0	237.9	237.9	237.9	241.1	247.5	255.5	274.8	302.2	337.5	364.8
77.5°	181.6	184.8	184.8	184.8	186.4	192.9	200.9	213.8	233.0	253.9	270.0
80°	130.2	133.4	133.4	136.6	136.6	138.2	146.3	152.7	162.3	178.4	194.5
82.5°	88.4	90.0	93.2	93.2	91.6	94.8	96.4	102.9	112.5	115.7	127.0
85°	48.2	49.8	51.4	51.4	53.0	56.3	54.6	61.1	61.1	67.5	70.7
87.5°	19.3	22.5	22.5	20.9	22.5	22.5	22.5	25.7	27.3	28.9	27.3
90°	10.4	10.2	10.1	10.0	9.8	9.3	8.8	8.4	7.9	7.3	6.6
92.5°	9.6	9.6	9.6	9.6	9.4	8.9	8.4	8.0	7.5	6.9	6.2
95°	10.2	10.1	10.0	10.0	9.8	9.3	8.8	8.4	7.9	7.8	7.7
97.5°	9.8	9.7	9.6	9.6	9.4	9.0	8.7	8.3	7.9	16.2	24.5
100°	9.8	9.7	9.6	9.6	10.3	11.6	13.0	14.3	15.7	26.7	37.6
102.5°	10.4	10.4	10.4	10.4	19.3	37.2	55.0	72.9	90.7	89.7	88.8
105°	107.4	110.3	113.2	114.6	114.2	113.5	112.8	112.1	111.4	111.0	110.6
107.5°	136.8	136.5	136.2	136.0	135.8	135.4	135.0	134.6	134.2	133.6	133.1
110°	158.8	158.5	158.3	158.2	158.1	157.9	157.8	157.6	157.4	156.9	156.5



TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
112.5°	180.4	180.1	179.8	179.6	179.6	179.7	179.8	179.8	179.9	179.7	179.6
115°	202.1	202.1	202.1	202.1	202.0	201.9	201.7	201.6	201.4	201.5	201.5
117.5°	223.8	223.8	223.8	223.8	223.8	223.9	224.0	224.1	224.2	224.0	223.7
120°	244.5	244.7	244.8	244.9	244.8	244.7	244.5	244.4	244.2	244.3	244.4
122.5°	264.5	264.7	264.8	264.9	264.9	264.8	264.7	264.6	264.5	264.3	264.2
125°	284.0	283.9	283.8	283.8	283.7	283.5	283.2	283.0	282.8	283.0	283.1
127.5°	301.8	301.9	302.0	302.0	302.0	302.1	302.2	302.3	302.4	302.0	301.6
130°	319.5	319.5	319.5	319.5	319.5	319.4	319.3	319.3	319.2	319.0	318.7
132.5°	336.1	336.2	336.3	336.3	336.3	336.2	336.1	336.0	335.9	335.6	335.3
135°	352.1	351.9	351.8	351.7	351.6	351.4	351.3	351.1	350.9	350.6	350.3
137.5°	366.5	366.6	366.7	366.7	366.6	366.4	366.3	366.1	365.9	365.5	365.1
140°	380.8	380.7	380.6	380.6	380.5	380.2	380.0	379.7	379.5	379.3	379.2
142.5°	393.1	393.1	393.1	393.1	393.0	392.9	392.7	392.6	392.4	392.3	392.2
145°	405.3	405.1	405.0	404.9	404.9	404.8	404.7	404.6	404.5	404.5	404.5
147.5°	415.8	415.7	415.6	415.6	415.6	415.5	415.4	415.3	415.2	415.3	415.4
150°	425.8	425.7	425.6	425.6	425.6	425.6	425.6	425.6	425.6	425.7	425.7
152.5°	434.6	434.7	434.8	434.8	434.7	434.6	434.4	434.3	434.1	434.3	434.4
155°	442.5	442.7	443.0	443.1	442.9	442.6	442.3	441.9	441.6	441.8	442.1
157.5°	449.2	449.6	450.0	450.2	450.0	449.6	449.2	448.8	448.4	448.7	449.0
160°	455.8	456.3	456.8	457.0	456.8	456.3	455.8	455.3	454.8	454.9	455.0
162.5°	460.9	461.5	462.0	462.3	462.1	461.6	461.1	460.7	460.2	460.3	460.3
165°	465.9	466.6	467.3	467.7	467.4	466.7	466.1	465.4	464.8	464.8	464.8
167.5°	469.6	470.4	471.2	471.6	471.2	470.5	469.8	469.1	468.4	468.5	468.6
170°	472.9	473.6	474.4	474.8	474.5	473.9	473.2	472.6	472.0	471.9	471.8
172.5°	474.8	475.7	476.6	477.0	476.7	476.0	475.4	474.7	474.1	474.0	474.0
175°	476.4	477.4	478.3	478.8	478.4	477.7	477.0	476.2	475.5	475.4	475.4
177.5°	477.1	478.1	479.0	479.5	479.2	478.5	477.9	477.2	476.6	476.4	476.3
180°	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	2001.0	1994.5	1989.7	1989.7	1975.3	1960.8	1952.8	1949.5	1946.3	1933.5	1915.8
5°	2082.9	2062.0	2047.6	2033.1	2009.0	1983.3	1957.6	1943.1	1922.2	1893.3	1872.4
7.5°	2174.5	2124.7	2108.7	2091.0	2042.8	1999.4	1964.0	1933.5	1899.7	1862.7	1825.8
10°	2251.7	2198.7	2163.3	2132.8	2070.1	2012.2	1959.2	1914.2	1870.8	1822.6	1777.6
12.5°	2325.6	2250.1	2213.1	2168.1	2102.2	2018.6	1949.5	1893.3	1829.0	1779.2	1724.5
15°	2428.5	2301.5	2240.4	2211.5	2123.1	2025.1	1941.5	1857.9	1804.9	1729.4	1681.1
17.5°	2444.6	2341.7	2301.5	2227.6	2121.5	2010.6	1914.2	1830.6	1750.2	1682.7	1620.1
20°	2500.8	2365.8	2301.5	2254.9	2115.1	2002.6	1896.5	1788.8	1711.7	1639.3	1568.6
22.5°	2536.2	2383.5	2316.0	2242.0	2108.7	1973.6	1848.3	1755.1	1660.2	1586.3	1530.1
25°	2526.5	2373.8	2298.3	2229.2	2066.9	1931.9	1819.4	1700.4	1612.0	1531.7	1457.7
27.5°	2521.7	2349.7	2269.4	2192.2	2039.5	1898.1	1756.7	1660.2	1562.2	1469.0	1414.3
30°	2508.8	2319.2	2226.0	2142.4	1983.3	1835.4	1714.9	1602.4	1504.3	1419.2	1346.8
32.5°	2465.5	2267.8	2177.8	2087.8	1922.2	1774.4	1652.2	1547.7	1449.7	1361.3	1292.2
35°	2407.6	2206.7	2108.7	2013.8	1848.3	1698.8	1586.3	1477.0	1385.4	1300.2	1234.3
37.5°	2349.7	2136.0	2044.4	1935.1	1782.4	1626.5	1510.8	1412.7	1327.6	1239.2	1166.8
40°	2266.2	2052.4	1951.1	1857.9	1679.5	1533.3	1427.2	1338.8	1255.2	1171.7	1110.6
42.5°	2152.0	1960.8	1856.3	1753.5	1586.3	1441.7	1338.8	1260.0	1181.3	1112.2	1044.7
45°	2036.3	1849.9	1756.7	1665.1	1483.4	1346.8	1252.0	1179.7	1113.8	1038.3	983.6
47.5°	1896.5	1739.0	1645.8	1555.8	1383.8	1247.2	1160.4	1092.9	1031.8	969.1	917.7
50°	1753.5	1616.8	1531.7	1438.4	1274.5	1150.8	1065.6	1009.3	959.5	900.0	858.2
52.5°	1599.2	1480.2	1407.9	1317.9	1173.3	1059.1	972.4	916.1	874.3	830.9	794.0
55°	1435.2	1348.4	1271.3	1199.0	1062.4	959.5	882.4	832.5	803.6	763.4	731.3
57.5°	1287.4	1203.8	1157.2	1075.2	956.3	855.0	794.0	752.2	718.4	694.3	668.6
60°	1133.1	1065.6	1014.1	954.7	850.2	765.0	700.7	676.6	641.3	623.6	612.3
62.5°	985.2	937.0	888.8	843.8	750.6	670.2	622.0	591.5	570.6	552.9	543.2
65°	845.4	800.4	766.6	726.5	649.3	585.0	540.0	515.9	495.0	490.2	478.9
67.5°	708.8	689.5	652.5	620.4	554.5	504.7	470.9	440.4	429.1	424.3	414.7
70°	593.1	570.6	541.6	514.3	464.5	421.1	390.6	379.3	363.2	361.6	350.4
72.5°	488.6	461.3	440.4	419.5	382.5	343.9	327.9	311.8	303.8	297.3	292.5
75°	387.3	368.0	353.6	335.9	303.8	278.0	255.5	249.1	244.3	242.7	239.5
77.5°	289.3	276.4	270.0	252.3	229.8	207.3	197.7	188.0	188.0	184.8	186.4
80°	205.7	197.7	189.7	180.0	160.7	151.1	143.0	136.6	133.4	131.8	133.4
82.5°	130.2	125.4	123.8	117.3	104.5	99.6	93.2	88.4	88.4	88.4	88.4
85°	72.3	72.3	72.3	62.7	57.9	53.0	49.8	48.2	48.2	48.2	49.8
87.5°	30.5	30.5	25.7	25.7	24.1	20.9	19.3	19.3	20.9	20.9	22.5
90°	6.0	5.3	5.0	4.6	3.7	2.8	2.0	1.1	2.0	2.8	3.7
92.5°	5.6	4.9	4.6	4.7	4.9	5.0	5.2	5.4	5.2	5.0	4.9
95°	7.6	7.5	7.5	8.8	11.5	14.2	16.9	19.6	16.9	14.2	11.5
97.5°	32.8	41.1	45.3	44.4	42.7	41.0	39.2	37.5	39.2	41.0	42.7
100°	48.6	59.5	65.0	64.3	62.9	61.4	60.0	58.6	60.0	61.4	62.9
102.5°	87.8	86.9	86.4	85.9	85.0	84.0	83.1	82.1	83.1	84.0	85.0
105°	110.2	109.8	109.6	109.4	108.9	108.4	108.0	107.5	108.0	108.4	108.9
107.5°	132.5	132.0	131.7	131.6	131.4	131.1	130.9	130.7	130.9	131.1	131.4
110°	156.0	155.5	155.3	155.2	154.9	154.7	154.4	154.2	154.4	154.7	154.9

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°	185°	190°	195°
112.5°	179.4	179.3	179.2	179.0	178.5	178.0	177.6	177.1	177.6	178.0	178.5
115°	201.6	201.7	201.7	201.6	201.3	201.1	200.8	200.6	200.8	201.1	201.3
117.5°	223.5	223.2	223.1	222.9	222.6	222.3	222.0	221.7	222.0	222.3	222.6
120°	244.5	244.6	244.6	244.4	244.1	243.8	243.4	243.1	243.4	243.8	244.1
122.5°	264.0	263.9	263.8	263.7	263.6	263.4	263.3	263.1	263.3	263.4	263.6
125°	283.3	283.4	283.5	283.3	283.0	282.7	282.3	282.0	282.3	282.7	283.0
127.5°	301.2	300.8	300.6	300.6	300.5	300.4	300.3	300.2	300.3	300.4	300.5
130°	318.5	318.2	318.1	318.1	318.0	317.9	317.8	317.7	317.8	317.9	318.0
132.5°	335.0	334.7	334.5	334.4	334.3	334.1	334.0	333.8	334.0	334.1	334.3
135°	350.0	349.7	349.5	349.5	349.6	349.7	349.8	349.9	349.8	349.7	349.6
137.5°	364.8	364.4	364.2	364.2	364.2	364.2	364.2	364.2	364.2	364.2	364.2
140°	379.0	378.9	378.8	378.7	378.6	378.4	378.3	378.1	378.3	378.4	378.6
142.5°	392.1	392.0	392.0	391.8	391.5	391.2	390.9	390.6	390.9	391.2	391.5
145°	404.5	404.5	404.5	404.4	404.1	403.9	403.6	403.4	403.6	403.9	404.1
147.5°	415.5	415.6	415.6	415.4	414.9	414.4	413.9	413.4	413.9	414.4	414.9
150°	425.8	425.9	425.9	425.7	425.4	425.1	424.8	424.5	424.8	425.1	425.4
152.5°	434.6	434.7	434.8	434.7	434.5	434.2	434.0	433.8	434.0	434.2	434.5
155°	442.3	442.6	442.7	442.7	442.6	442.5	442.4	442.3	442.4	442.5	442.6
157.5°	449.3	449.6	449.8	449.8	449.8	449.8	449.8	449.8	449.8	449.8	449.8
160°	455.1	455.2	455.2	455.3	455.6	455.8	456.1	456.3	456.1	455.8	455.6
162.5°	460.4	460.5	460.5	460.7	461.0	461.3	461.7	462.0	461.7	461.3	461.0
165°	464.8	464.8	464.8	465.0	465.4	465.8	466.2	466.6	466.2	465.8	465.4
167.5°	468.7	468.8	468.8	469.0	469.4	469.7	470.1	470.5	470.1	469.7	469.4
170°	471.7	471.6	471.6	471.8	472.3	472.8	473.3	473.8	473.3	472.8	472.3
172.5°	473.9	473.8	473.8	474.0	474.5	475.0	475.4	475.9	475.4	475.0	474.5
175°	475.3	475.2	475.2	475.4	475.9	476.4	476.8	477.3	476.8	476.4	475.9
177.5°	476.1	476.0	475.9	476.2	476.7	477.3	477.8	478.4	477.8	477.3	476.7
180°	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	1911.0	1904.5	1907.8	1891.7	1877.2	1856.3	1838.6	1835.4	1832.2	1841.9	1835.4
5°	1856.3	1848.3	1840.2	1821.0	1792.0	1774.4	1748.6	1747.0	1737.4	1722.9	1726.1
7.5°	1796.9	1792.0	1780.8	1750.2	1724.5	1694.0	1673.1	1655.4	1647.4	1634.5	1629.7
10°	1748.6	1731.0	1721.3	1687.6	1657.0	1624.9	1597.6	1584.7	1570.2	1559.0	1551.0
12.5°	1682.7	1677.9	1650.6	1623.3	1597.6	1560.6	1539.7	1502.7	1483.4	1493.1	1489.9
15°	1639.3	1616.8	1610.4	1571.8	1528.5	1504.3	1465.8	1441.7	1433.6	1419.2	1401.5
17.5°	1581.5	1567.0	1544.5	1509.2	1459.3	1425.6	1398.3	1375.8	1366.1	1346.8	1332.4
20°	1526.8	1502.7	1485.1	1452.9	1404.7	1361.3	1327.6	1313.1	1289.0	1272.9	1264.9
22.5°	1477.0	1459.3	1433.6	1385.4	1343.6	1301.8	1261.7	1240.8	1218.3	1208.6	1195.8
25°	1415.9	1387.0	1369.3	1316.3	1271.3	1237.5	1200.6	1173.3	1160.4	1144.3	1141.1
27.5°	1356.5	1329.2	1308.3	1261.7	1207.0	1163.6	1141.1	1121.8	1099.3	1099.3	1091.3
30°	1297.0	1277.7	1245.6	1200.6	1149.2	1107.4	1081.6	1064.0	1055.9	1049.5	1047.9
32.5°	1237.5	1211.8	1192.5	1131.5	1092.9	1054.3	1035.0	1020.6	1010.9	1009.3	1010.9
35°	1176.5	1147.5	1128.3	1073.6	1035.0	999.7	991.6	978.8	974.0	972.4	980.4
37.5°	1112.2	1089.7	1065.6	1020.6	977.2	956.3	940.2	935.4	933.8	943.4	946.6
40°	1052.7	1033.4	1010.9	962.7	930.6	908.1	900.0	895.2	901.6	911.3	916.1
42.5°	996.5	969.1	951.5	908.1	879.1	866.3	856.6	856.6	863.1	874.3	882.4
45°	937.0	916.1	898.4	859.9	834.1	819.7	818.1	819.7	827.7	835.7	845.4
47.5°	879.1	858.2	839.0	806.8	784.3	776.3	774.7	776.3	789.1	800.4	811.6
50°	826.1	803.6	785.9	755.4	737.7	728.1	729.7	737.7	747.3	763.4	777.9
52.5°	763.4	747.3	731.3	704.0	687.9	681.5	686.3	692.7	710.4	721.6	739.3
55°	702.3	687.9	675.0	654.1	641.3	636.5	639.7	649.3	663.8	683.1	704.0
57.5°	646.1	630.0	617.2	602.7	588.2	589.8	591.5	604.3	622.0	639.7	663.8
60°	583.4	573.8	562.5	544.8	538.4	538.4	543.2	557.7	573.8	602.7	623.6
62.5°	527.2	514.3	506.3	495.0	485.4	487.0	498.2	511.1	530.4	554.5	581.8
65°	469.3	454.8	448.4	438.8	435.6	437.2	445.2	464.5	485.4	506.3	532.0
67.5°	405.0	400.2	393.8	384.1	387.3	388.9	397.0	413.1	435.6	456.4	485.4
70°	350.4	340.7	339.1	331.1	331.1	335.9	352.0	363.2	384.1	406.6	437.2
72.5°	292.5	284.5	284.5	278.0	282.9	287.7	295.7	311.8	331.1	353.6	379.3
75°	233.0	229.8	233.0	229.8	229.8	237.9	247.5	260.4	281.3	305.4	326.3
77.5°	180.0	180.0	178.4	183.2	183.2	188.0	200.9	213.8	229.8	249.1	271.6
80°	131.8	131.8	131.8	136.6	141.4	141.4	149.5	165.5	180.0	192.9	213.8
82.5°	90.0	90.0	90.0	93.2	99.6	99.6	109.3	118.9	135.0	146.3	155.9
85°	54.6	54.6	53.0	56.3	57.9	62.7	70.7	77.1	85.2	94.8	104.5
87.5°	24.1	24.1	25.7	27.3	28.9	32.1	35.4	38.6	46.6	49.8	54.6
90°	4.6	5.0	5.3	6.0	6.6	7.3	7.9	8.4	8.8	9.3	9.8
92.5°	4.7	4.6	4.9	5.6	6.2	6.9	7.5	8.0	8.4	8.9	9.4
95°	8.8	7.5	7.5	7.6	7.7	7.8	7.9	8.4	8.8	9.3	9.8
97.5°	44.4	45.3	41.1	32.8	24.5	16.2	7.9	8.3	8.7	9.0	9.4
100°	64.3	65.0	59.5	48.6	37.6	26.7	15.7	14.3	13.0	11.6	10.3
102.5°	85.9	86.4	86.9	87.8	88.8	89.7	90.7	72.9	55.0	37.2	19.3
105°	109.4	109.6	109.8	110.2	110.6	111.0	111.4	112.1	112.8	113.5	114.2
107.5°	131.6	131.7	132.0	132.5	133.1	133.6	134.2	134.6	135.0	135.4	135.8
110°	155.2	155.3	155.5	156.0	156.5	156.9	157.4	157.6	157.8	157.9	158.1

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	200°	202.5°	205°	210°	215°	220°	225°	230°	235°	240°	245°
112.5°	179.0	179.2	179.3	179.4	179.6	179.7	179.9	179.8	179.8	179.7	179.6
115°	201.6	201.7	201.7	201.6	201.5	201.5	201.4	201.6	201.7	201.9	202.0
117.5°	222.9	223.1	223.2	223.5	223.7	224.0	224.2	224.1	224.0	223.9	223.8
120°	244.4	244.6	244.6	244.5	244.4	244.3	244.2	244.4	244.5	244.7	244.8
122.5°	263.7	263.8	263.9	264.0	264.2	264.3	264.5	264.6	264.7	264.8	264.9
125°	283.3	283.5	283.4	283.3	283.1	283.0	282.8	283.0	283.2	283.5	283.7
127.5°	300.6	300.6	300.8	301.2	301.6	302.0	302.4	302.3	302.2	302.1	302.0
130°	318.1	318.1	318.2	318.5	318.7	319.0	319.2	319.3	319.3	319.4	319.5
132.5°	334.4	334.5	334.7	335.0	335.3	335.6	335.9	336.0	336.1	336.2	336.3
135°	349.5	349.5	349.7	350.0	350.3	350.6	350.9	351.1	351.3	351.4	351.6
137.5°	364.2	364.2	364.4	364.8	365.1	365.5	365.9	366.1	366.3	366.4	366.6
140°	378.7	378.8	378.9	379.0	379.2	379.3	379.5	379.7	380.0	380.2	380.5
142.5°	391.8	392.0	392.0	392.1	392.2	392.3	392.4	392.6	392.7	392.9	393.0
145°	404.4	404.5	404.5	404.5	404.5	404.5	404.5	404.6	404.7	404.8	404.9
147.5°	415.4	415.6	415.6	415.5	415.4	415.3	415.2	415.3	415.4	415.5	415.6
150°	425.7	425.9	425.9	425.8	425.7	425.7	425.6	425.6	425.6	425.6	425.6
152.5°	434.7	434.8	434.7	434.6	434.4	434.3	434.1	434.3	434.4	434.6	434.7
155°	442.7	442.7	442.6	442.3	442.1	441.8	441.6	441.9	442.3	442.6	442.9
157.5°	449.8	449.8	449.6	449.3	449.0	448.7	448.4	448.8	449.2	449.6	450.0
160°	455.3	455.2	455.2	455.1	455.0	454.9	454.8	455.3	455.8	456.3	456.8
162.5°	460.7	460.5	460.5	460.4	460.3	460.3	460.2	460.7	461.1	461.6	462.1
165°	465.0	464.8	464.8	464.8	464.8	464.8	464.8	465.4	466.1	466.7	467.4
167.5°	469.0	468.8	468.8	468.7	468.6	468.5	468.4	469.1	469.8	470.5	471.2
170°	471.8	471.6	471.6	471.7	471.8	471.9	472.0	472.6	473.2	473.9	474.5
172.5°	474.0	473.8	473.8	473.9	474.0	474.0	474.1	474.7	475.4	476.0	476.7
175°	475.4	475.2	475.2	475.3	475.4	475.4	475.5	476.2	477.0	477.7	478.4
177.5°	476.2	475.9	476.0	476.1	476.3	476.4	476.6	477.2	477.9	478.5	479.2
180°	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	1830.6	1829.0	1821.0	1824.2	1814.5	1817.7	1822.6	1824.2	1830.6	1825.8	1824.2
5°	1718.1	1714.9	1710.1	1705.2	1703.6	1710.1	1698.8	1702.0	1705.2	1710.1	1716.5
7.5°	1626.5	1624.9	1620.1	1612.0	1608.8	1605.6	1607.2	1618.5	1616.8	1615.2	1626.5
10°	1542.9	1544.5	1534.9	1533.3	1523.6	1522.0	1523.6	1526.8	1531.7	1538.1	1539.7
12.5°	1456.1	1477.0	1459.3	1452.9	1438.4	1446.5	1449.7	1435.2	1443.3	1448.1	1472.2
15°	1401.5	1391.8	1380.6	1380.6	1374.2	1370.9	1362.9	1374.2	1380.6	1390.2	1387.0
17.5°	1325.9	1309.9	1303.4	1297.0	1298.6	1305.0	1287.4	1313.1	1313.1	1317.9	1309.9
20°	1260.0	1247.2	1239.2	1235.9	1231.1	1227.9	1226.3	1232.7	1242.4	1245.6	1253.6
22.5°	1190.9	1190.9	1178.1	1173.3	1170.0	1165.2	1173.3	1168.4	1174.9	1181.3	1194.2
25°	1133.1	1133.1	1128.3	1121.8	1117.0	1113.8	1118.6	1117.0	1121.8	1129.9	1133.1
27.5°	1086.5	1081.6	1080.0	1078.4	1076.8	1078.4	1076.8	1081.6	1086.5	1088.1	1084.9
30°	1046.3	1041.5	1043.1	1043.1	1044.7	1043.1	1041.5	1046.3	1047.9	1044.7	1046.3
32.5°	1009.3	1009.3	1012.5	1014.1	1014.1	1015.8	1017.4	1014.1	1015.8	1010.9	1012.5
35°	978.8	982.0	985.2	986.8	988.4	986.8	990.0	988.4	985.2	982.0	980.4
37.5°	948.3	951.5	957.9	959.5	964.3	965.9	962.7	962.7	961.1	954.7	951.5
40°	916.1	919.3	927.4	932.2	935.4	940.2	937.0	937.0	930.6	924.1	919.3
42.5°	885.6	892.0	900.0	904.9	911.3	911.3	911.3	908.1	900.0	893.6	888.8
45°	855.0	856.6	867.9	875.9	882.4	882.4	882.4	877.5	872.7	859.9	853.4
47.5°	821.3	826.1	839.0	847.0	853.4	855.0	855.0	850.2	840.6	829.3	821.3
50°	784.3	792.4	806.8	818.1	826.1	829.3	824.5	821.3	810.0	797.2	787.5
52.5°	749.0	758.6	776.3	785.9	797.2	798.8	797.2	792.4	779.5	761.8	753.8
55°	713.6	721.6	740.9	757.0	766.6	769.9	766.6	758.6	742.5	724.8	716.8
57.5°	675.0	686.3	707.2	723.2	734.5	736.1	732.9	724.8	712.0	689.5	678.2
60°	634.8	649.3	670.2	686.3	700.7	702.3	699.1	687.9	671.8	649.3	639.7
62.5°	594.7	605.9	630.0	647.7	659.0	667.0	660.6	649.3	633.2	610.7	596.3
65°	548.1	564.1	585.0	601.1	614.0	615.6	612.3	602.7	585.0	560.9	549.7
67.5°	503.1	514.3	535.2	556.1	560.9	565.7	560.9	551.3	536.8	515.9	499.8
70°	448.4	458.1	483.8	498.2	504.7	509.5	506.3	496.6	483.8	464.5	451.6
72.5°	393.8	401.8	425.9	437.2	450.0	448.4	446.8	440.4	422.7	409.8	401.8
75°	335.9	345.5	361.6	376.1	380.9	380.9	380.9	376.1	364.8	343.9	335.9
77.5°	282.9	287.7	300.5	308.6	313.4	315.0	313.4	305.4	298.9	284.5	279.7
80°	217.0	229.8	239.5	241.1	247.5	247.5	247.5	244.3	237.9	223.4	221.8
82.5°	163.9	167.1	176.8	181.6	184.8	183.2	183.2	176.8	175.2	167.1	163.9
85°	110.9	115.7	114.1	120.5	122.1	118.9	118.9	122.1	114.1	115.7	110.9
87.5°	61.1	61.1	64.3	62.7	69.1	69.1	65.9	67.5	64.3	62.7	61.1
90°	10.0	10.1	10.2	10.4	10.5	10.7	10.5	10.4	10.2	10.1	10.0
92.5°	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6	9.6
95°	10.0	10.0	10.1	10.2	10.3	10.4	10.3	10.2	10.1	10.0	10.0
97.5°	9.6	9.6	9.7	9.8	9.9	10.0	9.9	9.8	9.7	9.6	9.6
100°	9.6	9.6	9.7	9.8	9.9	10.0	9.9	9.8	9.7	9.6	9.6
102.5°	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4	10.4
105°	114.6	113.2	110.3	107.4	104.6	101.7	104.6	107.4	110.3	113.2	114.6
107.5°	136.0	136.2	136.5	136.8	137.1	137.4	137.1	136.8	136.5	136.2	136.0
110°	158.2	158.3	158.5	158.8	159.0	159.2	159.0	158.8	158.5	158.3	158.2

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	247.5°	250°	255°	260°	265°	270°	275°	280°	285°	290°	292.5°
112.5°	179.6	179.8	180.1	180.4	180.7	181.0	180.7	180.4	180.1	179.8	179.6
115°	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1	202.1
117.5°	223.8	223.8	223.8	223.8	223.8	223.8	223.8	223.8	223.8	223.8	223.8
120°	244.9	244.8	244.7	244.5	244.4	244.2	244.4	244.5	244.7	244.8	244.9
122.5°	264.9	264.8	264.7	264.5	264.4	264.2	264.4	264.5	264.7	264.8	264.9
125°	283.8	283.8	283.9	284.0	284.1	284.2	284.1	284.0	283.9	283.8	283.8
127.5°	302.0	302.0	301.9	301.8	301.8	301.7	301.8	301.8	301.9	302.0	302.0
130°	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5	319.5
132.5°	336.3	336.3	336.2	336.1	336.0	335.9	336.0	336.1	336.2	336.3	336.3
135°	351.7	351.8	351.9	352.1	352.2	352.4	352.2	352.1	351.9	351.8	351.7
137.5°	366.7	366.7	366.6	366.5	366.4	366.3	366.4	366.5	366.6	366.7	366.7
140°	380.6	380.6	380.7	380.8	380.8	380.9	380.8	380.8	380.7	380.6	380.6
142.5°	393.1	393.1	393.1	393.1	393.1	393.1	393.1	393.1	393.1	393.1	393.1
145°	404.9	405.0	405.1	405.3	405.4	405.6	405.4	405.3	405.1	405.0	404.9
147.5°	415.6	415.6	415.7	415.8	415.8	415.9	415.8	415.8	415.7	415.6	415.6
150°	425.6	425.6	425.7	425.8	425.8	425.9	425.8	425.8	425.7	425.6	425.6
152.5°	434.8	434.8	434.7	434.6	434.6	434.5	434.6	434.6	434.7	434.8	434.8
155°	443.1	443.0	442.7	442.5	442.2	442.0	442.2	442.5	442.7	443.0	443.1
157.5°	450.2	450.0	449.6	449.2	448.8	448.4	448.8	449.2	449.6	450.0	450.2
160°	457.0	456.8	456.3	455.8	455.3	454.8	455.3	455.8	456.3	456.8	457.0
162.5°	462.3	462.0	461.5	460.9	460.4	459.8	460.4	460.9	461.5	462.0	462.3
165°	467.7	467.3	466.6	465.9	465.2	464.5	465.2	465.9	466.6	467.3	467.7
167.5°	471.6	471.2	470.4	469.6	468.8	468.0	468.8	469.6	470.4	471.2	471.6
170°	474.8	474.4	473.6	472.9	472.1	471.3	472.1	472.9	473.6	474.4	474.8
172.5°	477.0	476.6	475.7	474.8	473.9	473.0	473.9	474.8	475.7	476.6	477.0
175°	478.8	478.3	477.4	476.4	475.5	474.5	475.5	476.4	477.4	478.3	478.8
177.5°	479.5	479.0	478.1	477.1	476.2	475.2	476.2	477.1	478.1	479.0	479.5
180°	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
0°	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9	1939.9
2.5°	1824.2	1833.8	1824.2	1830.6	1833.8	1841.9	1845.1	1859.5	1864.4	1875.6	1875.6
5°	1714.9	1719.7	1721.3	1727.7	1734.2	1750.2	1761.5	1782.4	1806.5	1809.7	1824.2
7.5°	1626.5	1634.5	1647.4	1642.6	1653.8	1677.9	1692.4	1718.1	1742.2	1755.1	1772.7
10°	1547.7	1557.4	1562.2	1567.0	1587.9	1608.8	1631.3	1649.0	1681.1	1700.4	1714.9
12.5°	1483.4	1475.4	1485.1	1502.7	1526.8	1539.7	1570.2	1597.6	1621.7	1642.6	1655.4
15°	1399.9	1406.3	1415.9	1446.5	1452.9	1485.1	1496.3	1526.8	1571.8	1591.1	1607.2
17.5°	1319.5	1340.4	1359.7	1370.9	1390.2	1415.9	1448.1	1481.8	1510.8	1533.3	1552.6
20°	1255.2	1276.1	1287.4	1295.4	1314.7	1350.1	1380.6	1422.4	1459.3	1477.0	1502.7
22.5°	1203.8	1203.8	1219.9	1244.0	1255.2	1289.0	1314.7	1359.7	1399.9	1422.4	1446.5
25°	1139.5	1149.2	1162.0	1182.9	1199.0	1226.3	1263.3	1301.8	1345.2	1364.5	1395.1
27.5°	1086.5	1097.7	1115.4	1120.2	1136.3	1160.4	1199.0	1240.8	1285.8	1306.7	1332.4
30°	1046.3	1052.7	1059.1	1068.8	1083.3	1104.1	1136.3	1173.3	1227.9	1244.0	1276.1
32.5°	1010.9	1014.1	1017.4	1025.4	1033.4	1054.3	1080.0	1120.2	1165.2	1189.3	1218.3
35°	978.8	975.6	977.2	982.0	990.0	998.1	1025.4	1059.1	1100.9	1129.9	1152.4
37.5°	948.3	941.8	940.2	940.2	943.4	953.1	974.0	1002.9	1047.9	1072.0	1094.5
40°	914.5	908.1	904.9	903.2	901.6	908.1	924.1	953.1	988.4	1010.9	1036.6
42.5°	882.4	875.9	867.9	866.3	863.1	866.3	877.5	904.9	935.4	957.9	978.8
45°	850.2	839.0	829.3	822.9	824.5	819.7	827.7	848.6	884.0	898.4	919.3
47.5°	814.9	802.0	789.1	782.7	776.3	779.5	782.7	800.4	830.9	845.4	866.3
50°	781.1	763.4	749.0	740.9	736.1	732.9	736.1	753.8	776.3	789.1	806.8
52.5°	742.5	724.8	710.4	697.5	691.1	686.3	687.9	704.0	724.8	737.7	755.4
55°	707.2	684.7	665.4	649.3	644.5	642.9	641.3	652.5	670.2	683.1	697.5
57.5°	667.0	644.5	623.6	604.3	594.7	593.1	593.1	596.3	618.8	628.4	636.5
60°	626.8	602.7	580.2	562.5	548.1	543.2	541.6	548.1	559.3	569.0	580.2
62.5°	581.8	557.7	530.4	514.3	499.8	487.0	491.8	493.4	509.5	514.3	523.9
65°	538.4	511.1	488.6	462.9	446.8	438.8	435.6	438.8	451.6	453.2	459.7
67.5°	488.6	462.9	435.6	417.9	403.4	388.9	385.7	385.7	392.2	397.0	405.0
70°	440.4	414.7	384.1	364.8	350.4	337.5	332.7	331.1	335.9	339.1	347.2
72.5°	384.1	358.4	335.9	315.0	297.3	287.7	282.9	279.7	284.5	287.7	289.3
75°	324.7	303.8	281.3	260.4	249.1	239.5	233.0	228.2	231.4	231.4	231.4
77.5°	268.4	247.5	229.8	215.4	200.9	189.7	184.8	180.0	181.6	181.6	184.8
80°	208.9	194.5	180.0	167.1	154.3	144.6	141.4	136.6	133.4	131.8	131.8
82.5°	154.3	143.0	130.2	118.9	112.5	102.9	99.6	93.2	93.2	91.6	91.6
85°	102.9	96.4	83.6	75.5	70.7	65.9	62.7	59.5	54.6	54.6	53.0
87.5°	54.6	51.4	48.2	38.6	38.6	33.8	32.1	30.5	25.7	27.3	27.3
90°	9.8	9.3	8.8	8.4	7.9	7.3	6.6	6.0	5.3	5.0	4.6
92.5°	9.4	8.9	8.4	8.0	7.5	6.9	6.2	5.6	4.9	4.6	4.7
95°	9.8	9.3	8.8	8.4	7.9	7.8	7.7	7.6	7.5	7.5	8.8
97.5°	9.4	9.0	8.7	8.3	7.9	16.2	24.5	32.8	41.1	45.3	44.4
100°	10.3	11.6	13.0	14.3	15.7	26.7	37.6	48.6	59.5	65.0	64.3
102.5°	19.3	37.2	55.0	72.9	90.7	89.7	88.8	87.8	86.9	86.4	85.9
105°	114.2	113.5	112.8	112.1	111.4	111.0	110.6	110.2	109.8	109.6	109.4
107.5°	135.8	135.4	135.0	134.6	134.2	133.6	133.1	132.5	132.0	131.7	131.6
110°	158.1	157.9	157.8	157.6	157.4	156.9	156.5	156.0	155.5	155.3	155.2

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	295°	300°	305°	310°	315°	320°	325°	330°	335°	337.5°	340°
112.5°	179.6	179.7	179.8	179.8	179.9	179.7	179.6	179.4	179.3	179.2	179.0
115°	202.0	201.9	201.7	201.6	201.4	201.5	201.5	201.6	201.7	201.7	201.6
117.5°	223.8	223.9	224.0	224.1	224.2	224.0	223.7	223.5	223.2	223.1	222.9
120°	244.8	244.7	244.5	244.4	244.2	244.3	244.4	244.5	244.6	244.6	244.4
122.5°	264.9	264.8	264.7	264.6	264.5	264.3	264.2	264.0	263.9	263.8	263.7
125°	283.7	283.5	283.2	283.0	282.8	283.0	283.1	283.3	283.4	283.5	283.3
127.5°	302.0	302.1	302.2	302.3	302.4	302.0	301.6	301.2	300.8	300.6	300.6
130°	319.5	319.4	319.3	319.3	319.2	319.0	318.7	318.5	318.2	318.1	318.1
132.5°	336.3	336.2	336.1	336.0	335.9	335.6	335.3	335.0	334.7	334.5	334.4
135°	351.6	351.4	351.3	351.1	350.9	350.6	350.3	350.0	349.7	349.5	349.5
137.5°	366.6	366.4	366.3	366.1	365.9	365.5	365.1	364.8	364.4	364.2	364.2
140°	380.5	380.2	380.0	379.7	379.5	379.3	379.2	379.0	378.9	378.8	378.7
142.5°	393.0	392.9	392.7	392.6	392.4	392.3	392.2	392.1	392.0	392.0	391.8
145°	404.9	404.8	404.7	404.6	404.5	404.5	404.5	404.5	404.5	404.5	404.4
147.5°	415.6	415.5	415.4	415.3	415.2	415.3	415.4	415.5	415.6	415.6	415.4
150°	425.6	425.6	425.6	425.6	425.6	425.7	425.7	425.8	425.9	425.9	425.7
152.5°	434.7	434.6	434.4	434.3	434.1	434.3	434.4	434.6	434.7	434.8	434.7
155°	442.9	442.6	442.3	441.9	441.6	441.8	442.1	442.3	442.6	442.7	442.7
157.5°	450.0	449.6	449.2	448.8	448.4	448.7	449.0	449.3	449.6	449.8	449.8
160°	456.8	456.3	455.8	455.3	454.8	454.9	455.0	455.1	455.2	455.2	455.3
162.5°	462.1	461.6	461.1	460.7	460.2	460.3	460.3	460.4	460.5	460.5	460.7
165°	467.4	466.7	466.1	465.4	464.8	464.8	464.8	464.8	464.8	464.8	465.0
167.5°	471.2	470.5	469.8	469.1	468.4	468.5	468.6	468.7	468.8	468.8	469.0
170°	474.5	473.9	473.2	472.6	472.0	471.9	471.8	471.7	471.6	471.6	471.8
172.5°	476.7	476.0	475.4	474.7	474.1	474.0	474.0	473.9	473.8	473.8	474.0
175°	478.4	477.7	477.0	476.2	475.5	475.4	475.4	475.3	475.2	475.2	475.4
177.5°	479.2	478.5	477.9	477.2	476.6	476.4	476.3	476.1	476.0	475.9	476.2
180°	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3	477.3

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
0°	1939.9	1939.9	1939.9	1939.9
2.5°	1886.9	1902.9	1917.4	1939.9
5°	1845.1	1867.6	1898.1	1931.9
7.5°	1796.9	1832.2	1872.4	1919.0
10°	1751.9	1792.0	1843.5	1899.7
12.5°	1705.2	1753.5	1809.7	1870.8
15°	1652.2	1700.4	1763.1	1845.1
17.5°	1604.0	1661.8	1729.4	1816.1
20°	1547.7	1602.4	1676.3	1776.0
22.5°	1497.9	1560.6	1642.6	1729.4
25°	1443.3	1497.9	1579.9	1684.3
27.5°	1388.6	1456.1	1534.9	1636.1
30°	1335.6	1391.8	1477.0	1583.1
32.5°	1277.7	1345.2	1424.0	1523.6
35°	1215.0	1279.3	1353.3	1460.9
37.5°	1158.8	1221.5	1297.0	1391.8
40°	1096.1	1162.0	1231.1	1325.9
42.5°	1035.0	1094.5	1163.6	1250.4
45°	975.6	1027.0	1089.7	1165.2
47.5°	914.5	957.9	1015.8	1083.3
50°	848.6	895.2	938.6	994.9
52.5°	787.5	827.7	863.1	909.7
55°	728.1	755.4	784.3	819.7
57.5°	665.4	686.3	707.2	744.1
60°	602.7	622.0	633.2	657.3
62.5°	541.6	549.7	564.1	578.6
65°	474.1	485.4	493.4	511.1
67.5°	413.1	417.9	425.9	437.2
70°	348.8	360.0	363.2	371.3
72.5°	294.1	298.9	302.2	303.8
75°	233.0	237.9	241.1	250.7
77.5°	183.2	181.6	188.0	189.7
80°	135.0	130.2	131.8	138.2
82.5°	88.4	90.0	88.4	88.4
85°	54.6	53.0	49.8	51.4
87.5°	24.1	24.1	22.5	22.5
90°	3.7	2.8	2.0	1.1
92.5°	4.9	5.0	5.2	5.4
95°	11.5	14.2	16.9	19.6
97.5°	42.7	41.0	39.2	37.5
100°	62.9	61.4	60.0	58.6
102.5°	85.0	84.0	83.1	82.1
105°	108.9	108.4	108.0	107.5
107.5°	131.4	131.1	130.9	130.7
110°	154.9	154.7	154.4	154.2

TEST NUMBER: P1012948

CATALOG NUMBER: S124DIP-B1195D365UB2750-4F0-XX-W2A-A_3500K

CANDELA DISTRIBUTION (continued):

	345°	350°	355°	360°
112.5°	178.5	178.0	177.6	177.1
115°	201.3	201.1	200.8	200.6
117.5°	222.6	222.3	222.0	221.7
120°	244.1	243.8	243.4	243.1
122.5°	263.6	263.4	263.3	263.1
125°	283.0	282.7	282.3	282.0
127.5°	300.5	300.4	300.3	300.2
130°	318.0	317.9	317.8	317.7
132.5°	334.3	334.1	334.0	333.8
135°	349.6	349.7	349.8	349.9
137.5°	364.2	364.2	364.2	364.2
140°	378.6	378.4	378.3	378.1
142.5°	391.5	391.2	390.9	390.6
145°	404.1	403.9	403.6	403.4
147.5°	414.9	414.4	413.9	413.4
150°	425.4	425.1	424.8	424.5
152.5°	434.5	434.2	434.0	433.8
155°	442.6	442.5	442.4	442.3
157.5°	449.8	449.8	449.8	449.8
160°	455.6	455.8	456.1	456.3
162.5°	461.0	461.3	461.7	462.0
165°	465.4	465.8	466.2	466.6
167.5°	469.4	469.7	470.1	470.5
170°	472.3	472.8	473.3	473.8
172.5°	474.5	475.0	475.4	475.9
175°	475.9	476.4	476.8	477.3
177.5°	476.7	477.3	477.8	478.4
180°	477.3	477.3	477.3	477.3

(END OF REPORT)