

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012964

Luminaire Tested: S124DIP-B1195D590UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012964
REPORT IS A COMBINATION OF REPORTS P995614 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D590UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7237.9 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 76.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012964

CATALOG NUMBER: S124DIP-B1195D590UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1012964

CATALOG NUMBER: S124DIP-B1195D590UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	62
1	99	94	90	86	93	88	84	81	77	74	72	67	65	63	58	56	54	54	54	50
2	90	82	75	69	84	77	71	65	67	62	58	58	55	51	50	47	45	45	45	41
3	82	71	63	57	76	67	60	54	59	53	48	51	47	43	44	40	38	38	38	34
4	75	63	54	48	69	59	51	46	52	46	41	45	40	36	39	35	32	32	32	29
5	68	56	47	41	64	53	45	39	46	40	35	40	35	31	35	31	28	28	28	25
6	63	50	41	35	59	47	39	34	42	35	30	36	31	27	32	27	24	24	24	21
7	58	45	37	31	54	43	35	29	38	31	27	33	28	24	29	25	21	21	21	19
8	54	41	33	27	50	39	31	26	34	28	24	30	25	21	26	22	19	19	19	17
9	50	37	30	24	47	35	28	23	31	25	21	28	23	19	24	20	17	17	17	15
10	47	34	27	22	44	33	26	21	29	23	19	26	21	17	23	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11653	11653	11653
5°	11685	11349	11370
10°	11609	11126	11094
15°	11501	10875	10783
20°	11339	10603	10481
25°	11158	10303	10156
30°	10962	10006	9823
35°	10739	9702	9528
40°	10561	9411	9221
45°	10298	9137	8950
50°	10073	8827	8665
55°	9841	8527	8336
60°	9481	8155	8027
65°	9085	7753	7654
70°	8605	7294	7225
75°	7931	6784	6815
80°	7173	6263	6384
85°	6171	5740	6037

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10298 cd/sqm

TEST NUMBER: P1012964

CATALOG NUMBER: S124DIP-B1195D590UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	135.4	1.9
10°-20°	387.9	5.4
20°-30°	586.6	8.1
30°-40°	709.6	9.8
40°-50°	750.2	10.4
50°-60°	706.0	9.8
60°-70°	585.9	8.1
70°-80°	411.1	5.7
80°-90°	233.3	3.2
90°-100°	163.3	2.3
100°-110°	269.2	3.7
110°-120°	387.5	5.4
120°-130°	443.5	6.1
130°-140°	449.9	6.2
140°-150°	408.3	5.6
150°-160°	326.7	4.5
160°-170°	210.7	2.9
170°-180°	72.6	1.0
0°-30°	1109.9	15.3
0°-40°	1819.6	25.1
0°-60°	3275.8	45.3
0°-90°	4506.2	62.3
90°-120°	820.1	11.3
90°-150°	2121.8	29.3
90°-180°	2732.0	37.7
0°-180°	7237.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1429	1429	1429	1429	1429	
5°	1431	1426	1415	1427	1426	136
15°	1371	1373	1368	1383	1381	386
25°	1255	1264	1269	1287	1288	578
35°	1098	1117	1133	1155	1160	687
45°	915	946	976	1003	1011	707
55°	717	750	798	830	840	639
65°	496	547	602	642	654	492
75°	275	334	402	446	461	292
85°	85	152	224	272	288	88
90°	27	98	171	221	235	19
95°	52	86	152	198	213	55
105°	186	222	284	329	321	196
115°	331	347	398	434	445	326
125°	458	459	497	530	540	409
135°	563	563	576	603	614	435
145°	647	648	648	658	665	405
155°	708	709	707	709	708	327
165°	747	744	744	749	744	211
175°	764	761	761	766	760	73
180°	764	764	764	764	764	

TEST NUMBER: P1012964

CATALOG NUMBER: S124DIP-B1195D590UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1429.0	1429.0	1429.0	1429.0	1429.0
2.5°	1435.4	1430.6	1417.8	1429.0	1427.4
5°	1430.6	1425.8	1414.6	1427.4	1425.8
7.5°	1421.0	1417.8	1408.2	1422.6	1421.0
10°	1408.2	1406.6	1398.6	1413.0	1411.4
12.5°	1390.6	1390.6	1385.8	1398.6	1398.6
15°	1371.4	1373.0	1368.2	1382.6	1381.0
17.5°	1345.8	1350.6	1349.0	1363.4	1361.8
20°	1318.6	1323.4	1325.0	1341.0	1341.0
22.5°	1288.2	1294.6	1297.8	1313.8	1317.0
25°	1254.6	1264.2	1269.0	1286.6	1288.2
27.5°	1217.8	1232.2	1238.6	1254.6	1256.2
30°	1181.0	1193.8	1205.0	1222.6	1225.8
32.5°	1140.9	1157.0	1169.8	1190.6	1193.8
35°	1097.7	1116.9	1132.9	1155.4	1160.2
37.5°	1054.5	1076.9	1096.1	1118.5	1123.3
40°	1012.9	1033.7	1056.1	1080.1	1086.5
42.5°	964.9	988.9	1016.1	1043.3	1048.1
45°	915.3	945.7	976.1	1003.3	1011.3
47.5°	868.9	899.3	934.5	961.7	971.3
50°	817.7	852.9	888.1	920.1	929.7
52.5°	766.5	801.7	843.3	875.3	884.9
55°	716.9	750.5	798.5	830.5	840.1
57.5°	660.9	702.5	748.9	787.3	795.3
60°	606.5	648.1	700.9	737.7	750.5
62.5°	553.7	600.1	652.9	689.7	702.5
65°	496.1	547.3	601.7	641.7	654.5
67.5°	441.7	496.1	553.7	593.7	606.5
70°	385.7	440.1	500.9	544.1	555.3
72.5°	331.2	387.3	452.9	494.5	507.3
75°	275.2	334.4	401.7	446.5	460.9
77.5°	222.4	284.8	355.2	400.1	416.1
80°	174.4	238.4	308.8	356.8	369.6
82.5°	126.4	193.6	264.0	313.6	328.0
85°	84.8	152.0	224.0	272.0	288.0
87.5°	52.8	118.4	188.8	235.2	249.6
90°	27.3	97.6	171.0	220.8	234.7
92.5°	32.6	87.4	160.8	209.0	221.8
95°	52.2	85.6	151.8	198.4	213.4
97.5°	79.2	138.2	143.8	188.2	203.2
100°	111.3	163.2	146.7	180.2	192.0
102.5°	149.0	191.1	258.8	171.8	184.6
105°	186.4	221.9	283.9	329.1	321.3
107.5°	223.6	252.5	312.5	355.3	368.8
110°	259.7	283.8	343.2	381.2	395.7



TEST NUMBER: P1012964

CATALOG NUMBER: S124DIP-B1195D590UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	294.7	317.3	371.2	405.9	421.0
115°	330.8	346.9	397.5	433.9	445.1
117.5°	364.5	376.4	426.1	459.1	471.9
120°	397.2	404.3	450.1	483.3	494.9
122.5°	429.2	430.3	474.7	507.3	517.3
125°	457.9	458.6	497.4	529.6	539.7
127.5°	487.0	486.0	520.9	549.1	559.7
130°	513.4	512.4	539.7	569.1	578.7
132.5°	539.2	538.7	560.2	588.0	597.0
135°	563.3	562.7	576.2	602.9	613.7
137.5°	586.1	584.5	593.8	618.9	626.4
140°	608.4	608.0	610.7	633.2	641.8
142.5°	626.8	629.1	628.1	646.8	653.2
145°	647.4	647.5	647.5	657.7	665.2
147.5°	663.4	665.2	664.7	666.8	673.8
150°	681.1	681.8	681.2	681.2	681.8
152.5°	694.4	696.1	695.0	696.1	695.5
155°	708.1	708.7	707.0	709.2	707.5
157.5°	720.1	720.1	717.8	720.7	717.8
160°	730.4	728.7	728.1	731.5	728.1
162.5°	739.5	737.2	736.7	740.1	736.1
165°	747.0	744.1	744.1	748.7	743.5
167.5°	753.3	750.4	749.8	755.0	749.2
170°	758.4	755.0	755.5	760.1	754.4
172.5°	761.8	758.4	759.0	763.5	757.3
175°	764.1	760.7	761.3	766.4	759.5
177.5°	765.8	761.8	763.0	767.5	760.7
180°	764.1	764.1	764.1	764.1	764.1

(END OF REPORT)