

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012981

Luminaire Tested: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012981
REPORT IS A COMBINATION OF REPORTS P995676 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7988.0 lumens
Efficiency: N/A
Efficacy: 96.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 82.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012981

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1012981

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	56		
1	98	93	89	85	91	87	83	79	74	72	69	63	61	59	53	51	50	45		
2	89	81	74	68	82	75	69	64	65	60	56	55	51	48	46	43	41	37		
3	81	71	63	56	75	66	59	53	57	51	47	48	44	40	40	37	34	31		
4	74	62	54	47	68	58	50	45	50	44	39	43	38	34	36	32	29	26		
5	68	55	47	40	62	52	44	38	45	38	34	38	33	30	32	28	25	22		
6	62	49	41	35	57	46	39	33	40	34	29	34	29	26	29	25	22	19		
7	57	45	36	30	53	42	34	29	36	30	26	31	26	23	26	23	20	17		
8	53	40	32	27	49	38	31	26	33	27	23	28	24	20	24	20	17	15		
9	50	37	29	24	46	35	28	23	30	24	20	26	21	18	22	19	16	14		
10	46	34	26	21	43	32	25	20	28	22	18	24	20	16	21	17	14	12		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11588	11588	11588
5°	11620	11286	11307
10°	11545	11064	11033
15°	11437	10814	10723
20°	11277	10544	10422
25°	11096	10246	10099
30°	10901	9951	9769
35°	10681	9649	9474
40°	10502	9359	9170
45°	10241	9087	8901
50°	10018	8778	8617
55°	9786	8480	8290
60°	9428	8109	7982
65°	9034	7709	7612
70°	8556	7253	7184
75°	7887	6745	6776
80°	7136	6228	6350
85°	6134	5709	6003

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10241 cd/sqm

TEST NUMBER: P1012981

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	134.6	1.7
10°-20°	385.8	4.8
20°-30°	583.3	7.3
30°-40°	705.7	8.8
40°-50°	746.0	9.3
50°-60°	702.1	8.8
60°-70°	582.6	7.3
70°-80°	408.9	5.1
80°-90°	232.6	2.9
90°-100°	170.9	2.1
100°-110°	323.5	4.0
110°-120°	491.9	6.2
120°-130°	576.3	7.2
130°-140°	592.0	7.4
140°-150°	541.4	6.8
150°-160°	433.9	5.4
160°-170°	279.8	3.5
170°-180°	96.4	1.2
0°-30°	1103.7	13.8
0°-40°	1809.5	22.7
0°-60°	3257.6	40.8
0°-90°	4481.7	56.1
90°-120°	986.3	12.3
90°-150°	2696.1	33.8
90°-180°	3506.0	43.9
0°-180°	7988.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1421	1421	1421	1421	1421	
5°	1423	1418	1407	1420	1418	135
15°	1364	1365	1361	1375	1373	384
25°	1248	1257	1262	1279	1281	575
35°	1092	1111	1127	1149	1154	684
45°	910	940	971	998	1006	704
55°	713	746	794	826	836	635
65°	493	544	598	638	651	489
75°	274	333	399	444	458	291
85°	84	151	223	270	286	88
90°	28	100	174	225	239	20
95°	62	89	155	203	218	68
105°	243	279	342	388	374	255
115°	436	453	503	540	551	430
125°	606	608	646	678	689	542
135°	747	746	761	788	799	576
145°	860	860	860	870	878	537
155°	941	941	939	942	940	434
165°	992	988	988	994	988	280
175°	1015	1010	1011	1018	1009	97
180°	1015	1015	1015	1015	1015	

TEST NUMBER: P1012981

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1421.1	1421.1	1421.1	1421.1	1421.1
2.5°	1427.4	1422.7	1409.9	1421.1	1419.5
5°	1422.7	1417.9	1406.7	1419.5	1417.9
7.5°	1413.1	1409.9	1400.4	1414.7	1413.1
10°	1400.4	1398.8	1390.8	1405.2	1403.6
12.5°	1382.9	1382.9	1378.1	1390.8	1390.8
15°	1363.8	1365.4	1360.6	1374.9	1373.3
17.5°	1338.3	1343.1	1341.5	1355.8	1354.2
20°	1311.3	1316.0	1317.6	1333.5	1333.5
22.5°	1281.0	1287.4	1290.6	1306.5	1309.7
25°	1247.6	1257.2	1261.9	1279.4	1281.0
27.5°	1211.0	1225.3	1231.7	1247.6	1249.2
30°	1174.4	1187.1	1198.3	1215.8	1219.0
32.5°	1134.6	1150.5	1163.3	1184.0	1187.1
35°	1091.7	1110.8	1126.7	1148.9	1153.7
37.5°	1048.7	1071.0	1090.1	1112.3	1117.1
40°	1007.3	1028.0	1050.3	1074.2	1080.5
42.5°	959.6	983.4	1010.5	1037.6	1042.3
45°	910.2	940.5	970.7	997.8	1005.7
47.5°	864.1	894.3	929.3	956.4	965.9
50°	813.2	848.2	883.2	915.0	924.6
52.5°	762.3	797.3	838.6	870.5	880.0
55°	712.9	746.3	794.1	825.9	835.5
57.5°	657.2	698.6	744.7	782.9	790.9
60°	603.1	644.5	697.0	733.6	746.3
62.5°	550.6	596.8	649.3	685.9	698.6
65°	493.3	544.2	598.3	638.1	650.9
67.5°	439.2	493.3	550.6	590.4	603.1
70°	383.5	437.6	498.1	541.1	552.2
72.5°	329.4	385.1	450.3	491.7	504.5
75°	273.7	332.6	399.4	444.0	458.3
77.5°	221.2	283.3	353.3	397.8	413.7
80°	173.5	237.1	307.1	354.9	367.6
82.5°	125.7	192.6	262.6	311.9	326.2
85°	84.3	151.2	222.8	270.5	286.4
87.5°	52.5	117.8	187.8	233.9	248.2
90°	27.8	99.7	174.2	225.0	239.2
92.5°	35.3	89.5	163.9	213.1	225.8
95°	62.5	89.1	155.1	202.7	217.7
97.5°	98.8	161.6	147.2	192.4	207.5
100°	142.0	197.1	154.3	184.4	196.3
102.5°	192.1	236.2	305.8	176.4	189.1
105°	242.8	279.2	341.9	388.5	373.9
107.5°	292.2	321.5	382.6	426.2	440.3
110°	340.7	365.2	425.5	463.6	478.6

TEST NUMBER: P1012981

CATALOG NUMBER: S124DIP-B1195D810UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	387.7	411.3	465.3	499.7	515.4
115°	436.2	452.8	503.0	539.5	550.6
117.5°	481.0	493.6	543.6	576.3	589.0
120°	525.0	532.7	578.2	611.5	622.7
122.5°	567.5	569.0	613.5	646.0	655.7
125°	606.2	607.6	645.9	678.4	688.6
127.5°	644.9	644.0	679.6	707.5	717.9
130°	680.5	679.6	707.3	736.8	746.3
132.5°	714.6	714.6	736.7	764.5	773.3
135°	747.2	746.5	760.6	787.6	798.6
137.5°	777.6	776.0	786.2	811.5	818.7
140°	807.2	807.1	810.2	833.2	841.9
142.5°	832.2	835.2	834.4	853.4	859.8
145°	859.5	860.2	860.2	870.4	878.3
147.5°	880.7	883.7	882.9	885.3	892.5
150°	904.3	905.7	905.0	905.0	905.7
152.5°	922.4	924.7	923.2	924.7	923.9
155°	940.6	941.4	939.1	942.2	939.9
157.5°	956.6	956.6	953.5	957.3	953.5
160°	970.3	968.0	967.2	971.8	967.2
162.5°	982.4	979.4	978.6	983.2	977.8
165°	992.3	988.5	988.5	994.5	987.7
167.5°	1000.6	996.8	996.1	1002.9	995.3
170°	1007.5	1002.9	1003.7	1009.7	1002.1
172.5°	1012.0	1007.5	1008.2	1014.3	1005.9
175°	1015.0	1010.5	1011.2	1018.1	1009.0
177.5°	1017.3	1012.0	1013.5	1019.6	1010.5
180°	1015.0	1015.0	1015.0	1015.0	1015.0

(END OF REPORT)