

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013022

Luminaire Tested: S124DIP-B350D365UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013022
REPORT IS A COMBINATION OF REPORTS P995853 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B350D365UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2850.0 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013022

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013022

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52			45
1	96	91	87	83	88	84	80	77	69	67	64	56	54	53	44	43	42			36
2	87	79	73	67	79	72	67	62	60	56	52	49	46	43	38	36	34			30
3	79	69	61	55	72	63	57	51	53	48	44	43	39	36	34	31	29			25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25			21
5	66	54	46	40	60	50	42	37	42	36	32	34	30	26	27	24	21			18
6	61	48	40	34	55	45	37	32	37	32	27	31	26	23	24	21	19			16
7	56	44	35	30	51	40	33	28	34	28	24	28	23	20	22	19	16			14
8	52	39	32	26	47	36	29	25	31	25	21	25	21	18	20	17	15			12
9	48	36	28	23	44	33	26	22	28	23	19	23	19	16	19	15	13			11
10	45	33	26	21	41	30	24	19	26	21	17	21	17	14	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3327	3327	3327
5°	3336	3240	3246
10°	3314	3176	3168
15°	3283	3105	3079
20°	3238	3027	2993
25°	3186	2942	2900
30°	3130	2857	2805
35°	3066	2770	2720
40°	3015	2687	2633
45°	2940	2609	2555
50°	2877	2520	2474
55°	2810	2435	2380
60°	2707	2328	2292
65°	2593	2214	2186
70°	2456	2082	2062
75°	2265	1937	1946
80°	2048	1789	1822
85°	1761	1640	1723

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2940 cd/sqm

TEST NUMBER: P1013022

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.7	1.4
10°-20°	110.8	3.9
20°-30°	167.5	5.9
30°-40°	202.6	7.1
40°-50°	214.2	7.5
50°-60°	201.6	7.1
60°-70°	167.3	5.9
70°-80°	117.4	4.1
80°-90°	67.2	2.4
90°-100°	55.0	1.9
100°-110°	132.2	4.6
110°-120°	216.3	7.6
120°-130°	260.7	9.1
130°-140°	271.9	9.5
140°-150°	250.7	8.8
150°-160°	201.4	7.1
160°-170°	129.9	4.6
170°-180°	44.8	1.6
0°-30°	316.9	11.1
0°-40°	519.5	18.2
0°-60°	935.3	32.8
0°-90°	1287.1	45.2
90°-120°	403.5	14.2
90°-150°	1186.8	41.6
90°-180°	1563.0	54.8
0°-180°	2850.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	408	408	408	408	408	
5°	408	407	404	408	407	39
15°	392	392	391	395	394	110
25°	358	361	362	367	368	165
35°	313	319	324	330	331	196
45°	261	270	279	286	289	202
55°	205	214	228	237	240	182
65°	142	156	172	183	187	140
75°	79	96	115	128	132	84
85°	24	43	64	78	82	25
90°	8	30	53	68	73	6
95°	25	28	48	62	66	29
105°	110	121	140	155	146	116
115°	201	206	220	231	234	198
125°	280	281	292	302	305	250
135°	346	346	350	358	362	267
145°	399	399	399	402	405	249
155°	437	437	436	437	436	201
165°	461	459	459	462	458	130
175°	471	469	469	473	468	45
180°	471	471	471	471	471	

TEST NUMBER: P1013022

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	408.0	408.0	408.0	408.0	408.0
2.5°	409.8	408.4	404.8	408.0	407.5
5°	408.4	407.1	403.9	407.5	407.1
7.5°	405.7	404.8	402.0	406.2	405.7
10°	402.0	401.6	399.3	403.4	403.0
12.5°	397.0	397.0	395.7	399.3	399.3
15°	391.5	392.0	390.6	394.7	394.3
17.5°	384.2	385.6	385.1	389.3	388.8
20°	376.5	377.8	378.3	382.9	382.9
22.5°	367.8	369.6	370.5	375.1	376.0
25°	358.2	360.9	362.3	367.3	367.8
27.5°	347.7	351.8	353.6	358.2	358.6
30°	337.2	340.8	344.0	349.1	350.0
32.5°	325.8	330.3	334.0	339.9	340.8
35°	313.4	318.9	323.5	329.9	331.2
37.5°	301.1	307.5	313.0	319.4	320.7
40°	289.2	295.1	301.5	308.4	310.2
42.5°	275.5	282.3	290.1	297.9	299.3
45°	261.3	270.0	278.7	286.5	288.7
47.5°	248.1	256.8	266.8	274.6	277.3
50°	233.5	243.5	253.6	262.7	265.4
52.5°	218.8	228.9	240.8	249.9	252.7
55°	204.7	214.3	228.0	237.1	239.9
57.5°	188.7	200.6	213.8	224.8	227.1
60°	173.2	185.0	200.1	210.6	214.3
62.5°	158.1	171.3	186.4	196.9	200.6
65°	141.6	156.3	171.8	183.2	186.9
67.5°	126.1	141.6	158.1	169.5	173.2
70°	110.1	125.6	143.0	155.3	158.5
72.5°	94.6	110.6	129.3	141.2	144.8
75°	78.6	95.5	114.7	127.5	131.6
77.5°	63.5	81.3	101.4	114.2	118.8
80°	49.8	68.1	88.2	101.9	105.5
82.5°	36.1	55.3	75.4	89.5	93.7
85°	24.2	43.4	64.0	77.7	82.2
87.5°	15.1	33.8	53.9	67.2	71.3
90°	8.4	30.5	53.0	68.4	72.7
92.5°	12.2	27.4	49.9	64.8	68.4
95°	25.3	28.4	47.5	62.0	66.4
97.5°	42.5	63.5	45.3	58.8	63.4
100°	62.8	81.0	50.2	56.6	60.2
102.5°	86.1	100.4	121.9	54.5	58.2
105°	110.2	121.4	140.2	154.7	145.6
107.5°	133.1	141.9	160.4	173.6	178.2
110°	155.9	163.4	181.4	192.6	197.4

TEST NUMBER: P1013022

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	178.0	185.6	201.4	211.1	216.2
115°	200.8	206.0	220.3	231.0	234.2
117.5°	221.6	225.8	240.5	249.8	253.4
120°	242.3	245.1	258.0	267.8	270.8
122.5°	262.0	262.7	275.7	285.3	287.8
125°	280.2	281.2	291.9	301.7	304.7
127.5°	298.2	298.1	309.0	316.8	319.7
130°	315.1	314.9	323.3	331.8	334.6
132.5°	330.9	331.1	338.0	346.2	348.5
135°	346.3	345.9	350.5	358.5	362.0
137.5°	360.4	360.0	363.5	371.0	373.0
140°	374.1	374.4	375.5	382.6	385.1
142.5°	386.1	387.5	387.3	393.0	394.9
145°	398.7	399.3	399.3	402.3	405.0
147.5°	408.6	410.2	409.9	410.7	412.9
150°	419.5	420.4	420.1	420.1	420.4
152.5°	428.2	429.3	428.5	429.3	428.9
155°	436.7	437.0	435.9	437.4	436.3
157.5°	444.1	444.1	442.6	444.4	442.6
160°	450.4	449.3	449.0	451.1	449.0
162.5°	456.0	454.6	454.3	456.4	453.9
165°	460.6	458.9	458.9	461.7	458.5
167.5°	464.5	462.7	462.4	465.6	462.0
170°	467.7	465.6	465.9	468.7	465.2
172.5°	469.8	467.7	468.0	470.8	467.0
175°	471.2	469.1	469.4	472.6	468.4
177.5°	472.2	469.8	470.5	473.3	469.1
180°	471.2	471.2	471.2	471.2	471.2

(END OF REPORT)