

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013023

Luminaire Tested: S124DIP-B350D365UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013023
REPORT IS A COMBINATION OF REPORTS P995854 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B350D365UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 2875.0 lumens
Efficiency: N/A
Efficacy: 128.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 22.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013023

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013023

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52			45
1	96	91	87	83	88	84	80	77	69	67	64	56	54	53	44	43	42			36
2	87	79	73	67	79	72	67	62	60	56	52	49	46	43	38	36	34			30
3	79	69	61	55	72	63	57	51	53	48	44	43	39	36	34	31	29			25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25			21
5	66	54	46	40	60	50	42	37	42	36	32	34	30	26	27	24	21			18
6	61	48	40	34	55	45	37	32	37	32	27	31	26	23	24	21	19			16
7	56	44	35	30	51	40	33	28	34	28	24	28	23	20	22	19	16			14
8	52	39	32	26	47	36	29	25	31	25	21	25	21	18	20	17	15			12
9	48	36	28	23	44	33	26	22	28	23	19	23	19	16	19	15	13			11
10	45	33	26	21	41	30	24	19	26	21	17	21	17	14	17	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3356	3356	3356
5°	3365	3268	3274
10°	3343	3204	3194
15°	3312	3132	3105
20°	3265	3054	3018
25°	3213	2967	2925
30°	3157	2881	2829
35°	3093	2794	2744
40°	3041	2710	2656
45°	2966	2631	2577
50°	2901	2542	2495
55°	2833	2455	2400
60°	2729	2348	2311
65°	2617	2233	2205
70°	2479	2100	2080
75°	2285	1954	1962
80°	2065	1803	1838
85°	1776	1653	1738

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2966 cd/sqm

TEST NUMBER: P1013023

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.0	1.4
10°-20°	111.7	3.9
20°-30°	168.9	5.9
30°-40°	204.4	7.1
40°-50°	216.0	7.5
50°-60°	203.3	7.1
60°-70°	168.7	5.9
70°-80°	118.4	4.1
80°-90°	67.7	2.4
90°-100°	55.5	1.9
100°-110°	133.3	4.6
110°-120°	218.2	7.6
120°-130°	263.1	9.1
130°-140°	274.3	9.5
140°-150°	253.0	8.8
150°-160°	203.2	7.1
160°-170°	131.1	4.6
170°-180°	45.2	1.6
0°-30°	319.6	11.1
0°-40°	524.0	18.2
0°-60°	943.3	32.8
0°-90°	1298.2	45.2
90°-120°	407.1	14.2
90°-150°	1197.4	41.6
90°-180°	1577.0	54.9
0°-180°	2875.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	412	412	412	412	412	
5°	412	411	407	411	411	39
15°	395	395	394	398	398	111
25°	361	364	365	370	371	166
35°	316	322	326	333	334	198
45°	264	272	281	289	291	204
55°	206	216	230	239	242	184
65°	143	158	173	185	188	142
75°	79	96	116	129	133	84
85°	24	44	64	78	83	25
90°	8	31	53	69	73	6
95°	26	29	48	62	67	29
105°	111	123	141	156	147	117
115°	203	208	222	233	236	200
125°	283	284	294	304	307	253
135°	349	349	354	362	365	269
145°	402	403	403	406	408	251
155°	440	441	440	441	440	203
165°	465	463	463	466	463	131
175°	475	473	474	477	472	45
180°	475	475	475	475	475	

TEST NUMBER: P1013023

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	411.5	411.5	411.5	411.5	411.5
2.5°	413.4	412.0	408.3	411.5	411.0
5°	412.0	410.6	407.4	411.0	410.6
7.5°	409.2	408.3	405.5	409.7	409.2
10°	405.5	405.1	402.8	406.9	406.4
12.5°	400.4	400.4	399.1	402.8	402.8
15°	394.9	395.4	394.0	398.1	397.7
17.5°	387.5	388.9	388.5	392.6	392.2
20°	379.7	381.1	381.6	386.2	386.2
22.5°	371.0	372.8	373.7	378.3	379.3
25°	361.3	364.0	365.4	370.5	371.0
27.5°	350.7	354.8	356.7	361.3	361.7
30°	340.1	343.8	347.0	352.1	353.0
32.5°	328.6	333.2	336.9	342.8	343.8
35°	316.1	321.6	326.3	332.7	334.1
37.5°	303.7	310.1	315.7	322.1	323.5
40°	291.7	297.7	304.1	311.1	312.9
42.5°	277.9	284.8	292.6	300.5	301.8
45°	263.6	272.3	281.1	288.9	291.2
47.5°	250.2	259.0	269.1	277.0	279.7
50°	235.5	245.6	255.8	265.0	267.7
52.5°	220.7	230.9	242.8	252.1	254.8
55°	206.4	216.1	229.9	239.2	241.9
57.5°	190.3	202.3	215.7	226.7	229.0
60°	174.6	186.6	201.8	212.4	216.1
62.5°	159.4	172.8	188.0	198.6	202.3
65°	142.9	157.6	173.3	184.8	188.5
67.5°	127.2	142.9	159.4	171.0	174.6
70°	111.1	126.7	144.2	156.7	159.9
72.5°	95.4	111.5	130.4	142.4	146.1
75°	79.3	96.3	115.7	128.6	132.7
77.5°	64.1	82.0	102.3	115.2	119.8
80°	50.2	68.7	88.9	102.8	106.4
82.5°	36.4	55.8	76.0	90.3	94.5
85°	24.4	43.8	64.5	78.3	82.9
87.5°	15.2	34.1	54.4	67.7	71.9
90°	8.5	30.8	53.4	69.0	73.4
92.5°	12.2	27.6	50.4	65.4	69.0
95°	25.6	28.7	47.9	62.5	67.0
97.5°	42.8	64.1	45.6	59.4	63.9
100°	63.4	81.8	50.6	57.1	60.7
102.5°	86.9	101.2	123.0	55.0	58.7
105°	111.1	122.6	141.3	156.0	146.9
107.5°	134.2	143.2	161.8	175.1	179.8
110°	157.3	164.8	183.1	194.4	199.2

TEST NUMBER: P1013023

CATALOG NUMBER: S124DIP-B350D365UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	179.6	187.3	203.2	212.9	218.1
115°	202.6	207.8	222.2	233.0	236.2
117.5°	223.6	227.7	242.7	251.9	255.6
120°	244.4	247.3	260.3	270.2	273.2
122.5°	264.4	265.1	278.2	287.8	290.3
125°	282.7	283.7	294.5	304.4	307.4
127.5°	300.8	300.8	311.8	319.7	322.6
130°	317.9	317.7	326.2	334.8	337.6
132.5°	333.9	334.1	341.1	349.2	351.7
135°	349.4	349.0	353.6	361.7	365.2
137.5°	363.6	363.2	366.8	374.4	376.3
140°	377.4	377.8	378.9	385.9	388.6
142.5°	389.5	390.9	390.8	396.6	398.4
145°	402.3	402.9	402.9	406.0	408.5
147.5°	412.2	413.9	413.5	414.4	416.5
150°	423.3	424.2	423.8	423.8	424.2
152.5°	432.0	433.1	432.4	433.1	432.7
155°	440.5	440.9	439.8	441.3	440.2
157.5°	448.0	448.0	446.6	448.4	446.6
160°	454.4	453.3	453.0	455.1	453.0
162.5°	460.1	458.7	458.3	460.5	458.0
165°	464.7	462.9	462.9	465.8	462.6
167.5°	468.6	466.9	466.5	469.7	466.1
170°	471.8	469.7	470.1	472.9	469.3
172.5°	474.0	471.8	472.2	475.0	471.1
175°	475.4	473.3	473.6	476.8	472.5
177.5°	476.5	474.0	474.7	477.5	473.3
180°	475.4	475.4	475.4	475.4	475.4

(END OF REPORT)