

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012562

Luminaire Tested: S123RDIP-B560D1025UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012562
REPORT IS A COMBINATION OF REPORTS P993339 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1025UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5613.0 lumens
Efficiency: N/A
Efficacy: 106.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 52.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012562

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012562

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	80	77	67	65	63	53	52	50	40	39	38
2	87	80	74	69	79	73	68	63	59	56	53	47	45	43	36	34	33
3	79	70	63	58	72	64	58	53	53	48	45	42	39	36	32	30	28
4	73	62	55	49	66	57	50	45	47	42	38	37	34	31	29	26	24
5	67	56	48	42	60	51	44	39	42	37	33	34	30	27	26	23	21
6	62	50	42	36	56	46	39	34	38	33	29	30	27	24	23	21	19
7	57	45	37	32	52	41	35	30	34	29	25	28	24	21	21	19	17
8	53	41	33	28	48	38	31	26	31	26	23	25	22	19	20	17	15
9	49	37	30	25	45	34	28	23	29	24	20	23	20	17	18	16	14
10	46	34	27	22	42	31	25	21	26	21	18	21	18	15	17	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1012562

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	1.6
10°-20°	246.0	4.4
20°-30°	354.2	6.3
30°-40°	398.8	7.1
40°-50°	381.5	6.8
50°-60°	312.3	5.6
60°-70°	210.6	3.8
70°-80°	105.6	1.9
80°-90°	30.3	0.5
90°-100°	81.0	1.4
100°-110°	245.1	4.4
110°-120°	417.2	7.4
120°-130°	548.9	9.8
130°-140°	617.0	11.0
140°-150°	606.5	10.8
150°-160°	510.6	9.1
160°-170°	340.0	6.1
170°-180°	119.0	2.1
0°-30°	688.6	12.3
0°-40°	1087.4	19.4
0°-60°	1781.2	31.7
0°-90°	2127.7	37.9
90°-120°	743.3	13.2
90°-150°	2515.7	44.8
90°-180°	3485.0	62.1
0°-180°	5613.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	11	24	28	30	7
95°	58	65	73	77	77	64
105°	222	224	233	233	235	238
115°	420	423	421	422	421	416
125°	615	618	616	612	608	548
135°	797	803	802	798	796	614
145°	967	969	972	971	967	604
155°	1108	1108	1109	1113	1106	510
165°	1206	1204	1204	1210	1202	340
175°	1255	1251	1251	1257	1250	119
180°	1258	1258	1258	1258	1258	

TEST NUMBER: P1012562

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	1.0	10.9	23.7	27.7	29.6
92.5°	29.6	35.6	41.5	44.5	42.5
95°	58.3	65.2	73.1	77.1	77.1
97.5°	95.8	100.8	106.7	111.7	110.7
100°	134.4	140.3	145.3	148.2	150.2
102.5°	178.8	181.8	188.7	191.7	190.7
105°	222.3	224.3	233.2	233.2	235.2
107.5°	273.7	274.7	278.6	281.6	280.6
110°	321.1	323.1	325.1	329.0	327.1

TEST NUMBER: P1012562

CATALOG NUMBER: S123RDIP-B560D1025UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.5	371.5	371.5	376.5	376.5
115°	420.0	422.9	420.9	421.9	420.9
117.5°	470.3	471.3	469.4	469.4	466.4
120°	516.8	522.7	517.8	516.8	514.8
122.5°	565.2	569.2	567.2	564.2	561.3
125°	614.6	617.6	615.6	611.6	607.7
127.5°	660.1	666.0	664.0	658.1	654.1
130°	705.5	713.4	710.5	706.5	699.6
132.5°	751.0	758.9	756.9	752.0	747.0
135°	797.4	803.3	802.4	798.4	796.4
137.5°	839.9	844.8	847.8	842.9	839.9
140°	884.4	889.3	890.3	889.3	882.4
142.5°	924.9	929.8	931.8	930.8	925.9
145°	967.4	969.3	972.3	971.3	967.4
147.5°	1003.9	1007.9	1010.8	1010.8	1004.9
150°	1042.5	1044.4	1046.4	1046.4	1040.5
152.5°	1074.1	1077.0	1078.0	1080.0	1075.1
155°	1107.7	1107.7	1108.7	1112.6	1105.7
157.5°	1136.3	1135.3	1136.3	1140.3	1134.4
160°	1163.0	1161.0	1161.0	1166.0	1162.0
162.5°	1186.7	1183.8	1184.8	1189.7	1182.8
165°	1206.5	1203.5	1203.5	1209.5	1202.5
167.5°	1223.3	1219.3	1220.3	1226.3	1220.3
170°	1237.1	1233.2	1233.2	1240.1	1233.2
172.5°	1248.0	1244.0	1244.0	1250.0	1243.1
175°	1254.9	1251.0	1251.0	1256.9	1250.0
177.5°	1258.9	1254.9	1254.9	1260.8	1253.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9

(END OF REPORT)