

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013052

Luminaire Tested: S124DIP-B350D810UB2750-4F0-XX-W2A-D_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013052
REPORT IS A COMBINATION OF REPORTS P995975 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B350D810UB2750-4F0-XX-W2A-D_3500K
Description: Define 4 Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721} {m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4584.0 lumens
Efficiency: N/A
Efficacy: 134.4 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 34.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013052

CATALOG NUMBER: S124DIP-B350D810UB2750-4F0-XX-W2A-D_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013052

CATALOG NUMBER: S124DIP-B350D810UB2750-4F0-XX-W2A-D_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36			28
1	92	88	84	80	82	79	75	72	62	59	57	46	44	43	31	30	29			23
2	84	76	70	65	75	68	63	59	54	50	47	40	37	35	27	26	24			19
3	76	67	60	54	68	60	54	49	47	43	39	35	32	30	24	22	20			15
4	70	59	51	45	62	53	46	41	42	37	33	31	28	25	21	19	17			13
5	64	52	44	38	57	47	40	35	37	32	28	28	24	22	19	17	15			11
6	59	47	39	33	52	42	35	30	33	28	24	25	21	19	17	15	13			10
7	54	42	34	29	48	38	31	26	30	25	21	22	19	16	16	13	12			9
8	50	38	30	25	44	34	28	23	27	22	19	20	17	14	14	12	10			8
9	46	34	27	22	41	31	25	20	25	20	17	19	15	13	13	11	9			7
10	43	31	24	20	39	28	22	18	23	18	15	17	14	12	12	10	8			6

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3370	3370	3370
5°	3379	3282	3288
10°	3358	3218	3209
15°	3326	3145	3119
20°	3279	3066	3031
25°	3227	2980	2937
30°	3170	2894	2841
35°	3106	2806	2755
40°	3054	2721	2667
45°	2978	2643	2589
50°	2913	2552	2506
55°	2846	2466	2411
60°	2742	2358	2321
65°	2628	2242	2214
70°	2488	2110	2089
75°	2294	1962	1971
80°	2073	1811	1847
85°	1783	1660	1746

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 90°

Luminance: 3164 cd/sqm

TEST NUMBER: P1013052

CATALOG NUMBER: S124DIP-B350D810UB2750-4F0-XX-W2A-D_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.2	0.9
10°-20°	112.2	2.4
20°-30°	169.6	3.7
30°-40°	205.2	4.5
40°-50°	217.0	4.7
50°-60°	204.2	4.5
60°-70°	169.4	3.7
70°-80°	118.9	2.6
80°-90°	69.2	1.5
90°-100°	73.9	1.6
100°-110°	253.7	5.5
110°-120°	447.9	9.8
120°-130°	554.6	12.1
130°-140°	586.1	12.8
140°-150°	544.5	11.9
150°-160°	438.3	9.6
160°-170°	282.7	6.2
170°-180°	97.4	2.1
0°-30°	321.0	7.0
0°-40°	526.2	11.5
0°-60°	947.4	20.7
0°-90°	1304.9	28.5
90°-120°	775.5	16.9
90°-150°	2460.7	53.7
90°-180°	3279.0	71.5
0°-180°	4584.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	413	413	413	413	413	
5°	414	412	409	413	412	39
15°	397	397	396	400	399	112
25°	363	366	367	372	372	167
35°	318	323	328	334	336	199
45°	265	274	282	290	292	205
55°	207	217	231	240	243	185
65°	144	158	174	186	189	142
75°	80	97	116	129	133	85
85°	24	44	65	79	83	26
90°	10	37	63	81	86	7
95°	48	37	57	74	79	57
105°	235	249	270	288	264	246
115°	434	440	454	466	469	427
125°	608	610	620	632	635	543
135°	752	752	758	767	771	580
145°	867	869	869	872	876	542
155°	950	951	949	952	950	438
165°	1002	998	998	1005	998	283
175°	1025	1021	1022	1028	1019	98
180°	1025	1025	1025	1025	1025	

TEST NUMBER: P1013052

CATALOG NUMBER: S124DIP-B350D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	413.3	413.3	413.3	413.3	413.3
2.5°	415.1	413.7	410.0	413.3	412.8
5°	413.7	412.3	409.1	412.8	412.3
7.5°	411.0	410.0	407.3	411.4	411.0
10°	407.3	406.8	404.5	408.6	408.2
12.5°	402.2	402.2	400.8	404.5	404.5
15°	396.6	397.1	395.7	399.8	399.4
17.5°	389.2	390.6	390.1	394.3	393.8
20°	381.3	382.7	383.2	387.8	387.8
22.5°	372.5	374.4	375.3	379.9	380.9
25°	362.8	365.6	367.0	372.1	372.5
27.5°	352.2	356.3	358.2	362.8	363.3
30°	341.5	345.2	348.5	353.6	354.5
32.5°	330.0	334.6	338.3	344.3	345.2
35°	317.5	323.0	327.7	334.1	335.5
37.5°	305.0	311.5	317.0	323.5	324.9
40°	292.9	299.0	305.4	312.4	314.2
42.5°	279.1	286.0	293.9	301.7	303.1
45°	264.7	273.5	282.3	290.2	292.5
47.5°	251.3	260.1	270.3	278.1	280.9
50°	236.5	246.7	256.8	266.1	268.9
52.5°	221.7	231.9	243.9	253.1	255.9
55°	207.3	217.0	230.9	240.2	243.0
57.5°	191.1	203.2	216.6	227.7	230.0
60°	175.4	187.4	202.7	213.3	217.0
62.5°	160.1	173.5	188.8	199.5	203.2
65°	143.5	158.3	174.0	185.6	189.3
67.5°	127.7	143.5	160.1	171.7	175.4
70°	111.5	127.3	144.9	157.3	160.6
72.5°	95.8	112.0	131.0	143.0	146.7
75°	79.6	96.7	116.2	129.1	133.3
77.5°	64.3	82.4	102.7	115.7	120.3
80°	50.4	69.0	89.3	103.2	106.9
82.5°	36.6	56.0	76.4	90.7	94.9
85°	24.5	44.0	64.8	78.7	83.3
87.5°	15.3	34.2	54.6	68.0	72.2
90°	9.7	36.6	62.7	80.7	85.9
92.5°	18.4	33.1	59.1	76.7	80.4
95°	48.2	37.4	57.2	74.3	79.1
97.5°	86.1	116.4	54.8	70.7	75.6
100°	130.9	156.7	68.9	68.4	72.4
102.5°	181.5	200.9	227.7	67.1	70.8
105°	235.0	248.8	269.8	288.3	264.4
107.5°	284.9	295.0	316.6	332.0	338.3
110°	335.0	343.8	364.6	376.7	382.7

TEST NUMBER: P1013052

CATALOG NUMBER: S124DIP-B350D810UB2750-4F0-XX-W2A-D_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	383.6	393.8	410.6	420.0	426.7
115°	433.8	440.2	454.3	466.0	469.3
117.5°	479.1	484.9	501.0	510.1	513.8
120°	524.6	529.0	541.7	552.5	554.7
122.5°	567.5	569.1	583.1	593.2	594.8
125°	607.8	610.3	620.4	631.5	635.0
127.5°	646.9	647.2	660.2	667.8	670.3
130°	684.0	684.2	693.9	703.1	705.8
132.5°	718.5	719.5	728.2	736.7	738.8
135°	752.5	751.7	758.1	767.0	771.3
137.5°	783.2	782.8	788.4	796.9	798.5
140°	813.1	814.2	816.1	824.4	827.6
142.5°	839.5	842.6	842.9	849.5	851.3
145°	867.1	868.9	868.9	872.5	875.8
147.5°	888.6	892.7	891.9	893.2	895.8
150°	912.4	914.9	914.2	914.2	914.9
152.5°	931.8	934.1	932.6	934.1	933.3
155°	950.2	951.0	948.7	951.8	949.5
157.5°	966.3	966.3	963.3	967.1	963.3
160°	980.1	977.8	977.1	981.7	977.1
162.5°	992.4	989.3	988.6	993.2	987.8
165°	1002.4	998.5	998.5	1004.7	997.8
167.5°	1010.8	1007.0	1006.2	1013.1	1005.4
170°	1017.7	1013.1	1013.9	1020.0	1012.3
172.5°	1022.3	1017.7	1018.5	1024.6	1016.2
175°	1025.4	1020.8	1021.5	1028.4	1019.2
177.5°	1027.7	1022.3	1023.8	1030.0	1020.8
180°	1025.4	1025.4	1025.4	1025.4	1025.4

(END OF REPORT)