

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012592

Luminaire Tested: S123RDIP-B560D1195UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012592
REPORT IS A COMBINATION OF REPORTS P993379 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6224.0 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012592

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012592

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	75	75	75	57	57	57	42	42	42
1	94	90	87	83	85	82	79	76	66	63	62	51	49	48	37	36	36
2	86	79	73	68	78	72	67	62	58	54	51	45	43	40	33	31	30
3	79	70	63	57	71	63	57	52	51	47	43	40	37	34	29	28	26
4	72	62	54	48	65	56	50	44	45	41	37	36	32	30	26	24	23
5	66	55	47	41	59	50	43	38	41	36	32	32	28	26	24	22	20
6	61	49	41	36	55	45	38	33	37	32	28	29	25	23	22	19	17
7	56	44	37	31	51	41	34	29	33	28	24	26	23	20	20	17	16
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	16	14
9	48	37	29	25	44	34	27	23	28	23	19	22	19	16	17	14	13
10	45	34	27	22	41	31	25	20	25	21	17	20	17	14	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1012592

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	1.4
10°-20°	246.0	4.0
20°-30°	354.2	5.7
30°-40°	398.8	6.4
40°-50°	381.5	6.1
50°-60°	312.3	5.0
60°-70°	210.6	3.4
70°-80°	105.6	1.7
80°-90°	30.7	0.5
90°-100°	95.2	1.5
100°-110°	288.0	4.6
110°-120°	490.3	7.9
120°-130°	645.0	10.4
130°-140°	725.0	11.6
140°-150°	712.8	11.5
150°-160°	600.1	9.6
160°-170°	399.5	6.4
170°-180°	139.9	2.2
0°-30°	688.6	11.1
0°-40°	1087.4	17.5
0°-60°	1781.2	28.6
0°-90°	2128.1	34.2
90°-120°	873.5	14.0
90°-150°	2956.4	47.5
90°-180°	4096.0	65.8
0°-180°	6224.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	13	28	32	35	8
95°	68	77	86	91	91	75
105°	261	264	274	274	276	280
115°	494	497	495	496	495	488
125°	722	726	723	719	714	644
135°	937	944	943	938	936	722
145°	1137	1139	1143	1142	1137	710
155°	1302	1302	1303	1308	1299	599
165°	1418	1414	1414	1421	1413	400
175°	1475	1470	1470	1477	1469	140
180°	1478	1478	1478	1478	1478	

TEST NUMBER: P1012592

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	1.2	12.8	27.9	32.5	34.8
92.5°	34.8	41.8	48.8	52.3	49.9
95°	68.5	76.6	85.9	90.6	90.6
97.5°	112.6	118.4	125.4	131.2	130.1
100°	157.9	164.9	170.7	174.2	176.5
102.5°	210.2	213.7	221.8	225.3	224.1
105°	261.3	263.6	274.0	274.0	276.4
107.5°	321.7	322.8	327.5	330.9	329.8
110°	377.4	379.7	382.0	386.7	384.4

TEST NUMBER: P1012592

CATALOG NUMBER: S123RDIP-B560D1195UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	435.5	436.6	436.6	442.4	442.4
115°	493.5	497.0	494.7	495.8	494.7
117.5°	552.7	553.9	551.6	551.6	548.1
120°	607.3	614.3	608.5	607.3	605.0
122.5°	664.2	668.9	666.5	663.1	659.6
125°	722.3	725.8	723.4	718.8	714.1
127.5°	775.7	782.7	780.3	773.4	768.7
130°	829.1	838.4	834.9	830.3	822.1
132.5°	882.5	891.8	889.5	883.7	877.9
135°	937.1	944.1	942.9	938.3	935.9
137.5°	987.0	992.8	996.3	990.5	987.0
140°	1039.3	1045.1	1046.2	1045.1	1037.0
142.5°	1086.9	1092.7	1095.0	1093.9	1088.1
145°	1136.8	1139.1	1142.6	1141.5	1136.8
147.5°	1179.8	1184.4	1187.9	1187.9	1180.9
150°	1225.1	1227.4	1229.7	1229.7	1222.8
152.5°	1262.2	1265.7	1266.9	1269.2	1263.4
155°	1301.7	1301.7	1302.9	1307.5	1299.4
157.5°	1335.4	1334.2	1335.4	1340.0	1333.1
160°	1366.7	1364.4	1364.4	1370.2	1365.6
162.5°	1394.6	1391.1	1392.3	1398.1	1390.0
165°	1417.8	1414.4	1414.4	1421.3	1413.2
167.5°	1437.6	1432.9	1434.1	1441.1	1434.1
170°	1453.8	1449.2	1449.2	1457.3	1449.2
172.5°	1466.6	1462.0	1462.0	1468.9	1460.8
175°	1474.7	1470.1	1470.1	1477.1	1468.9
177.5°	1479.4	1474.7	1474.7	1481.7	1473.6
180°	1478.2	1478.2	1478.2	1478.2	1478.2

(END OF REPORT)