

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012599

Luminaire Tested: S123RDIP-B560D1195UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012599
REPORT IS A COMBINATION OF REPORTS P993386 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB35-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6480.1 lumens
Efficiency: N/A
Efficacy: 109.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012599

CATALOG NUMBER: S123RDIP-B560D1195UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012599

CATALOG NUMBER: S123RDIP-B560D1195UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	50	49	47	36	35	35
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	32	31	29
3	78	69	62	57	70	63	57	52	51	46	43	39	36	34	29	27	25
4	72	61	54	48	64	56	49	44	45	40	37	35	32	29	26	24	22
5	66	55	47	41	59	50	43	38	40	35	32	31	28	25	23	21	19
6	61	49	41	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	44	37	31	50	40	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	28	47	37	30	25	30	25	21	24	20	17	18	15	14
9	48	37	29	24	44	33	27	23	27	23	19	22	18	16	16	14	12
10	45	33	26	22	41	31	24	20	25	20	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1012599

CATALOG NUMBER: S123RDIP-B560D1195UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	1.4
10°-20°	247.0	3.8
20°-30°	355.7	5.5
30°-40°	400.5	6.2
40°-50°	383.1	5.9
50°-60°	313.6	4.8
60°-70°	211.5	3.3
70°-80°	106.1	1.6
80°-90°	31.0	0.5
90°-100°	327.3	5.1
100°-110°	914.9	14.1
110°-120°	892.1	13.8
120°-130°	710.4	11.0
130°-140°	560.8	8.7
140°-150°	418.4	6.5
150°-160°	291.8	4.5
160°-170°	171.5	2.6
170°-180°	55.8	0.9
0°-30°	691.5	10.7
0°-40°	1092.0	16.9
0°-60°	1788.8	27.6
0°-90°	2137.2	33.0
90°-120°	2134.3	32.9
90°-150°	3823.8	59.0
90°-180°	4343.0	67.0
0°-180°	6480.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	2	14	29	33	34	6
95°	40	129	691	202	135	42
105°	135	200	938	1639	1483	144
115°	239	298	717	1572	1804	237
125°	332	392	669	1213	1422	295
135°	389	465	660	999	1153	301
145°	444	509	652	819	901	278
155°	505	545	631	717	747	232
165°	552	567	604	641	652	155
175°	575	575	580	588	586	55
180°	576	576	576	576	576	

TEST NUMBER: P1012599

CATALOG NUMBER: S123RDIP-B560D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	2.3	14.0	29.2	32.6	33.8
92.5°	17.5	70.0	216.9	74.0	61.8
95°	39.6	128.8	691.4	201.7	135.3
97.5°	63.0	147.5	1063.4	507.2	277.5
100°	86.3	162.6	1104.2	1061.1	731.1
102.5°	110.8	180.1	1028.4	1420.8	1157.9
105°	135.3	200.0	937.5	1639.4	1483.2
107.5°	160.9	223.3	857.0	1735.6	1695.4
110°	188.9	247.2	790.6	1738.5	1816.6

TEST NUMBER: P1012599

CATALOG NUMBER: S123RDIP-B560D1195UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	214.5	272.2	746.2	1672.6	1841.1
115°	239.0	298.0	717.1	1572.4	1803.8
117.5°	263.5	322.4	697.3	1465.1	1722.2
120°	289.2	346.9	684.4	1363.6	1614.9
122.5°	311.3	370.2	676.3	1283.8	1514.7
125°	332.3	392.4	669.3	1212.6	1422.5
127.5°	348.6	413.4	665.8	1154.4	1343.2
130°	363.8	432.0	662.3	1100.8	1278.0
132.5°	375.5	449.0	661.1	1050.6	1213.8
135°	389.4	464.6	660.0	998.7	1153.2
137.5°	402.3	477.5	657.6	949.8	1089.1
140°	415.1	489.2	656.5	901.9	1021.4
142.5°	429.1	499.6	654.1	858.2	958.5
145°	444.3	509.0	651.8	819.1	901.3
147.5°	459.4	518.8	648.3	788.8	852.4
150°	474.6	527.0	643.6	762.0	810.4
152.5°	489.7	535.8	637.8	738.6	775.4
155°	504.9	544.6	630.8	717.1	747.4
157.5°	516.5	552.1	625.0	696.1	720.6
160°	530.5	558.6	618.0	676.9	694.9
162.5°	541.0	563.2	611.0	658.8	671.6
165°	551.5	567.2	604.0	640.7	651.8
167.5°	559.7	570.8	597.0	625.0	632.0
170°	566.7	572.5	590.0	611.0	614.5
172.5°	571.3	574.2	584.2	598.8	598.2
175°	574.8	575.4	579.5	587.7	586.5
177.5°	577.2	576.0	576.0	580.7	578.3
180°	576.0	576.0	576.0	576.0	576.0

(END OF REPORT)