

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012603

Luminaire Tested: S123RDIP-B560D1195UB40-4F0-XX-W2A-F

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012603
REPORT IS A COMBINATION OF REPORTS P993390 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D1195UB40-4F0-XX-W2A-F
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6853.0 lumens
Efficiency: N/A
Efficacy: 116.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 59
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012603

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F

Luminous Intensity Polar Plot



TEST NUMBER: P1012603

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	39	39	39	31
1	94	90	86	83	84	81	78	75	64	62	60	49	47	46	34	34	33	33	33	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	28	28	28	22
3	78	69	62	57	70	62	56	52	50	46	42	38	35	33	27	25	24	24	24	24	19
4	71	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	21	21	21	17
5	65	54	47	41	59	49	43	38	40	35	31	30	27	25	22	20	18	18	18	18	15
6	60	49	41	35	54	44	37	33	36	31	27	28	24	21	20	18	16	16	16	16	13
7	56	44	36	31	50	40	33	29	32	27	24	25	22	19	18	16	14	14	14	14	11
8	52	40	32	27	46	36	30	25	29	24	21	23	19	17	17	15	13	13	13	13	10
9	48	36	29	24	43	33	27	22	27	22	19	21	18	15	16	13	12	12	12	12	9
10	45	33	26	22	40	30	24	20	25	20	17	19	16	14	14	12	11	11	11	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10067	10067	10067
5°	10084	9711	9685
10°	10005	9346	9162
15°	9875	8895	8589
20°	9704	8404	7949
25°	9529	7894	7342
30°	9303	7352	6625
35°	9071	6819	5972
40°	8853	6239	5251
45°	8574	5673	4603
50°	8264	5069	3932
55°	7944	4422	3316
60°	7639	3759	2691
65°	7242	3077	2100
70°	6747	2327	1501
75°	6029	1576	1190
80°	5147	1096	834
85°	3861	590	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8574 cd/sqm

TEST NUMBER: P1012603

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	1.3
10°-20°	244.6	3.6
20°-30°	352.2	5.1
30°-40°	396.6	5.8
40°-50°	379.4	5.5
50°-60°	310.5	4.5
60°-70°	209.4	3.1
70°-80°	105.0	1.5
80°-90°	30.6	0.4
90°-100°	54.8	0.8
100°-110°	264.9	3.9
110°-120°	649.2	9.5
120°-130°	824.1	12.0
130°-140°	880.4	12.8
140°-150°	823.3	12.0
150°-160°	664.0	9.7
160°-170°	428.5	6.3
170°-180°	147.7	2.2
0°-30°	684.7	10.0
0°-40°	1081.3	15.8
0°-60°	1771.2	25.8
0°-90°	2116.1	30.9
90°-120°	968.9	14.1
90°-150°	3496.7	51.0
90°-180°	4737.0	69.1
0°-180°	6853.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	935	935	935	935	935	
5°	935	932	922	929	928	89
15°	892	884	862	859	853	251
25°	812	793	758	742	734	373
35°	702	675	628	596	582	440
45°	577	543	485	442	423	445
55°	438	401	337	293	278	393
65°	300	258	199	162	153	297
75°	158	122	80	73	71	169
85°	40	24	21	20	20	44
90°	1	13	28	32	35	6
95°	70	23	36	44	44	84
105°	344	357	253	48	51	365
115°	645	652	663	674	679	637
125°	910	919	924	926	928	813
135°	1132	1139	1144	1148	1144	872
145°	1307	1315	1317	1320	1320	818
155°	1440	1437	1438	1444	1437	663
165°	1518	1515	1513	1523	1515	429
175°	1554	1548	1549	1557	1548	148
180°	1554	1554	1554	1554	1554	

TEST NUMBER: P1012603

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	935.3	935.3	935.3	935.3	935.3
2.5°	939.1	936.1	927.0	935.3	933.8
5°	935.3	931.5	922.4	929.2	927.7
7.5°	928.5	924.7	913.3	917.8	915.6
10°	919.4	914.1	900.4	901.2	897.4
12.5°	906.5	900.4	883.0	882.2	877.6
15°	892.1	883.7	862.5	858.7	853.4
17.5°	874.6	865.5	839.0	831.4	823.8
20°	854.9	842.8	813.9	804.1	795.0
22.5°	832.9	818.5	787.4	774.5	766.1
25°	811.7	792.7	757.8	741.9	733.5
27.5°	785.9	765.4	727.5	706.2	693.3
30°	759.3	736.6	694.1	668.3	656.1
32.5°	732.8	706.2	660.7	631.9	619.0
35°	702.4	675.1	628.1	595.5	581.8
37.5°	672.1	642.5	593.2	556.8	540.1
40°	643.3	609.9	556.0	516.6	499.1
42.5°	610.6	577.3	521.1	477.1	462.0
45°	577.3	543.1	484.7	441.5	423.3
47.5°	544.6	506.7	449.1	402.0	386.1
50°	508.2	472.6	411.1	364.1	346.7
52.5°	475.6	436.2	375.5	326.2	311.0
55°	438.4	401.3	336.8	292.8	277.6
57.5°	405.1	364.9	299.6	257.9	245.0
60°	370.2	328.5	265.5	224.5	211.6
62.5°	335.3	293.6	230.6	192.7	179.0
65°	299.6	257.9	198.7	161.6	153.2
67.5°	264.0	221.5	163.8	135.8	126.7
70°	229.1	188.1	135.0	108.5	100.1
72.5°	194.2	154.0	107.0	86.5	84.2
75°	158.5	122.1	80.4	72.8	71.3
77.5°	125.9	92.5	63.0	58.4	56.9
80°	94.8	63.7	47.8	45.5	44.0
82.5°	65.2	39.4	34.1	31.9	31.9
85°	40.2	23.5	21.2	19.7	19.7
87.5°	18.2	9.9	9.9	9.1	8.3
90°	1.2	12.7	27.7	32.3	34.6
92.5°	26.6	19.6	30.0	38.1	39.2
95°	70.4	23.1	35.8	43.9	43.9
97.5°	128.1	95.8	36.9	46.2	47.3
100°	195.1	218.2	38.1	47.3	48.5
102.5°	271.3	286.3	85.4	47.3	49.6
105°	344.0	356.7	252.8	48.5	50.8
107.5°	421.4	431.7	449.1	271.3	120.1
110°	498.7	507.9	520.6	482.5	317.5

TEST NUMBER: P1012603

CATALOG NUMBER: S123RDIP-B560D1195UB40-4F0-XX-W2A-F

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	572.6	580.7	593.4	603.7	601.4
115°	645.3	652.2	662.6	674.2	678.8
117.5°	716.9	725.0	730.7	740.0	741.1
120°	782.7	793.1	796.5	805.8	805.8
122.5°	849.6	857.7	862.3	868.1	869.3
125°	909.7	918.9	923.5	925.8	928.1
127.5°	969.7	978.9	984.7	988.2	985.8
130°	1025.1	1034.3	1038.9	1043.6	1041.3
132.5°	1078.2	1087.4	1090.9	1095.5	1092.0
135°	1132.5	1139.4	1144.0	1147.5	1144.0
137.5°	1178.6	1187.9	1190.2	1195.9	1193.6
140°	1224.8	1231.7	1235.2	1239.8	1237.5
142.5°	1267.5	1274.4	1277.9	1281.4	1277.9
145°	1306.8	1314.8	1317.2	1319.5	1319.5
147.5°	1344.9	1350.6	1352.9	1355.2	1349.5
150°	1379.5	1383.0	1385.3	1387.6	1384.1
152.5°	1410.7	1411.8	1413.0	1417.6	1411.8
155°	1439.5	1437.2	1438.4	1444.1	1437.2
157.5°	1462.6	1462.6	1461.5	1468.4	1459.1
160°	1483.4	1482.2	1481.1	1488.0	1479.9
162.5°	1503.0	1499.5	1498.4	1506.5	1499.5
165°	1518.0	1514.6	1513.4	1522.6	1514.6
167.5°	1530.7	1526.1	1526.1	1535.3	1526.1
170°	1541.1	1536.5	1536.5	1545.7	1536.5
172.5°	1548.0	1542.3	1543.4	1552.6	1542.3
175°	1553.8	1548.0	1549.2	1557.3	1548.0
177.5°	1556.1	1550.3	1551.5	1560.7	1549.2
180°	1553.8	1553.8	1553.8	1553.8	1553.8

(END OF REPORT)