

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013108

Luminaire Tested: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013108
REPORT IS A COMBINATION OF REPORTS P996214 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4725.0 lumens
Efficiency: N/A
Efficacy: 119.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013108

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013108

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	81	81	81	66	66	66	53	53	53			46
1	96	91	87	83	88	84	80	77	70	67	65	57	55	53	45	44	43			37
2	87	79	73	67	79	73	67	62	61	56	53	49	46	44	39	37	35			30
3	79	69	62	55	72	64	57	52	53	48	44	43	40	37	34	32	29			25
4	72	61	53	47	66	56	49	43	47	41	37	38	34	31	30	27	25			21
5	66	54	46	40	60	50	43	37	42	36	32	34	30	27	27	24	22			18
6	61	48	40	34	55	45	37	32	38	32	28	31	27	23	25	21	19			16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	20	22	19	17			14
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	17	15			12
9	48	36	28	23	44	33	27	22	28	23	19	23	19	16	19	16	13			11
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	14	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5642	5642	5642
5°	5658	5495	5505
10°	5621	5387	5372
15°	5568	5266	5221
20°	5490	5133	5075
25°	5403	4988	4917
30°	5307	4845	4756
35°	5200	4698	4613
40°	5114	4557	4465
45°	4986	4424	4334
50°	4877	4274	4196
55°	4765	4129	4037
60°	4591	3949	3887
65°	4399	3754	3706
70°	4165	3531	3498
75°	3841	3285	3299
80°	3475	3032	3092
85°	2991	2780	2924

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4986 cd/sqm

TEST NUMBER: P1013108

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.6	1.4
10°-20°	187.8	4.0
20°-30°	284.0	6.0
30°-40°	343.6	7.3
40°-50°	363.2	7.7
50°-60°	341.9	7.2
60°-70°	283.7	6.0
70°-80°	199.1	4.2
80°-90°	113.8	2.4
90°-100°	92.2	2.0
100°-110°	216.5	4.6
110°-120°	352.2	7.5
120°-130°	423.6	9.0
130°-140°	441.2	9.3
140°-150°	406.6	8.6
150°-160°	326.6	6.9
160°-170°	210.7	4.5
170°-180°	72.6	1.5
0°-30°	537.4	11.4
0°-40°	881.0	18.6
0°-60°	1586.1	33.6
0°-90°	2182.7	46.2
90°-120°	660.9	14.0
90°-150°	1932.4	40.9
90°-180°	2542.0	53.8
0°-180°	4725.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	692	692	692	692	692	
5°	693	690	685	691	690	66
15°	664	665	662	669	669	187
25°	608	612	614	623	624	280
35°	532	541	549	559	562	333
45°	443	458	473	486	490	343
55°	347	363	387	402	407	309
65°	240	265	291	311	317	238
75°	133	162	194	216	223	142
85°	41	74	108	132	140	43
90°	14	51	89	115	122	10
95°	42	48	80	104	112	47
105°	179	198	229	254	240	188
115°	326	334	359	377	382	321
125°	455	456	474	491	496	406
135°	562	561	569	582	588	433
145°	647	648	648	653	657	404
155°	708	709	707	709	708	327
165°	747	744	744	749	744	211
175°	764	761	761	766	760	73
180°	764	764	764	764	764	

TEST NUMBER: P1013108

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	691.9	691.9	691.9	691.9	691.9
2.5°	695.0	692.7	686.5	691.9	691.1
5°	692.7	690.4	684.9	691.1	690.4
7.5°	688.0	686.5	681.8	688.8	688.0
10°	681.8	681.1	677.2	684.2	683.4
12.5°	673.3	673.3	671.0	677.2	677.2
15°	664.0	664.8	662.5	669.4	668.7
17.5°	651.6	653.9	653.2	660.1	659.4
20°	638.4	640.8	641.5	649.3	649.3
22.5°	623.7	626.8	628.4	636.1	637.7
25°	607.5	612.1	614.4	623.0	623.7
27.5°	589.6	596.6	599.7	607.5	608.2
30°	571.8	578.0	583.4	592.0	593.5
32.5°	552.4	560.2	566.4	576.5	578.0
35°	531.5	540.8	548.6	559.4	561.7
37.5°	510.6	521.4	530.7	541.6	543.9
40°	490.5	500.5	511.4	523.0	526.1
42.5°	467.2	478.8	492.0	505.2	507.5
45°	443.2	457.9	472.6	485.8	489.7
47.5°	420.7	435.4	452.5	465.7	470.3
50°	395.9	413.0	430.0	445.5	450.2
52.5°	371.1	388.2	408.3	423.8	428.5
55°	347.1	363.4	386.6	402.1	406.8
57.5°	320.0	340.1	362.6	381.2	385.1
60°	293.7	313.8	339.4	357.2	363.4
62.5°	268.1	290.6	316.1	333.9	340.1
65°	240.2	265.0	291.3	310.7	316.9
67.5°	213.8	240.2	268.1	287.5	293.7
70°	186.7	213.1	242.5	263.4	268.9
72.5°	160.4	187.5	219.3	239.4	245.6
75°	133.3	161.9	194.5	216.2	223.1
77.5°	107.7	137.9	172.0	193.7	201.5
80°	84.5	115.4	149.5	172.8	179.0
82.5°	61.2	93.8	127.8	151.9	158.8
85°	41.1	73.6	108.5	131.7	139.5
87.5°	25.6	57.3	91.4	113.9	120.9
90°	14.1	51.4	89.3	115.2	122.5
92.5°	20.2	46.1	84.1	109.2	115.4
95°	41.5	47.6	80.0	104.3	111.9
97.5°	69.3	104.4	76.1	99.1	106.7
100°	102.2	132.7	84.0	95.2	101.2
102.5°	139.9	163.9	200.2	91.8	98.0
105°	179.0	198.0	229.4	254.0	239.6
107.5°	216.2	231.0	262.2	284.3	292.1
110°	253.1	265.6	296.2	315.2	323.1

TEST NUMBER: P1013108

CATALOG NUMBER: S124DIP-B575D590UB2750-4F0-XX-W2A-D_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.9	301.6	328.3	344.8	353.3
115°	325.8	334.5	358.7	377.0	382.4
117.5°	359.5	366.5	391.4	407.1	413.3
120°	393.1	397.7	419.6	436.3	441.3
122.5°	425.1	426.2	448.3	464.4	468.6
125°	454.6	456.1	474.3	490.8	496.0
127.5°	483.7	483.5	501.9	515.3	520.1
130°	510.9	510.7	524.8	539.4	544.0
132.5°	536.7	537.0	548.6	562.4	566.5
135°	561.6	561.0	568.8	582.3	588.1
137.5°	584.4	583.7	589.7	602.4	605.8
140°	606.7	607.2	609.0	620.8	625.3
142.5°	626.0	628.3	628.1	637.7	640.8
145°	646.6	647.5	647.5	652.7	656.9
147.5°	662.6	665.2	664.7	666.0	669.7
150°	680.3	681.8	681.2	681.2	681.8
152.5°	694.4	696.1	695.0	696.1	695.5
155°	708.1	708.7	707.0	709.2	707.5
157.5°	720.1	720.1	717.8	720.7	717.8
160°	730.4	728.7	728.1	731.5	728.1
162.5°	739.5	737.2	736.7	740.1	736.1
165°	747.0	744.1	744.1	748.7	743.5
167.5°	753.3	750.4	749.8	755.0	749.2
170°	758.4	755.0	755.5	760.1	754.4
172.5°	761.8	758.4	759.0	763.5	757.3
175°	764.1	760.7	761.3	766.4	759.5
177.5°	765.8	761.8	763.0	767.5	760.7
180°	764.1	764.1	764.1	764.1	764.1

(END OF REPORT)