

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013125

Luminaire Tested: S124DIP-B575D810UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013125
REPORT IS A COMBINATION OF REPORTS P996276 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D810UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5489.0 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013125

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013125

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	105	105	105	105	95	95	95	95	78	78	78	61	61	61	47	47	47			40
1	95	90	86	82	86	82	78	75	67	64	62	53	51	49	40	39	38			32
2	86	78	72	66	78	71	66	61	58	54	51	46	43	41	35	33	31			26
3	78	68	61	55	71	62	56	51	51	46	42	40	37	34	30	28	26			22
4	71	60	52	46	64	55	48	43	45	40	36	36	32	29	27	24	22			18
5	65	53	45	39	59	49	42	36	40	35	30	32	28	25	24	21	19			16
6	60	48	40	34	54	44	36	31	36	30	26	29	25	21	22	19	17			14
7	55	43	35	29	50	39	32	27	32	27	23	26	22	19	20	17	15			12
8	51	39	31	26	46	36	29	24	29	24	20	24	20	17	18	15	13			11
9	48	35	28	23	43	33	26	21	27	22	18	22	18	15	17	14	12			10
10	44	32	25	20	40	30	23	19	25	20	16	20	16	13	16	13	11			9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5611	5611	5611
5°	5627	5465	5475
10°	5590	5358	5342
15°	5538	5236	5192
20°	5460	5105	5047
25°	5373	4961	4890
30°	5279	4818	4730
35°	5172	4672	4587
40°	5086	4532	4440
45°	4959	4400	4310
50°	4850	4251	4173
55°	4738	4106	4014
60°	4565	3927	3865
65°	4375	3733	3686
70°	4143	3512	3479
75°	3818	3266	3281
80°	3455	3016	3075
85°	2969	2765	2907

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4959 cd/sqm

TEST NUMBER: P1013125

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.2	1.2
10°-20°	186.8	3.4
20°-30°	282.4	5.1
30°-40°	341.7	6.2
40°-50°	361.2	6.6
50°-60°	340.0	6.2
60°-70°	282.1	5.1
70°-80°	198.0	3.6
80°-90°	113.7	2.1
90°-100°	100.1	1.8
100°-110°	271.1	4.9
110°-120°	456.7	8.3
120°-130°	556.5	10.1
130°-140°	583.5	10.6
140°-150°	539.7	9.8
150°-160°	433.9	7.9
160°-170°	279.8	5.1
170°-180°	96.4	1.8
0°-30°	534.4	9.7
0°-40°	876.2	16.0
0°-60°	1577.4	28.7
0°-90°	2171.2	39.6
90°-120°	828.0	15.1
90°-150°	2507.6	45.7
90°-180°	3318.0	60.4
0°-180°	5489.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	688	688	688	688	688	
5°	689	687	681	687	687	65
15°	660	661	659	666	665	186
25°	604	609	611	620	620	278
35°	529	538	546	556	559	331
45°	441	455	470	483	487	341
55°	345	361	384	400	404	308
65°	239	264	290	309	315	237
75°	132	161	193	215	222	141
85°	41	73	108	131	139	43
90°	15	54	93	120	128	11
95°	52	51	84	109	117	59
105°	235	255	288	314	293	247
115°	431	440	464	483	488	425
125°	603	605	623	640	645	539
135°	746	745	753	767	773	575
145°	859	860	860	866	870	537
155°	941	941	939	942	940	434
165°	992	988	988	994	988	280
175°	1015	1010	1011	1018	1009	97
180°	1015	1015	1015	1015	1015	

TEST NUMBER: P1013125

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	688.1	688.1	688.1	688.1	688.1
2.5°	691.2	688.9	682.7	688.1	687.3
5°	688.9	686.6	681.2	687.3	686.6
7.5°	684.2	682.7	678.1	685.0	684.2
10°	678.1	677.3	673.5	680.4	679.6
12.5°	669.6	669.6	667.3	673.5	673.5
15°	660.4	661.1	658.8	665.7	665.0
17.5°	648.0	650.3	649.6	656.5	655.7
20°	634.9	637.2	638.0	645.7	645.7
22.5°	620.3	623.4	624.9	632.6	634.2
25°	604.1	608.7	611.0	619.5	620.3
27.5°	586.4	593.3	596.4	604.1	604.9
30°	568.7	574.8	580.2	588.7	590.2
32.5°	549.4	557.1	563.3	573.3	574.8
35°	528.6	537.8	545.5	556.3	558.6
37.5°	507.8	518.6	527.8	538.6	540.9
40°	487.8	497.8	508.6	520.1	523.2
42.5°	464.6	476.2	489.3	502.4	504.7
45°	440.8	455.4	470.0	483.1	487.0
47.5°	418.4	433.0	450.0	463.1	467.7
50°	393.7	410.7	427.7	443.1	447.7
52.5°	369.1	386.0	406.1	421.5	426.1
55°	345.2	361.4	384.5	399.9	404.5
57.5°	318.2	338.3	360.6	379.1	383.0
60°	292.0	312.1	337.5	355.2	361.4
62.5°	266.6	289.0	314.4	332.1	338.3
65°	238.9	263.5	289.7	309.0	315.2
67.5°	212.7	238.9	266.6	285.9	292.0
70°	185.7	211.9	241.2	262.0	267.4
72.5°	159.5	186.5	218.1	238.1	244.3
75°	132.5	161.0	193.4	215.0	221.9
77.5°	107.1	137.2	171.1	192.6	200.3
80°	84.0	114.8	148.7	171.8	178.0
82.5°	60.9	93.2	127.1	151.0	158.0
85°	40.8	73.2	107.9	131.0	138.7
87.5°	25.4	57.0	90.9	113.3	120.2
90°	14.6	53.8	93.0	119.9	127.6
92.5°	23.0	48.4	87.6	113.7	119.9
95°	51.8	51.3	83.7	109.1	116.8
97.5°	88.9	128.0	79.9	103.7	111.5
100°	133.0	166.7	92.0	99.9	106.1
102.5°	183.1	209.1	247.5	96.7	102.9
105°	235.4	255.4	287.8	313.8	292.7
107.5°	284.8	300.1	332.5	355.6	364.0
110°	334.2	347.2	378.7	397.9	406.4

TEST NUMBER: P1013125

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	382.0	395.7	422.7	438.9	448.1
115°	431.3	440.5	464.4	482.9	488.3
117.5°	476.1	483.7	509.2	524.5	530.7
120°	520.9	526.2	547.8	564.7	569.4
122.5°	563.4	564.9	587.3	603.4	607.3
125°	602.9	605.1	622.9	639.8	645.1
127.5°	641.6	641.5	660.7	673.9	678.5
130°	678.0	677.9	692.6	707.2	711.9
132.5°	712.1	712.9	725.2	739.1	742.9
135°	745.5	744.8	753.2	767.1	773.2
137.5°	775.9	775.2	782.1	795.1	798.2
140°	805.5	806.3	808.5	820.9	825.5
142.5°	831.4	834.4	834.4	844.4	847.5
145°	858.7	860.2	860.2	865.5	870.1
147.5°	879.9	883.7	882.9	884.5	888.4
150°	903.5	905.7	905.0	905.0	905.7
152.5°	922.4	924.7	923.2	924.7	923.9
155°	940.6	941.4	939.1	942.2	939.9
157.5°	956.6	956.6	953.5	957.3	953.5
160°	970.3	968.0	967.2	971.8	967.2
162.5°	982.4	979.4	978.6	983.2	977.8
165°	992.3	988.5	988.5	994.5	987.7
167.5°	1000.6	996.8	996.1	1002.9	995.3
170°	1007.5	1002.9	1003.7	1009.7	1002.1
172.5°	1012.0	1007.5	1008.2	1014.3	1005.9
175°	1015.0	1010.5	1011.2	1018.1	1009.0
177.5°	1017.3	1012.0	1013.5	1019.6	1010.5
180°	1015.0	1015.0	1015.0	1015.0	1015.0

(END OF REPORT)