

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013128

Luminaire Tested: S124DIP-B575D810UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013128
REPORT IS A COMBINATION OF REPORTS P996279 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B575D810UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589} {m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5643.0 lumens
Efficiency: N/A
Efficacy: 125.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.17 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 45.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013128

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013128

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51			44
1	96	92	88	85	88	84	81	78	70	68	66	57	55	54	45	44	43			37
2	88	80	74	69	80	74	69	64	61	58	54	50	47	45	39	38	36			31
3	80	71	63	58	73	65	59	54	54	49	46	44	41	38	35	33	31			26
4	73	62	55	49	67	57	51	45	48	43	39	39	36	32	31	28	26			23
5	67	56	48	42	61	51	44	39	43	38	33	35	31	28	28	25	23			20
6	62	50	42	36	56	46	39	34	39	33	29	32	28	25	25	22	20			17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	23	20	18			15
8	53	41	33	28	48	38	31	26	32	27	23	26	22	19	21	18	16			14
9	49	37	30	25	45	34	28	23	29	24	20	24	20	17	20	17	14			12
10	46	34	27	22	42	32	25	21	27	22	18	22	18	16	18	15	13			11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7885	7885	7885
5°	7892	7659	7668
10°	7825	7446	7394
15°	7713	7193	7084
20°	7569	6920	6765
25°	7409	6631	6420
30°	7214	6318	6042
35°	7012	5999	5676
40°	6802	5655	5287
45°	6582	5309	4923
50°	6338	4974	4521
55°	6073	4585	4121
60°	5801	4156	3705
65°	5492	3714	3235
70°	5133	3182	2732
75°	4599	2565	2188
80°	3920	1854	1539
85°	3042	1033	828

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6582 cd/sqm

TEST NUMBER: P1013128

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	91.1	1.6
10°-20°	256.8	4.6
20°-30°	377.9	6.7
30°-40°	439.3	7.8
40°-50°	439.3	7.8
50°-60°	384.2	6.8
60°-70°	285.2	5.1
70°-80°	161.8	2.9
80°-90°	48.5	0.9
90°-100°	33.9	0.6
100°-110°	223.2	4.0
110°-120°	426.1	7.6
120°-130°	541.0	9.6
130°-140°	578.7	10.3
140°-150°	541.2	9.6
150°-160°	436.4	7.7
160°-170°	281.4	5.0
170°-180°	97.0	1.7
0°-30°	725.8	12.9
0°-40°	1165.1	20.6
0°-60°	1988.6	35.2
0°-90°	2484.1	44.0
90°-120°	683.2	12.1
90°-150°	2344.0	41.5
90°-180°	3159.0	56.0
0°-180°	5643.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	967	967	967	967	967	
5°	966	963	955	963	962	92
15°	920	917	905	910	907	259
25°	833	828	817	818	814	383
35°	717	711	700	695	691	448
45°	585	580	567	559	556	451
55°	442	440	429	420	415	396
65°	300	296	288	280	277	297
75°	160	156	152	149	148	169
85°	42	42	40	40	40	45
90°	2	11	17	21	23	5
95°	42	16	17	21	22	52
105°	230	234	238	245	218	241
115°	429	431	431	432	432	422
125°	603	606	605	607	608	539
135°	748	748	751	752	754	577
145°	863	865	865	866	867	539
155°	946	947	944	948	945	436
165°	998	994	994	1000	993	282
175°	1021	1016	1017	1024	1015	97
180°	1021	1021	1021	1021	1021	

TEST NUMBER: P1013128

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	967.0	967.0	967.0	967.0	967.0
2.5°	970.1	967.8	959.3	967.0	966.2
5°	966.2	963.1	954.6	963.1	961.6
7.5°	959.3	956.2	946.9	953.8	953.1
10°	949.2	946.1	936.0	942.2	940.7
12.5°	936.0	932.9	922.1	929.0	926.7
15°	919.7	916.6	905.0	909.7	907.3
17.5°	901.1	897.3	886.4	889.5	888.0
20°	880.2	876.3	864.7	867.0	865.5
22.5°	857.7	852.3	840.7	845.4	842.3
25°	833.0	827.5	816.7	817.5	814.4
27.5°	805.1	799.6	789.6	788.0	784.1
30°	777.2	771.0	760.9	757.8	753.9
32.5°	747.7	742.3	731.5	727.6	723.7
35°	716.7	711.3	700.5	695.0	691.2
37.5°	684.2	679.5	667.9	662.5	657.1
40°	652.4	646.2	634.6	626.8	623.0
42.5°	618.3	615.2	602.1	592.8	590.4
45°	585.0	579.6	567.2	558.7	556.3
47.5°	550.1	546.3	534.6	525.3	519.1
50°	514.5	511.4	500.5	489.7	485.1
52.5°	479.6	475.8	464.1	454.8	448.6
55°	442.4	440.1	429.3	420.0	415.3
57.5°	407.6	405.2	394.4	385.1	380.4
60°	371.1	367.3	357.2	350.2	346.4
62.5°	335.5	332.4	321.6	315.4	311.5
65°	299.9	296.0	288.2	280.5	276.6
67.5°	263.4	260.3	252.6	244.8	244.1
70°	230.1	224.7	218.5	212.3	210.0
72.5°	194.5	189.1	184.4	179.8	177.4
75°	159.6	155.7	151.9	148.8	148.0
77.5°	125.5	124.0	120.1	119.3	117.0
80°	95.3	93.0	91.4	89.9	89.1
82.5°	65.9	65.1	65.1	64.3	63.5
85°	41.8	41.8	40.3	40.3	39.5
87.5°	20.1	19.4	18.6	18.6	18.6
90°	2.3	10.7	16.8	21.4	22.9
92.5°	11.5	9.9	16.0	20.6	20.6
95°	42.0	16.0	16.8	21.4	22.1
97.5°	80.2	97.0	16.8	20.6	21.4
100°	125.2	139.0	33.6	20.6	21.4
102.5°	175.6	184.8	193.9	22.1	22.1
105°	229.8	234.4	238.2	245.1	217.6
107.5°	279.5	281.7	287.1	290.9	294.0
110°	329.9	332.1	336.7	338.2	340.5

TEST NUMBER: P1013128

CATALOG NUMBER: S124DIP-B575D810UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	378.7	383.3	384.8	384.1	387.1
115°	429.1	431.4	430.6	432.2	432.2
117.5°	474.2	477.2	479.5	478.7	478.7
120°	520.0	523.0	522.3	523.8	522.3
122.5°	562.7	564.3	565.8	566.5	565.0
125°	603.2	606.3	604.7	607.0	607.8
127.5°	642.1	642.9	646.7	646.0	645.2
130°	679.6	680.3	682.6	683.4	683.4
132.5°	713.9	715.4	718.5	719.3	718.5
135°	748.3	747.5	750.6	752.1	753.6
137.5°	778.8	778.8	782.6	784.2	783.4
140°	808.6	810.1	811.6	813.9	814.7
142.5°	835.3	838.4	839.1	840.7	840.7
145°	862.8	865.1	865.1	865.9	867.4
147.5°	884.2	888.8	888.0	888.8	889.5
150°	907.9	910.9	910.1	910.1	910.9
152.5°	927.7	930.0	928.5	930.0	929.2
155°	946.0	946.8	944.5	947.6	945.3
157.5°	962.1	962.1	959.0	962.8	959.0
160°	975.8	973.5	972.8	977.3	972.8
162.5°	988.0	985.0	984.2	988.8	983.4
165°	998.0	994.1	994.1	1000.2	993.4
167.5°	1006.3	1002.5	1001.8	1008.6	1001.0
170°	1013.2	1008.6	1009.4	1015.5	1007.9
172.5°	1017.8	1013.2	1014.0	1020.1	1011.7
175°	1020.9	1016.3	1017.0	1023.9	1014.7
177.5°	1023.1	1017.8	1019.3	1025.4	1016.3
180°	1020.9	1020.9	1020.9	1020.9	1020.9

(END OF REPORT)