

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012623

Luminaire Tested: S123RDIP-B560D365UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012623
REPORT IS A COMBINATION OF REPORTS P993420 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D365UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3450.1 lumens
Efficiency: N/A
Efficacy: 103.6 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012623

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012623

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67
1	101	97	93	89	94	91	87	84	79	77	75	69	67	66	60	58	57
2	92	85	79	74	86	80	74	70	70	66	63	61	58	56	53	51	49
3	84	75	68	62	79	70	64	59	62	57	53	54	51	47	47	44	42
4	77	67	59	53	72	63	56	50	56	50	46	49	44	41	43	39	37
5	71	60	51	45	66	56	49	43	50	44	40	44	39	36	39	35	32
6	66	54	46	40	61	51	43	38	45	39	35	40	35	32	35	31	28
7	61	49	41	35	57	46	39	34	41	35	31	36	32	28	32	28	25
8	57	44	37	31	53	42	35	30	38	32	28	33	29	25	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	24	21
10	49	37	30	25	46	35	29	24	32	26	23	29	24	21	25	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8621 cd/sqm

TEST NUMBER: P1012623

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	2.6
10°-20°	246.0	7.1
20°-30°	354.2	10.3
30°-40°	398.8	11.6
40°-50°	381.5	11.1
50°-60°	312.3	9.1
60°-70°	210.6	6.1
70°-80°	105.6	3.1
80°-90°	28.6	0.8
90°-100°	99.8	2.9
100°-110°	278.9	8.1
110°-120°	272.0	7.9
120°-130°	216.6	6.3
130°-140°	171.0	5.0
140°-150°	127.6	3.7
150°-160°	89.0	2.6
160°-170°	52.3	1.5
170°-180°	17.0	0.5
0°-30°	688.6	20.0
0°-40°	1087.4	31.5
0°-60°	1781.2	51.6
0°-90°	2126.0	61.6
90°-120°	650.7	18.9
90°-150°	1165.8	33.8
90°-180°	1324.0	38.4
0°-180°	3450.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	4	9	10	10	3
95°	12	39	211	62	41	13
105°	41	61	286	500	452	44
115°	73	91	219	479	550	72
125°	101	120	204	370	434	90
135°	119	142	201	304	352	92
145°	135	155	199	250	275	85
155°	154	166	192	219	228	71
165°	168	173	184	195	199	47
175°	175	175	177	179	179	17
180°	176	176	176	176	176	

TEST NUMBER: P1012623

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	0.7	4.2	8.9	10.0	10.3
92.5°	5.3	21.3	66.1	22.6	18.8
95°	12.1	39.3	210.8	61.5	41.2
97.5°	19.2	45.0	324.2	154.6	84.6
100°	26.3	49.6	336.7	323.6	222.9
102.5°	33.8	54.9	313.6	433.2	353.0
105°	41.2	61.0	285.8	499.8	452.2
107.5°	49.1	68.0	261.3	529.2	516.9
110°	57.6	75.4	241.0	530.0	553.9

TEST NUMBER: P1012623

CATALOG NUMBER: S123RDIP-B560D365UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	65.4	83.0	227.5	510.0	561.3
115°	72.9	90.8	218.6	479.4	550.0
117.5°	80.3	98.3	212.6	446.7	525.1
120°	88.2	105.8	208.7	415.8	492.4
122.5°	94.9	112.9	206.2	391.5	461.8
125°	101.3	119.6	204.1	369.7	433.7
127.5°	106.3	126.0	203.0	352.0	409.5
130°	110.9	131.7	201.9	335.6	389.6
132.5°	114.5	136.8	201.6	320.3	370.1
135°	118.7	141.7	201.2	304.5	351.6
137.5°	122.6	145.6	200.5	289.6	332.0
140°	126.6	149.1	200.1	275.0	311.4
142.5°	130.8	152.3	199.4	261.7	292.2
145°	135.4	155.2	198.7	249.8	274.8
147.5°	140.1	158.2	197.7	240.5	259.9
150°	144.7	160.7	196.2	232.3	247.1
152.5°	149.3	163.4	194.5	225.2	236.4
155°	153.9	166.0	192.3	218.6	227.9
157.5°	157.5	168.4	190.6	212.2	219.7
160°	161.8	170.3	188.4	206.4	211.9
162.5°	165.0	171.7	186.3	200.9	204.8
165°	168.2	173.0	184.2	195.4	198.7
167.5°	170.6	174.0	182.0	190.6	192.7
170°	172.8	174.6	179.9	186.2	187.4
172.5°	174.2	175.1	178.1	182.6	182.4
175°	175.3	175.4	176.7	179.2	178.8
177.5°	176.0	175.6	175.6	177.0	176.3
180°	175.6	175.6	175.6	175.6	175.6

(END OF REPORT)