

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012628

Luminaire Tested: S123RDIP-B560D365UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012628
REPORT IS A COMBINATION OF REPORTS P993425 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D365UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 3394.0 lumens
Efficiency: N/A
Efficacy: 101.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 33.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012628

CATALOG NUMBER: S123RDIP-B560D365UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012628

CATALOG NUMBER: S123RDIP-B560D365UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68
1	101	97	93	90	95	91	88	85	80	78	75	70	68	67	61	59	58
2	92	85	79	74	86	80	75	70	71	67	63	62	59	56	54	52	50
3	85	75	68	62	79	71	64	59	63	58	53	55	51	48	48	45	43
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37
5	71	60	52	46	67	57	49	44	50	44	40	45	40	36	39	36	33
6	66	54	46	40	62	51	44	38	46	40	35	40	36	32	36	32	29
7	61	49	41	35	57	46	39	34	41	35	31	37	32	28	33	29	26
8	57	44	37	31	53	42	35	30	38	32	28	34	29	26	30	26	23
9	53	41	33	28	50	39	32	27	35	29	25	31	27	23	28	24	21
10	50	38	30	25	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10168	10168	10168
5°	10184	9808	9781
10°	10104	9440	9253
15°	9972	8983	8675
20°	9801	8487	8028
25°	9623	7972	7415
30°	9396	7425	6691
35°	9161	6886	6032
40°	8940	6301	5303
45°	8658	5730	4648
50°	8347	5119	3970
55°	8023	4466	3349
60°	7715	3796	2718
65°	7315	3108	2122
70°	6814	2351	1516
75°	6090	1592	1201
80°	5201	1107	842
85°	3900	599	441

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8658 cd/sqm

TEST NUMBER: P1012628

CATALOG NUMBER: S123RDIP-B560D365UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.8	2.6
10°-20°	247.0	7.3
20°-30°	355.7	10.5
30°-40°	400.5	11.8
40°-50°	383.1	11.3
50°-60°	313.6	9.2
60°-70°	211.5	6.2
70°-80°	106.1	3.1
80°-90°	28.7	0.8
90°-100°	29.3	0.9
100°-110°	88.5	2.6
110°-120°	150.7	4.4
120°-130°	198.3	5.8
130°-140°	222.9	6.6
140°-150°	219.1	6.5
150°-160°	184.5	5.4
160°-170°	122.8	3.6
170°-180°	43.0	1.3
0°-30°	691.5	20.4
0°-40°	1092.0	32.2
0°-60°	1788.8	52.7
0°-90°	2135.0	62.9
90°-120°	268.5	7.9
90°-150°	908.8	26.8
90°-180°	1259.0	37.1
0°-180°	3394.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	945	945	945	945	945	
5°	945	941	932	938	937	90
15°	901	892	871	867	862	254
25°	820	801	765	749	741	377
35°	709	682	634	601	588	444
45°	583	548	490	446	428	450
55°	443	405	340	296	280	397
65°	303	260	201	163	155	299
75°	160	123	81	74	72	171
85°	41	24	22	20	20	44
90°	0	4	9	10	11	4
95°	21	24	26	28	28	23
105°	80	81	84	84	85	86
115°	152	153	152	152	152	150
125°	222	223	222	221	220	198
135°	288	290	290	288	288	222
145°	350	350	351	351	350	218
155°	400	400	400	402	399	184
165°	436	435	435	437	434	123
175°	453	452	452	454	452	43
180°	454	454	454	454	454	

TEST NUMBER: P1012628

CATALOG NUMBER: S123RDIP-B560D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	944.6	944.6	944.6	944.6	944.6
2.5°	948.4	945.4	936.2	944.6	943.1
5°	944.6	940.8	931.6	938.5	936.9
7.5°	937.7	933.9	922.4	927.0	924.7
10°	928.5	923.1	909.4	910.1	906.3
12.5°	915.5	909.4	891.7	891.0	886.4
15°	900.9	892.5	871.0	867.2	861.9
17.5°	883.3	874.1	847.3	839.6	832.0
20°	863.4	851.1	822.0	812.1	802.9
22.5°	841.2	826.6	795.2	782.2	773.8
25°	819.7	800.6	765.3	749.2	740.8
27.5°	793.7	773.0	734.7	713.2	700.2
30°	766.9	743.9	701.0	674.9	662.7
32.5°	740.0	713.2	667.3	638.2	625.1
35°	709.4	681.8	634.3	601.4	587.6
37.5°	678.8	648.9	599.1	562.3	545.5
40°	649.6	615.9	561.5	521.7	504.1
42.5°	616.7	583.0	526.3	481.9	466.6
45°	583.0	548.5	489.5	445.9	427.5
47.5°	550.1	511.7	453.5	406.0	389.9
50°	513.3	477.3	415.2	367.7	350.1
52.5°	480.3	440.5	379.2	329.4	314.1
55°	442.8	405.3	340.1	295.7	280.4
57.5°	409.1	368.5	302.6	260.5	247.4
60°	373.9	331.7	268.1	226.8	213.7
62.5°	338.6	296.5	232.9	194.6	180.8
65°	302.6	260.5	200.7	163.2	154.8
67.5°	266.6	223.7	165.5	137.1	127.9
70°	231.4	190.0	136.4	109.6	101.1
72.5°	196.1	155.5	108.0	87.3	85.0
75°	160.1	123.3	81.2	73.5	72.0
77.5°	127.2	93.5	63.6	59.0	57.5
80°	95.8	64.4	48.3	46.0	44.4
82.5°	65.9	39.8	34.5	32.2	32.2
85°	40.6	23.7	21.5	19.9	19.9
87.5°	18.4	10.0	10.0	9.2	8.4
90°	0.4	3.9	8.6	10.0	10.7
92.5°	10.7	12.9	15.0	16.1	15.3
95°	21.1	23.6	26.4	27.8	27.8
97.5°	34.6	36.4	38.6	40.3	40.0
100°	48.5	50.7	52.5	53.5	54.3
102.5°	64.6	65.7	68.2	69.2	68.9
105°	80.3	81.0	84.2	84.2	85.0
107.5°	98.9	99.2	100.7	101.7	101.4
110°	116.0	116.7	117.4	118.9	118.1

TEST NUMBER: P1012628

CATALOG NUMBER: S123RDIP-B560D365UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	133.9	134.2	134.2	136.0	136.0
115°	151.7	152.8	152.1	152.4	152.1
117.5°	169.9	170.3	169.5	169.5	168.5
120°	186.7	188.8	187.0	186.7	186.0
122.5°	204.2	205.6	204.9	203.8	202.7
125°	222.0	223.1	222.4	220.9	219.5
127.5°	238.4	240.6	239.9	237.7	236.3
130°	254.9	257.7	256.6	255.2	252.7
132.5°	271.3	274.1	273.4	271.6	269.9
135°	288.1	290.2	289.8	288.4	287.7
137.5°	303.4	305.2	306.3	304.5	303.4
140°	319.5	321.3	321.6	321.3	318.8
142.5°	334.1	335.9	336.6	336.2	334.5
145°	349.5	350.2	351.2	350.9	349.5
147.5°	362.7	364.1	365.2	365.2	363.0
150°	376.6	377.3	378.0	378.0	375.9
152.5°	388.0	389.1	389.4	390.1	388.4
155°	400.1	400.1	400.5	401.9	399.4
157.5°	410.5	410.1	410.5	411.9	409.8
160°	420.1	419.4	419.4	421.2	419.8
162.5°	428.7	427.6	428.0	429.8	427.3
165°	435.8	434.8	434.8	436.9	434.4
167.5°	441.9	440.5	440.8	443.0	440.8
170°	446.9	445.5	445.5	448.0	445.5
172.5°	450.8	449.4	449.4	451.5	449.0
175°	453.3	451.9	451.9	454.0	451.5
177.5°	454.7	453.3	453.3	455.5	453.0
180°	454.4	454.4	454.4	454.4	454.4

(END OF REPORT)