

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013179

Luminaire Tested: S124DIP-B795D590UB2750-4F0-XX-W2A-D_2700K

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013179
REPORT IS A COMBINATION OF REPORTS P996513 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B795D590UB2750-4F0-XX-W2A-D_2700K
Description: Define 4 Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473} {m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5574.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 51.3
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013179

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1013179

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	98	93	88	84	90	86	82	79	73	70	68	62	60	58	51	49	48
2	88	80	74	68	81	74	69	64	64	59	55	53	50	47	44	42	40
3	80	70	62	56	74	65	58	53	56	50	46	47	43	39	39	36	33
4	73	62	54	47	67	57	50	44	49	43	39	41	37	33	34	31	28
5	67	55	46	40	62	51	44	38	44	38	33	37	32	29	31	27	24
6	62	49	41	35	57	46	38	33	39	33	29	33	29	25	28	24	21
7	57	44	36	30	53	41	34	29	36	30	25	30	26	22	25	22	19
8	53	40	32	27	49	38	30	25	32	27	22	28	23	20	23	20	17
9	49	37	29	24	46	34	27	22	30	24	20	25	21	18	21	18	15
10	46	34	26	21	43	31	25	20	27	22	18	24	19	16	20	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7721	7721	7721
5°	7742	7519	7533
10°	7692	7371	7350
15°	7619	7205	7144
20°	7513	7025	6944
25°	7393	6827	6729
30°	7263	6630	6508
35°	7116	6428	6313
40°	6997	6236	6110
45°	6824	6054	5931
50°	6674	5848	5741
55°	6520	5650	5523
60°	6281	5403	5319
65°	6020	5136	5071
70°	5700	4833	4786
75°	5256	4494	4514
80°	4754	4149	4230
85°	4090	3803	3999

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6824 cd/sqm

TEST NUMBER: P1013179

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	89.7	1.6
10°-20°	257.0	4.6
20°-30°	388.6	7.0
30°-40°	470.2	8.4
40°-50°	497.1	8.9
50°-60°	467.8	8.4
60°-70°	388.2	7.0
70°-80°	272.4	4.9
80°-90°	155.1	2.8
90°-100°	116.6	2.1
100°-110°	233.3	4.2
110°-120°	361.7	6.5
120°-130°	427.1	7.7
130°-140°	440.6	7.9
140°-150°	403.8	7.2
150°-160°	323.9	5.8
160°-170°	208.9	3.7
170°-180°	72.0	1.3
0°-30°	735.4	13.2
0°-40°	1205.6	21.6
0°-60°	2170.4	38.9
0°-90°	2986.1	53.6
90°-120°	711.6	12.8
90°-150°	1983.1	35.6
90°-180°	2588.0	46.4
0°-180°	5574.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	947	947	947	947	947	
5°	948	945	937	946	945	90
15°	909	910	906	916	915	256
25°	831	838	841	852	854	383
35°	727	740	751	766	769	455
45°	606	627	647	665	670	469
55°	475	497	529	550	557	423
65°	329	363	399	425	434	326
75°	182	222	266	296	305	194
85°	56	101	148	180	191	59
90°	19	67	118	152	161	13
95°	45	61	105	137	147	49
105°	180	205	247	278	266	189
115°	325	336	369	394	401	320
125°	452	453	478	500	507	404
135°	557	557	566	585	592	430
145°	641	642	642	649	654	401
155°	702	703	701	703	702	324
165°	741	738	738	742	737	209
175°	758	754	755	760	753	72
180°	758	758	758	758	758	

TEST NUMBER: P1013179

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	946.8	946.8	946.8	946.8	946.8
2.5°	951.0	947.9	939.4	946.8	945.7
5°	947.9	944.7	937.2	945.7	944.7
7.5°	941.5	939.4	933.0	942.6	941.5
10°	933.0	931.9	926.6	936.2	935.1
12.5°	921.3	921.3	918.2	926.6	926.6
15°	908.6	909.7	906.5	916.0	915.0
17.5°	891.7	894.8	893.8	903.3	902.3
20°	873.6	876.8	877.9	888.5	888.5
22.5°	853.5	857.7	859.9	870.5	872.6
25°	831.2	837.6	840.8	852.4	853.5
27.5°	806.8	816.4	820.6	831.2	832.3
30°	782.5	790.9	798.4	810.0	812.1
32.5°	755.9	766.6	775.0	788.8	790.9
35°	727.3	740.0	750.6	765.5	768.7
37.5°	698.7	713.5	726.3	741.1	744.3
40°	671.1	684.9	699.8	715.7	719.9
42.5°	639.3	655.2	673.3	691.3	694.5
45°	606.5	626.6	646.7	664.8	670.1
47.5°	575.7	595.9	619.2	637.2	643.6
50°	541.8	565.1	588.4	609.6	616.0
52.5°	507.9	531.2	558.7	579.9	586.3
55°	475.0	497.3	529.1	550.3	556.6
57.5°	437.9	465.4	496.2	521.6	526.9
60°	401.8	429.4	464.4	488.8	497.3
62.5°	366.8	397.6	432.6	457.0	465.4
65°	328.7	362.6	398.6	425.2	433.6
67.5°	292.6	328.7	366.8	393.3	401.8
70°	255.5	291.6	331.9	360.5	367.9
72.5°	219.5	256.6	300.0	327.6	336.1
75°	182.4	221.6	266.1	295.8	305.3
77.5°	147.4	188.7	235.4	265.1	275.7
80°	115.6	158.0	204.6	236.4	244.9
82.5°	83.8	128.3	174.9	207.8	217.3
85°	56.2	100.7	148.4	180.2	190.8
87.5°	35.0	78.5	125.1	155.9	165.4
90°	18.7	67.3	117.5	151.6	161.2
92.5°	24.4	60.4	110.5	143.6	152.1
95°	45.0	60.7	104.7	136.8	146.8
97.5°	72.2	115.5	99.4	129.8	139.9
100°	104.6	142.3	105.5	124.5	132.5
102.5°	142.0	172.1	219.2	119.2	127.7
105°	180.1	204.7	246.8	278.4	266.5
107.5°	216.9	236.7	277.8	307.1	316.8
110°	253.3	269.8	310.3	335.8	346.0

TEST NUMBER: P1013179

CATALOG NUMBER: S124DIP-B795D590UB2750-4F0-XX-W2A-D_2700K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	288.5	304.6	340.7	363.5	374.2
115°	324.9	336.1	369.4	393.9	401.3
117.5°	358.3	366.9	400.4	422.1	430.6
120°	391.2	396.7	426.8	449.1	456.5
122.5°	422.9	424.1	453.8	475.6	481.9
125°	451.9	453.1	478.5	500.3	507.3
127.5°	480.8	480.3	504.4	522.9	529.7
130°	507.5	507.0	525.7	545.4	551.7
132.5°	533.0	533.1	548.0	566.7	572.4
135°	557.4	556.9	566.5	584.7	592.2
137.5°	580.1	579.1	586.1	603.2	607.9
140°	602.2	602.3	604.5	620.0	625.8
142.5°	621.0	623.3	622.8	635.6	639.8
145°	641.4	642.0	642.0	649.0	654.3
147.5°	657.3	659.6	659.0	660.7	665.5
150°	674.9	676.0	675.5	675.5	676.0
152.5°	688.5	690.2	689.1	690.2	689.6
155°	702.1	702.7	701.0	703.2	701.5
157.5°	714.0	714.0	711.7	714.6	711.7
160°	724.2	722.5	721.9	725.3	721.9
162.5°	733.3	731.0	730.4	733.8	729.9
165°	740.6	737.8	737.8	742.3	737.2
167.5°	746.9	744.0	743.5	748.6	742.9
170°	752.0	748.6	749.1	753.7	748.0
172.5°	755.4	752.0	752.5	757.1	750.8
175°	757.6	754.2	754.8	759.9	753.1
177.5°	759.3	755.4	756.5	761.0	754.2
180°	757.6	757.6	757.6	757.6	757.6

(END OF REPORT)