

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012651

Luminaire Tested: S123RDIP-B560D585UB30-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012651
REPORT IS A COMBINATION OF REPORTS P993460 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB30-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4254.9 lumens
Efficiency: N/A
Efficacy: 108.0 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012651

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012651

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	48	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	44	43	41	41	41	36
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	31	31	27
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27	27	27	24
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24	24	24	21
7	59	47	39	34	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	22	19	19	19	17
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17	17	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10125	10125	10125
5°	10141	9766	9740
10°	10061	9399	9214
15°	9930	8946	8638
20°	9759	8451	7994
25°	9583	7939	7384
30°	9356	7393	6663
35°	9123	6857	6006
40°	8903	6275	5281
45°	8621	5706	4629
50°	8311	5098	3953
55°	7989	4447	3335
60°	7682	3780	2706
65°	7284	3096	2113
70°	6785	2341	1510
75°	6063	1586	1196
80°	5179	1103	838
85°	3881	596	439

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8621 cd/sqm

TEST NUMBER: P1012651

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	88.4	2.1
10°-20°	246.0	5.8
20°-30°	354.2	8.3
30°-40°	398.8	9.4
40°-50°	381.5	9.0
50°-60°	312.3	7.3
60°-70°	210.6	4.9
70°-80°	105.6	2.5
80°-90°	29.2	0.7
90°-100°	160.4	3.8
100°-110°	448.4	10.5
110°-120°	437.2	10.3
120°-130°	348.1	8.2
130°-140°	274.8	6.5
140°-150°	205.0	4.8
150°-160°	143.0	3.4
160°-170°	84.0	2.0
170°-180°	27.3	0.6
0°-30°	688.6	16.2
0°-40°	1087.4	25.6
0°-60°	1781.2	41.9
0°-90°	2126.6	50.0
90°-120°	1046.0	24.6
90°-150°	1874.0	44.0
90°-180°	2128.0	50.0
0°-180°	4254.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	941	941	941	941	941	
5°	941	937	928	934	933	89
15°	897	889	867	864	858	253
25°	816	797	762	746	738	375
35°	706	679	632	599	585	442
45°	580	546	488	444	426	448
55°	441	404	339	294	279	395
65°	301	259	200	162	154	298
75°	159	123	81	73	72	170
85°	40	24	21	20	20	44
90°	1	7	14	16	17	4
95°	19	63	339	99	66	21
105°	66	98	459	803	727	70
115°	117	146	351	771	884	116
125°	163	192	328	594	697	145
135°	191	228	323	489	565	147
145°	218	249	319	401	442	136
155°	247	267	309	351	366	114
165°	270	278	296	314	319	76
175°	282	282	284	288	287	27
180°	282	282	282	282	282	

TEST NUMBER: P1012651

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	940.6	940.6	940.6	940.6	940.6
2.5°	944.4	941.4	932.2	940.6	939.1
5°	940.6	936.8	927.6	934.5	933.0
7.5°	933.7	929.9	918.5	923.1	920.8
10°	924.6	919.2	905.5	906.3	902.5
12.5°	911.6	905.5	888.0	887.2	882.6
15°	897.1	888.7	867.4	863.6	858.2
17.5°	879.6	870.4	843.7	836.1	828.5
20°	859.7	847.5	818.5	808.6	799.5
22.5°	837.6	823.1	791.8	778.9	770.5
25°	816.3	797.2	762.1	746.1	737.7
27.5°	790.3	769.7	731.6	710.2	697.3
30°	763.6	740.7	698.0	672.1	659.9
32.5°	736.9	710.2	664.5	635.5	622.5
35°	706.4	678.9	631.6	598.8	585.1
37.5°	675.9	646.1	596.6	559.9	543.2
40°	646.9	613.3	559.2	519.5	502.0
42.5°	614.1	580.5	524.1	479.8	464.6
45°	580.5	546.2	487.5	444.0	425.7
47.5°	547.7	509.6	451.6	404.3	388.3
50°	511.1	475.3	413.5	366.2	348.6
52.5°	478.3	438.6	377.6	328.0	312.8
55°	440.9	403.6	338.7	294.5	279.2
57.5°	407.4	366.9	301.3	259.4	246.4
60°	372.3	330.3	267.0	225.8	212.8
62.5°	337.2	295.2	231.9	193.8	180.0
65°	301.3	259.4	199.9	162.5	154.1
67.5°	265.5	222.8	164.8	136.6	127.4
70°	230.4	189.2	135.8	109.1	100.7
72.5°	195.3	154.9	107.6	87.0	84.7
75°	159.4	122.8	80.9	73.2	71.7
77.5°	126.6	93.1	63.3	58.7	57.2
80°	95.4	64.1	48.1	45.8	44.2
82.5°	65.6	39.7	34.3	32.0	32.0
85°	40.4	23.6	21.4	19.8	19.8
87.5°	18.3	9.9	9.9	9.2	8.4
90°	1.1	6.8	14.3	16.0	16.6
92.5°	8.6	34.2	106.3	36.3	30.3
95°	19.4	63.2	338.9	98.8	66.3
97.5°	30.9	72.3	521.2	248.6	136.0
100°	42.3	79.8	541.2	520.0	358.3
102.5°	54.3	88.3	504.0	696.3	567.4
105°	66.3	98.0	459.4	803.4	726.9
107.5°	78.9	109.4	420.0	850.6	830.9
110°	92.6	121.1	387.4	852.0	890.3

TEST NUMBER: P1012651

CATALOG NUMBER: S123RDIP-B560D585UB30-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	105.1	133.4	365.7	819.8	902.3
115°	117.1	146.0	351.4	770.6	884.0
117.5°	129.1	158.0	341.7	718.0	844.0
120°	141.7	170.0	335.4	668.3	791.4
122.5°	152.6	181.4	331.4	629.2	742.3
125°	162.9	192.3	328.0	594.3	697.2
127.5°	170.9	202.6	326.3	565.8	658.3
130°	178.3	211.7	324.6	539.4	626.3
132.5°	184.0	220.0	324.0	514.9	594.9
135°	190.9	227.7	323.4	489.4	565.2
137.5°	197.1	234.0	322.3	465.4	533.7
140°	203.4	239.8	321.7	442.0	500.6
142.5°	210.3	244.8	320.6	420.6	469.7
145°	217.7	249.4	319.4	401.4	441.7
147.5°	225.1	254.3	317.7	386.6	417.7
150°	232.6	258.2	315.4	373.4	397.2
152.5°	240.0	262.5	312.6	362.0	380.0
155°	247.4	266.9	309.2	351.4	366.3
157.5°	253.1	270.5	306.3	341.2	353.2
160°	260.0	273.8	302.9	331.7	340.6
162.5°	265.1	276.0	299.4	322.9	329.2
165°	270.3	278.0	296.0	314.0	319.4
167.5°	274.3	279.8	292.6	306.3	309.7
170°	277.7	280.6	289.2	299.4	301.2
172.5°	280.0	281.4	286.3	293.4	293.2
175°	281.7	282.0	284.0	288.0	287.4
177.5°	282.9	282.3	282.3	284.6	283.4
180°	282.3	282.3	282.3	282.3	282.3

(END OF REPORT)