

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013197

Luminaire Tested: S124DIP-B795D810UB2750-4F0-XX-W2A-D_4000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013197
REPORT IS A COMBINATION OF REPORTS P996576 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124DIP-B795D810UB2750-4F0-XX-W2A-D_4000K
Description: Define 4 Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865} {m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6380.0 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.23 / 1.28 / 1.39
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013197

CATALOG NUMBER: S124DIP-B795D810UB2750-4F0-XX-W2A-D_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013197

CATALOG NUMBER: S124DIP-B795D810UB2750-4F0-XX-W2A-D_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53			47
1	96	91	87	83	88	84	80	77	70	67	65	57	55	54	46	44	43			38
2	87	79	73	67	80	73	67	62	61	57	53	50	47	44	40	37	36			31
3	79	69	62	56	72	64	57	52	53	48	44	44	40	37	35	32	30			26
4	72	61	53	47	66	56	49	43	47	42	37	39	35	31	31	28	25			22
5	66	54	46	40	60	50	43	37	42	36	32	35	30	27	28	24	22			19
6	61	49	40	34	56	45	37	32	38	32	28	31	27	23	25	22	19			16
7	56	44	36	30	51	40	33	28	34	28	24	28	24	21	23	19	17			14
8	52	40	32	26	48	37	30	25	31	25	21	26	21	18	21	18	15			13
9	49	36	28	23	44	33	27	22	28	23	19	24	19	16	19	16	14			11
10	45	33	26	21	41	31	24	20	26	21	17	22	18	15	18	15	12			10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	7742	7742	7742
5°	7763	7541	7554
10°	7713	7392	7371
15°	7641	7225	7164
20°	7534	7044	6964
25°	7413	6845	6747
30°	7283	6648	6527
35°	7136	6446	6330
40°	7017	6253	6127
45°	6842	6071	5947
50°	6693	5865	5757
55°	6538	5665	5539
60°	6300	5418	5333
65°	6036	5152	5085
70°	5716	4846	4799
75°	5271	4507	4527
80°	4767	4162	4242
85°	4097	3813	4012

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6842 cd/sqm

TEST NUMBER: P1013197

CATALOG NUMBER: S124DIP-B795D810UB2750-4F0-XX-W2A-D_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	90.0	1.4
10°-20°	257.7	4.0
20°-30°	389.7	6.1
30°-40°	471.5	7.4
40°-50°	498.4	7.8
50°-60°	469.1	7.4
60°-70°	389.3	6.1
70°-80°	273.2	4.3
80°-90°	156.1	2.4
90°-100°	125.4	2.0
100°-110°	289.8	4.5
110°-120°	469.3	7.4
120°-130°	563.6	8.8
130°-140°	586.5	9.2
140°-150°	540.3	8.5
150°-160°	433.9	6.8
160°-170°	279.8	4.4
170°-180°	96.4	1.5
0°-30°	737.4	11.6
0°-40°	1208.9	18.9
0°-60°	2176.5	34.1
0°-90°	2995.0	46.9
90°-120°	884.5	13.9
90°-150°	2574.8	40.4
90°-180°	3385.0	53.1
0°-180°	6380.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	949	949	949	949	949	
5°	950	947	940	948	947	90
15°	911	912	909	919	918	257
25°	834	840	843	855	856	384
35°	729	742	753	768	771	457
45°	608	628	648	667	672	470
55°	476	499	530	552	558	424
65°	330	364	400	426	435	327
75°	183	222	267	297	306	194
85°	56	101	149	181	191	59
90°	19	70	122	157	167	14
95°	56	65	109	142	153	62
105°	238	264	307	340	322	250
115°	433	445	478	503	510	427
125°	604	606	631	654	661	540
135°	746	745	756	774	782	575
145°	859	860	860	867	873	537
155°	941	941	939	942	940	434
165°	992	988	988	994	988	280
175°	1015	1010	1011	1018	1009	97
180°	1015	1015	1015	1015	1015	

TEST NUMBER: P1013197

CATALOG NUMBER: S124DIP-B795D810UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	949.4	949.4	949.4	949.4	949.4
2.5°	953.7	950.5	942.0	949.4	948.4
5°	950.5	947.3	939.9	948.4	947.3
7.5°	944.1	942.0	935.6	945.2	944.1
10°	935.6	934.5	929.2	938.8	937.7
12.5°	923.9	923.9	920.7	929.2	929.2
15°	911.2	912.2	909.0	918.6	917.5
17.5°	894.1	897.3	896.3	905.8	904.8
20°	876.1	879.3	880.3	891.0	891.0
22.5°	855.9	860.1	862.2	872.9	875.0
25°	833.5	839.9	843.1	854.8	855.9
27.5°	809.1	818.7	822.9	833.5	834.6
30°	784.6	793.1	800.6	812.3	814.4
32.5°	758.1	768.7	777.2	791.0	793.1
35°	729.4	742.1	752.7	767.6	770.8
37.5°	700.6	715.5	728.3	743.2	746.4
40°	673.0	686.8	701.7	717.7	721.9
42.5°	641.1	657.1	675.1	693.2	696.4
45°	608.1	628.3	648.5	666.6	671.9
47.5°	577.3	597.5	620.9	639.0	645.4
50°	543.3	566.7	590.1	611.3	617.7
52.5°	509.3	532.7	560.3	581.6	587.9
55°	476.3	498.6	530.5	551.8	558.2
57.5°	439.1	466.7	497.6	523.1	528.4
60°	403.0	430.6	465.7	490.1	498.6
62.5°	367.9	398.7	433.8	458.2	466.7
65°	329.6	363.6	399.8	426.3	434.8
67.5°	293.4	329.6	367.9	394.4	403.0
70°	256.2	292.4	332.8	361.5	368.9
72.5°	220.1	257.3	300.9	328.5	337.0
75°	182.9	222.2	266.9	296.6	306.2
77.5°	147.8	189.2	236.0	265.8	276.4
80°	115.9	158.4	205.2	237.1	245.6
82.5°	84.0	128.6	175.4	208.4	218.0
85°	56.3	101.0	148.8	180.7	191.4
87.5°	35.1	78.7	125.5	156.3	165.9
90°	19.3	70.1	122.0	157.4	167.4
92.5°	27.3	63.1	114.8	149.1	157.7
95°	55.6	64.8	109.2	142.5	152.8
97.5°	92.5	140.0	103.9	135.3	145.7
100°	136.2	177.5	114.2	130.0	138.3
102.5°	186.3	218.8	268.3	125.1	133.6
105°	238.1	263.9	307.1	340.5	321.7
107.5°	287.5	307.7	350.4	380.7	391.2
110°	336.5	353.6	395.4	421.4	432.2

TEST NUMBER: P1013197

CATALOG NUMBER: S124DIP-B795D810UB2750-4F0-XX-W2A-D_4000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	384.0	401.3	437.9	460.6	472.1
115°	433.1	444.8	478.2	503.1	510.5
117.5°	477.9	487.3	521.5	543.0	551.5
120°	522.3	528.5	558.6	581.4	588.4
122.5°	564.8	566.3	596.6	618.6	624.5
125°	604.1	606.0	631.1	653.6	660.6
127.5°	642.8	642.4	667.5	685.9	692.5
130°	678.9	678.5	697.8	717.8	724.2
132.5°	713.0	713.5	729.3	748.2	753.7
135°	746.1	745.4	755.9	774.4	782.3
137.5°	776.5	775.5	783.5	801.0	805.5
140°	806.1	806.6	809.1	825.2	831.4
142.5°	831.7	834.7	834.4	847.6	851.8
145°	859.0	860.2	860.2	867.3	873.0
147.5°	880.2	883.7	882.9	884.8	889.8
150°	903.8	905.7	905.0	905.0	905.7
152.5°	922.4	924.7	923.2	924.7	923.9
155°	940.6	941.4	939.1	942.2	939.9
157.5°	956.6	956.6	953.5	957.3	953.5
160°	970.3	968.0	967.2	971.8	967.2
162.5°	982.4	979.4	978.6	983.2	977.8
165°	992.3	988.5	988.5	994.5	987.7
167.5°	1000.6	996.8	996.1	1002.9	995.3
170°	1007.5	1002.9	1003.7	1009.7	1002.1
172.5°	1012.0	1007.5	1008.2	1014.3	1005.9
175°	1015.0	1010.5	1011.2	1018.1	1009.0
177.5°	1017.3	1012.0	1013.5	1019.6	1010.5
180°	1015.0	1015.0	1015.0	1015.0	1015.0

(END OF REPORT)