

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012669

Luminaire Tested: S123RDIP-B560D585UB50-4F0-XX-W2A-F4

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012669
REPORT IS A COMBINATION OF REPORTS P993478 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B560D585UB50-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 4091.7 lumens
Efficiency: N/A
Efficacy: 103.9 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 39.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012669

CATALOG NUMBER: S123RDIP-B560D585UB50-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012669

CATALOG NUMBER: S123RDIP-B560D585UB50-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	44	43	41
3	82	73	66	60	75	67	61	56	57	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31
5	69	58	50	44	64	54	47	41	46	41	36	39	35	32	32	29	27
6	64	52	44	38	59	48	41	36	42	36	32	35	31	28	29	26	24
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19
9	51	39	32	27	47	36	30	25	32	26	23	27	23	20	23	20	17
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	9734	9734	9734
5°	9750	9389	9364
10°	9673	9037	8858
15°	9547	8600	8305
20°	9383	8126	7685
25°	9213	7632	7099
30°	8996	7108	6406
35°	8771	6593	5774
40°	8559	6033	5077
45°	8288	5486	4450
50°	7991	4901	3801
55°	7681	4275	3206
60°	7385	3634	2602
65°	7003	2977	2032
70°	6523	2250	1451
75°	5831	1523	1149
80°	4978	1059	806
85°	3737	571	423

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 8288 cd/sqm

TEST NUMBER: P1012669

CATALOG NUMBER: S123RDIP-B560D585UB50-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	85.0	2.1
10°-20°	236.5	5.8
20°-30°	340.5	8.3
30°-40°	383.4	9.4
40°-50°	366.8	9.0
50°-60°	300.2	7.3
60°-70°	202.4	4.9
70°-80°	101.5	2.5
80°-90°	28.1	0.7
90°-100°	154.3	3.8
100°-110°	431.3	10.5
110°-120°	420.5	10.3
120°-130°	334.9	8.2
130°-140°	264.3	6.5
140°-150°	197.2	4.8
150°-160°	137.6	3.4
160°-170°	80.8	2.0
170°-180°	26.3	0.6
0°-30°	662.0	16.2
0°-40°	1045.4	25.6
0°-60°	1712.5	41.9
0°-90°	2044.5	50.0
90°-120°	1006.1	24.6
90°-150°	1802.6	44.1
90°-180°	2047.0	50.0
0°-180°	4091.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	904	904	904	904	904	
5°	904	901	892	898	897	86
15°	862	854	834	830	825	243
25°	785	766	733	717	709	361
35°	679	653	607	576	562	425
45°	558	525	469	427	409	431
55°	424	388	326	283	268	380
65°	290	249	192	156	148	287
75°	153	118	78	70	69	163
85°	39	23	20	19	19	43
90°	1	7	14	15	16	4
95°	19	61	326	95	64	20
105°	64	94	442	773	699	68
115°	113	140	338	741	850	112
125°	157	185	316	572	671	139
135°	184	219	311	471	544	142
145°	209	240	307	386	425	131
155°	238	257	297	338	352	109
165°	260	267	285	302	307	73
175°	271	271	273	277	276	26
180°	272	272	272	272	272	

TEST NUMBER: P1012669

CATALOG NUMBER: S123RDIP-B560D585UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	904.3	904.3	904.3	904.3	904.3
2.5°	908.0	905.0	896.2	904.3	902.8
5°	904.3	900.6	891.8	898.4	897.0
7.5°	897.7	894.0	883.0	887.4	885.2
10°	888.9	883.8	870.6	871.3	867.6
12.5°	876.4	870.6	853.7	853.0	848.6
15°	862.5	854.4	833.9	830.2	825.1
17.5°	845.6	836.8	811.2	803.8	796.5
20°	826.6	814.8	787.0	777.4	768.6
22.5°	805.3	791.4	761.3	748.8	740.8
25°	784.8	766.4	732.7	717.3	709.2
27.5°	759.8	740.0	703.4	682.8	670.3
30°	734.2	712.2	671.1	646.1	634.4
32.5°	708.5	682.8	638.8	610.9	598.5
35°	679.2	652.7	607.3	575.7	562.5
37.5°	649.8	621.2	573.5	538.3	522.2
40°	621.9	589.7	537.6	499.5	482.6
42.5°	590.4	558.1	503.9	461.3	446.7
45°	558.1	525.1	468.7	426.9	409.3
47.5°	526.6	489.9	434.2	388.7	373.3
50°	491.4	456.9	397.5	352.0	335.2
52.5°	459.9	421.7	363.0	315.4	300.7
55°	423.9	388.0	325.6	283.1	268.4
57.5°	391.6	352.8	289.7	249.4	236.9
60°	357.9	317.6	256.7	217.1	204.6
62.5°	324.2	283.8	223.0	186.3	173.1
65°	289.7	249.4	192.2	156.2	148.2
67.5°	255.2	214.2	158.4	131.3	122.5
70°	221.5	181.9	130.5	104.9	96.8
72.5°	187.8	148.9	103.4	83.6	81.4
75°	153.3	118.1	77.7	70.4	68.9
77.5°	121.7	89.5	60.9	56.5	55.0
80°	91.7	61.6	46.2	44.0	42.5
82.5°	63.1	38.1	33.0	30.8	30.8
85°	38.9	22.7	20.5	19.1	19.1
87.5°	17.6	9.5	9.5	8.8	8.1
90°	1.1	6.6	13.7	15.4	15.9
92.5°	8.2	33.0	102.2	34.9	29.1
95°	18.7	60.8	325.9	95.1	63.8
97.5°	29.7	69.5	501.3	239.1	130.8
100°	40.7	76.7	520.5	500.2	344.6
102.5°	52.2	84.9	484.8	669.8	545.8
105°	63.8	94.2	441.9	772.8	699.2
107.5°	75.9	105.2	404.0	818.2	799.2
110°	89.0	116.5	372.7	819.6	856.4

TEST NUMBER: P1012669

CATALOG NUMBER: S123RDIP-B560D585UB50-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	101.1	128.4	351.8	788.5	867.9
115°	112.7	140.4	338.0	741.2	850.3
117.5°	124.2	152.0	328.7	690.7	811.8
120°	136.3	163.6	322.7	642.8	761.3
122.5°	146.8	174.5	318.8	605.2	714.0
125°	156.7	185.0	315.5	571.7	670.6
127.5°	164.3	194.9	313.9	544.2	633.2
130°	171.5	203.6	312.2	518.9	602.4
132.5°	177.0	211.6	311.7	495.2	572.2
135°	183.6	219.0	311.1	470.8	543.6
137.5°	189.6	225.1	310.0	447.7	513.4
140°	195.7	230.6	309.5	425.2	481.5
142.5°	202.3	235.6	308.4	404.5	451.8
145°	209.4	239.9	307.3	386.2	424.9
147.5°	216.6	244.6	305.6	371.8	401.8
150°	223.7	248.4	303.4	359.2	382.0
152.5°	230.9	252.6	300.7	348.2	365.5
155°	238.0	256.6	297.4	338.0	352.3
157.5°	243.5	260.2	294.6	328.2	339.7
160°	250.1	263.2	291.3	319.1	327.6
162.5°	255.0	265.5	288.0	310.5	316.6
165°	260.0	267.4	284.7	302.0	307.3
167.5°	263.8	269.0	281.4	294.6	297.9
170°	267.1	269.8	278.1	288.0	289.7
172.5°	269.3	270.7	275.4	282.2	282.0
175°	271.0	271.2	273.2	277.0	276.5
177.5°	272.1	271.5	271.5	273.7	272.6
180°	271.5	271.5	271.5	271.5	271.5

(END OF REPORT)