

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013211

Luminaire Tested: S124RDIP-B1020D1035UB2750-4F0-XX-W2A-F_3500K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013211
REPORT IS A COMBINATION OF REPORTS P998832 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1020D1035UB2750-4F0-XX-W2A-F_3500K
Description: Define 4 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8274.0 lumens
Efficiency: N/A
Efficacy: 109.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 75.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013211

CATALOG NUMBER: S124RDIP-B1020D1035UB2750-4F0-XX-W2A-F_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1013211

CATALOG NUMBER: S124RDIP-B1020D1035UB2750-4F0-XX-W2A-F_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	84	84	84	69	69	69	56	56	56	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	62	60	58	50	49	48	48	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	52	49	45	43	41	41	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	31	31	31	27
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	27	27	24
6	64	52	44	38	59	48	41	36	41	36	32	35	31	28	29	26	24	24	24	21
7	59	47	39	33	54	44	37	32	38	32	28	32	28	25	27	24	21	21	21	19
8	55	42	35	30	50	40	33	28	34	29	25	29	25	22	25	21	19	19	19	17
9	51	39	31	26	47	36	30	25	32	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14699	14699	14699
5°	14700	14262	14264
10°	14576	13812	13648
15°	14375	13252	12922
20°	14113	12613	12093
25°	13785	11923	11284
30°	13464	11220	10375
35°	13112	10508	9487
40°	12692	9740	8574
45°	12298	8979	7671
50°	11851	8148	6753
55°	11367	7296	5807
60°	10831	6391	4872
65°	10312	5353	3970
70°	9575	4261	3035
75°	8631	3101	2122
80°	7210	1904	1525
85°	5421	1097	838

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 12298 cd/sqm

TEST NUMBER: P1013211

CATALOG NUMBER: S124RDIP-B1020D1035UB2750-4F0-XX-W2A-F_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	169.5	2.0
10°-20°	472.6	5.7
20°-30°	682.3	8.2
30°-40°	773.3	9.3
40°-50°	746.6	9.0
50°-60°	620.7	7.5
60°-70°	428.4	5.2
70°-80°	216.5	2.6
80°-90°	57.7	0.7
90°-100°	44.0	0.5
100°-110°	290.1	3.5
110°-120°	553.9	6.7
120°-130°	703.2	8.5
130°-140°	752.3	9.1
140°-150°	703.4	8.5
150°-160°	567.3	6.9
160°-170°	365.8	4.4
170°-180°	126.1	1.5
0°-30°	1324.4	16.0
0°-40°	2097.7	25.4
0°-60°	3465.1	41.9
0°-90°	4167.7	50.4
90°-120°	888.1	10.7
90°-150°	3047.1	36.8
90°-180°	4106.0	49.6
0°-180°	8274.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1803	1803	1803	1803	1803	
5°	1800	1794	1778	1792	1789	171
15°	1714	1702	1667	1664	1655	483
25°	1550	1525	1468	1445	1431	714
35°	1340	1296	1227	1180	1155	838
45°	1093	1042	959	892	867	843
55°	828	773	683	611	585	741
65°	563	504	415	356	340	556
75°	300	248	184	152	144	316
85°	74	47	43	40	40	82
90°	3	14	22	28	30	7
95°	55	21	22	28	29	67
105°	299	305	310	319	283	313
115°	558	561	560	562	562	549
125°	784	788	786	789	790	700
135°	973	972	976	978	980	750
145°	1122	1124	1124	1126	1128	701
155°	1230	1231	1228	1232	1229	567
165°	1297	1292	1292	1300	1291	367
175°	1327	1321	1322	1331	1319	126
180°	1327	1327	1327	1327	1327	

TEST NUMBER: P1013211

CATALOG NUMBER: S124RDIP-B1020D1035UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1802.6	1802.6	1802.6	1802.6	1802.6
2.5°	1808.1	1802.6	1787.4	1802.6	1801.2
5°	1799.8	1794.3	1777.7	1791.5	1788.8
7.5°	1787.4	1781.9	1761.2	1770.8	1766.7
10°	1768.1	1761.2	1736.3	1741.8	1736.3
12.5°	1743.2	1734.9	1704.6	1707.3	1699.0
15°	1714.2	1701.8	1667.3	1664.5	1654.9
17.5°	1681.1	1663.2	1623.1	1616.2	1602.4
20°	1641.1	1623.1	1576.2	1565.2	1547.2
22.5°	1596.9	1576.2	1525.1	1507.2	1493.4
25°	1550.0	1525.1	1468.5	1445.1	1431.3
27.5°	1501.7	1471.3	1412.0	1384.4	1365.0
30°	1450.6	1416.1	1351.2	1316.7	1294.6
32.5°	1396.8	1356.7	1289.1	1247.7	1227.0
35°	1340.2	1296.0	1227.0	1180.1	1155.2
37.5°	1280.8	1235.3	1159.4	1108.3	1083.5
40°	1217.3	1171.8	1093.1	1035.2	1010.3
42.5°	1156.6	1108.3	1025.5	966.1	939.9
45°	1093.1	1042.1	959.2	891.6	866.8
47.5°	1028.3	975.8	890.2	819.8	792.2
50°	962.0	908.2	819.8	750.8	724.6
52.5°	894.4	841.9	750.8	680.4	652.8
55°	828.1	772.9	683.2	611.4	585.2
57.5°	763.3	705.3	617.0	543.8	524.5
60°	692.9	637.7	549.3	477.6	455.5
62.5°	629.4	571.4	480.3	415.4	398.9
65°	563.1	503.8	415.4	356.1	339.5
67.5°	494.1	437.5	354.7	302.3	282.9
70°	429.2	371.3	292.6	247.1	233.3
72.5°	360.2	309.2	236.0	198.8	186.3
75°	299.5	248.4	183.6	151.8	143.5
77.5°	236.0	191.8	136.6	114.6	111.8
80°	175.3	135.3	93.9	89.7	88.3
82.5°	122.8	87.0	67.6	64.9	63.5
85°	74.5	46.9	42.8	40.0	40.0
87.5°	31.7	20.7	19.3	17.9	19.3
90°	3.0	13.9	21.8	27.8	29.8
92.5°	14.9	12.9	20.8	26.8	26.8
95°	54.6	20.8	21.8	27.8	28.8
97.5°	104.2	126.1	21.8	26.8	27.8
100°	162.8	180.6	43.7	26.8	27.8
102.5°	228.3	240.2	252.1	28.8	28.8
105°	298.8	304.7	309.7	318.6	282.9
107.5°	363.3	366.2	373.2	378.2	382.1
110°	428.8	431.8	437.7	439.7	442.7

TEST NUMBER: P1013211

CATALOG NUMBER: S124RDIP-B1020D1035UB2750-4F0-XX-W2A-F_3500K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	492.3	498.3	500.2	499.2	503.2
115°	557.8	560.8	559.8	561.8	561.8
117.5°	616.4	620.3	623.3	622.3	622.3
120°	675.9	679.9	678.9	680.9	678.9
122.5°	731.5	733.5	735.5	736.5	734.5
125°	784.1	788.1	786.1	789.1	790.1
127.5°	834.7	835.7	840.7	839.7	838.7
130°	883.4	884.3	887.3	888.3	888.3
132.5°	928.0	930.0	934.0	935.0	934.0
135°	972.7	971.7	975.7	977.6	979.6
137.5°	1012.4	1012.4	1017.3	1019.3	1018.3
140°	1051.1	1053.1	1055.1	1058.0	1059.0
142.5°	1085.8	1089.8	1090.8	1092.8	1092.8
145°	1121.6	1124.5	1124.5	1125.5	1127.5
147.5°	1149.4	1155.3	1154.3	1155.3	1156.3
150°	1180.1	1184.1	1183.1	1183.1	1184.1
152.5°	1205.9	1208.9	1206.9	1208.9	1207.9
155°	1229.7	1230.7	1227.8	1231.7	1228.8
157.5°	1250.6	1250.6	1246.6	1251.6	1246.6
160°	1268.5	1265.5	1264.5	1270.4	1264.5
162.5°	1284.3	1280.4	1279.4	1285.3	1278.4
165°	1297.2	1292.3	1292.3	1300.2	1291.3
167.5°	1308.2	1303.2	1302.2	1311.1	1301.2
170°	1317.1	1311.1	1312.1	1320.1	1310.1
172.5°	1323.0	1317.1	1318.1	1326.0	1315.1
175°	1327.0	1321.1	1322.1	1331.0	1319.1
177.5°	1330.0	1323.0	1325.0	1333.0	1321.1
180°	1327.0	1327.0	1327.0	1327.0	1327.0

(END OF REPORT)