

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012702

Luminaire Tested: S123RDIP-B775D1025UB27-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012702
REPORT IS A COMBINATION OF REPORTS P993523 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB27-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 2700K BioUP LEDs {m-DER=0.473}
{m-EER=0.52}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6365.0 lumens
Efficiency: N/A
Efficacy: 98.8 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012702

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012702

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	56	47	46	45
2	89	81	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	31	28
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13851	13851	13851
5°	13874	13360	13324
10°	13764	12858	12605
15°	13586	12238	11816
20°	13350	11562	10936
25°	13109	10861	10102
30°	12799	10114	9115
35°	12480	9381	8216
40°	12180	8585	7224
45°	11795	7806	6331
50°	11370	6974	5408
55°	10930	6085	4562
60°	10509	5172	3703
65°	9964	4234	2890
70°	9282	3203	2066
75°	8296	2168	1637
80°	7079	1506	1147
85°	5312	813	601

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11795 cd/sqm

TEST NUMBER: P1012702

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.0	1.9
10°-20°	336.5	5.3
20°-30°	484.5	7.6
30°-40°	545.6	8.6
40°-50°	521.9	8.2
50°-60°	427.2	6.7
60°-70°	288.0	4.5
70°-80°	144.5	2.3
80°-90°	40.4	0.6
90°-100°	80.3	1.3
100°-110°	243.0	3.8
110°-120°	413.6	6.5
120°-130°	544.2	8.5
130°-140°	611.7	9.6
140°-150°	601.3	9.4
150°-160°	506.3	8.0
160°-170°	337.0	5.3
170°-180°	118.0	1.9
0°-30°	942.0	14.8
0°-40°	1487.6	23.4
0°-60°	2436.7	38.3
0°-90°	2909.6	45.7
90°-120°	736.9	11.6
90°-150°	2494.0	39.2
90°-180°	3455.0	54.3
0°-180°	6365.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1287	1287	1287	1287	1287	
5°	1287	1282	1269	1278	1276	122
15°	1227	1216	1187	1181	1174	346
25°	1117	1091	1043	1021	1009	514
35°	966	929	864	819	800	605
45°	794	747	667	607	582	613
55°	603	552	463	403	382	541
65°	412	355	273	222	211	408
75°	218	168	111	100	98	232
85°	55	32	29	27	27	61
90°	1	11	24	27	29	8
95°	58	65	72	76	76	64
105°	220	222	231	231	233	236
115°	416	419	417	418	417	412
125°	609	612	610	606	602	543
135°	791	796	796	792	790	609
145°	959	961	964	963	959	599
155°	1098	1098	1099	1103	1096	506
165°	1196	1193	1193	1199	1192	337
175°	1244	1240	1240	1246	1239	118
180°	1247	1247	1247	1247	1247	

TEST NUMBER: P1012702

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1286.8	1286.8	1286.8	1286.8	1286.8
2.5°	1292.0	1287.8	1275.3	1286.8	1284.7
5°	1286.8	1281.5	1269.0	1278.4	1276.3
7.5°	1277.4	1272.1	1256.5	1262.7	1259.6
10°	1264.8	1257.5	1238.7	1239.8	1234.6
12.5°	1247.1	1238.7	1214.7	1213.7	1207.4
15°	1227.3	1215.8	1186.6	1181.3	1174.0
17.5°	1203.3	1190.7	1154.2	1143.8	1133.3
20°	1176.1	1159.4	1119.8	1106.2	1093.7
22.5°	1145.9	1126.0	1083.3	1065.5	1054.0
25°	1116.6	1090.6	1042.6	1020.6	1009.2
27.5°	1081.2	1053.0	1000.8	971.6	953.8
30°	1044.6	1013.3	954.9	919.4	902.7
32.5°	1008.1	971.6	909.0	869.3	851.6
35°	966.4	928.8	864.1	819.2	800.4
37.5°	924.6	883.9	816.1	766.0	743.0
40°	885.0	839.0	765.0	710.7	686.7
42.5°	840.1	794.2	716.9	656.4	635.5
45°	794.2	747.2	666.9	607.4	582.3
47.5°	749.3	697.1	617.8	553.1	531.2
50°	699.2	650.2	565.6	500.9	476.9
52.5°	654.3	600.1	516.6	448.7	427.9
55°	603.2	552.1	463.4	402.8	382.0
57.5°	557.3	502.0	412.2	354.8	337.1
60°	509.3	451.9	365.3	308.9	291.2
62.5°	461.3	403.9	317.3	265.1	246.3
65°	412.2	354.8	273.4	222.3	210.8
67.5°	363.2	304.7	225.4	186.8	174.3
70°	315.2	258.8	185.8	149.2	137.8
72.5°	267.2	211.8	147.1	119.0	115.8
75°	218.1	168.0	110.6	100.2	98.1
77.5°	173.2	127.3	86.6	80.4	78.3
80°	130.4	87.7	65.7	62.6	60.5
82.5°	89.7	54.3	47.0	43.8	43.8
85°	55.3	32.4	29.2	27.1	27.1
87.5°	25.0	13.6	13.6	12.5	11.5
90°	1.0	10.8	23.5	27.4	29.4
92.5°	29.4	35.3	41.1	44.1	42.1
95°	57.8	64.7	72.5	76.4	76.4
97.5°	95.0	99.9	105.8	110.7	109.7
100°	133.2	139.1	144.0	146.9	148.9
102.5°	177.3	180.2	187.1	190.0	189.1
105°	220.4	222.4	231.2	231.2	233.1
107.5°	271.4	272.3	276.3	279.2	278.2
110°	318.4	320.3	322.3	326.2	324.3

TEST NUMBER: P1012702

CATALOG NUMBER: S123RDIP-B775D1025UB27-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	367.4	368.3	368.3	373.2	373.2
115°	416.3	419.3	417.3	418.3	417.3
117.5°	466.3	467.3	465.3	465.3	462.4
120°	512.3	518.2	513.3	512.3	510.4
122.5°	560.3	564.3	562.3	559.4	556.4
125°	609.3	612.3	610.3	606.4	602.5
127.5°	654.4	660.3	658.3	652.4	648.5
130°	699.4	707.3	704.3	700.4	693.6
132.5°	744.5	752.3	750.4	745.5	740.6
135°	790.6	796.4	795.5	791.5	789.6
137.5°	832.7	837.6	840.5	835.6	832.7
140°	876.8	881.7	882.6	881.7	874.8
142.5°	916.9	921.8	923.8	922.8	917.9
145°	959.0	961.0	963.9	963.0	959.0
147.5°	995.3	999.2	1002.2	1002.2	996.3
150°	1033.5	1035.5	1037.4	1037.4	1031.5
152.5°	1064.8	1067.8	1068.8	1070.7	1065.8
155°	1098.2	1098.2	1099.1	1103.1	1096.2
157.5°	1126.6	1125.6	1126.6	1130.5	1124.6
160°	1153.0	1151.1	1151.1	1156.0	1152.0
162.5°	1176.5	1173.6	1174.6	1179.5	1172.6
165°	1196.1	1193.2	1193.2	1199.1	1192.2
167.5°	1212.8	1208.9	1209.8	1215.7	1209.8
170°	1226.5	1222.6	1222.6	1229.4	1222.6
172.5°	1237.3	1233.3	1233.3	1239.2	1232.4
175°	1244.1	1240.2	1240.2	1246.1	1239.2
177.5°	1248.0	1244.1	1244.1	1250.0	1243.1
180°	1247.1	1247.1	1247.1	1247.1	1247.1

(END OF REPORT)