

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012708

Luminaire Tested: S123RDIP-B775D1025UB30-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012708
REPORT IS A COMBINATION OF REPORTS P993539 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB30-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6420.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012708

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012708

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	56	47	46	45
2	89	81	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	31	28
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13969	13969	13969
5°	13992	13475	13439
10°	13882	12969	12713
15°	13702	12343	11918
20°	13465	11661	11030
25°	13221	10953	10188
30°	12909	10201	9194
35°	12588	9461	8287
40°	12284	8657	7286
45°	11896	7873	6386
50°	11467	7034	5455
55°	11024	6136	4601
60°	10600	5216	3735
65°	10051	4272	2915
70°	9362	3230	2083
75°	8369	2188	1650
80°	7145	1520	1157
85°	5360	821	607

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11896 cd/sqm

TEST NUMBER: P1012708

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.0	1.9
10°-20°	339.4	5.3
20°-30°	488.7	7.6
30°-40°	550.3	8.6
40°-50°	526.4	8.2
50°-60°	430.9	6.7
60°-70°	290.5	4.5
70°-80°	145.7	2.3
80°-90°	40.8	0.6
90°-100°	81.0	1.3
100°-110°	245.1	3.8
110°-120°	417.2	6.5
120°-130°	548.9	8.5
130°-140°	617.0	9.6
140°-150°	606.5	9.4
150°-160°	510.6	8.0
160°-170°	340.0	5.3
170°-180°	119.0	1.9
0°-30°	950.1	14.8
0°-40°	1500.4	23.4
0°-60°	2457.7	38.3
0°-90°	2934.7	45.7
90°-120°	743.3	11.6
90°-150°	2515.7	39.2
90°-180°	3485.0	54.3
0°-180°	6420.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1298	1298	1298	1298	1298	
5°	1298	1293	1280	1289	1287	123
15°	1238	1226	1197	1192	1184	349
25°	1126	1100	1052	1029	1018	518
35°	975	937	872	826	807	610
45°	801	754	673	613	587	618
55°	608	557	467	406	385	546
65°	416	358	276	224	213	411
75°	220	170	112	101	99	234
85°	56	33	30	27	27	61
90°	1	11	24	28	30	8
95°	58	65	73	77	77	64
105°	222	224	233	233	235	238
115°	420	423	421	422	421	416
125°	615	618	616	612	608	548
135°	797	803	802	798	796	614
145°	967	969	972	971	967	604
155°	1108	1108	1109	1113	1106	510
165°	1206	1204	1204	1210	1202	340
175°	1255	1251	1251	1257	1250	119
180°	1258	1258	1258	1258	1258	

TEST NUMBER: P1012708

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1297.8	1297.8	1297.8	1297.8	1297.8
2.5°	1303.1	1298.9	1286.2	1297.8	1295.7
5°	1297.8	1292.6	1279.9	1289.4	1287.3
7.5°	1288.3	1283.1	1267.3	1273.6	1270.5
10°	1275.7	1268.3	1249.4	1250.5	1245.2
12.5°	1257.8	1249.4	1225.2	1224.1	1217.8
15°	1237.8	1226.2	1196.8	1191.5	1184.1
17.5°	1213.6	1201.0	1164.1	1153.6	1143.1
20°	1186.2	1169.4	1129.4	1115.7	1103.1
22.5°	1155.7	1135.7	1092.6	1074.7	1063.1
25°	1126.2	1099.9	1051.5	1029.4	1017.8
27.5°	1090.5	1062.0	1009.4	979.9	962.0
30°	1053.6	1022.0	963.1	927.3	910.5
32.5°	1016.8	979.9	916.8	876.8	858.9
35°	974.7	936.8	871.5	826.3	807.3
37.5°	932.6	891.5	823.1	772.6	749.4
40°	892.6	846.3	771.5	716.8	692.6
42.5°	847.3	801.0	723.1	662.1	641.0
45°	801.0	753.6	672.6	612.6	587.3
47.5°	755.7	703.1	623.1	557.9	535.8
50°	705.2	655.8	570.5	505.2	481.0
52.5°	660.0	605.2	521.0	452.6	431.6
55°	608.4	556.8	467.3	406.3	385.2
57.5°	562.1	506.3	415.8	357.9	340.0
60°	513.7	455.8	368.4	311.6	293.7
62.5°	465.2	407.3	320.0	267.4	248.4
65°	415.8	357.9	275.8	224.2	212.6
67.5°	366.3	307.4	227.4	188.4	175.8
70°	317.9	261.0	187.4	150.5	138.9
72.5°	269.5	213.7	148.4	120.0	116.8
75°	220.0	169.5	111.6	101.0	98.9
77.5°	174.7	128.4	87.4	81.0	78.9
80°	131.6	88.4	66.3	63.2	61.0
82.5°	90.5	54.7	47.4	44.2	44.2
85°	55.8	32.6	29.5	27.4	27.4
87.5°	25.3	13.7	13.7	12.6	11.6
90°	1.0	10.9	23.7	27.7	29.6
92.5°	29.6	35.6	41.5	44.5	42.5
95°	58.3	65.2	73.1	77.1	77.1
97.5°	95.8	100.8	106.7	111.7	110.7
100°	134.4	140.3	145.3	148.2	150.2
102.5°	178.8	181.8	188.7	191.7	190.7
105°	222.3	224.3	233.2	233.2	235.2
107.5°	273.7	274.7	278.6	281.6	280.6
110°	321.1	323.1	325.1	329.0	327.1

TEST NUMBER: P1012708

CATALOG NUMBER: S123RDIP-B775D1025UB30-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	370.5	371.5	371.5	376.5	376.5
115°	420.0	422.9	420.9	421.9	420.9
117.5°	470.3	471.3	469.4	469.4	466.4
120°	516.8	522.7	517.8	516.8	514.8
122.5°	565.2	569.2	567.2	564.2	561.3
125°	614.6	617.6	615.6	611.6	607.7
127.5°	660.1	666.0	664.0	658.1	654.1
130°	705.5	713.4	710.5	706.5	699.6
132.5°	751.0	758.9	756.9	752.0	747.0
135°	797.4	803.3	802.4	798.4	796.4
137.5°	839.9	844.8	847.8	842.9	839.9
140°	884.4	889.3	890.3	889.3	882.4
142.5°	924.9	929.8	931.8	930.8	925.9
145°	967.4	969.3	972.3	971.3	967.4
147.5°	1003.9	1007.9	1010.8	1010.8	1004.9
150°	1042.5	1044.4	1046.4	1046.4	1040.5
152.5°	1074.1	1077.0	1078.0	1080.0	1075.1
155°	1107.7	1107.7	1108.7	1112.6	1105.7
157.5°	1136.3	1135.3	1136.3	1140.3	1134.4
160°	1163.0	1161.0	1161.0	1166.0	1162.0
162.5°	1186.7	1183.8	1184.8	1189.7	1182.8
165°	1206.5	1203.5	1203.5	1209.5	1202.5
167.5°	1223.3	1219.3	1220.3	1226.3	1220.3
170°	1237.1	1233.2	1233.2	1240.1	1233.2
172.5°	1248.0	1244.0	1244.0	1250.0	1243.1
175°	1254.9	1251.0	1251.0	1256.9	1250.0
177.5°	1258.9	1254.9	1254.9	1260.8	1253.9
180°	1257.9	1257.9	1257.9	1257.9	1257.9

(END OF REPORT)