

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012714

Luminaire Tested: S123RDIP-B775D1025UB35-4F0-XX-W2A-F1

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012714
REPORT IS A COMBINATION OF REPORTS P993545 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB35-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6448.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012714

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012714

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52
1	97	93	89	86	89	85	82	79	71	69	67	58	57	56	47	46	45
2	89	81	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	31	28
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14032	14032	14032
5°	14055	13535	13499
10°	13944	13026	12769
15°	13763	12397	11971
20°	13525	11713	11079
25°	13280	11002	10233
30°	12967	10246	9234
35°	12643	9503	8324
40°	12338	8697	7319
45°	11949	7908	6414
50°	11518	7065	5479
55°	11073	6164	4621
60°	10645	5239	3752
65°	10095	4290	2928
70°	9403	3244	2093
75°	8407	2197	1658
80°	7177	1527	1163
85°	5379	824	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11949 cd/sqm

TEST NUMBER: P1012714

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	1.9
10°-20°	340.9	5.3
20°-30°	490.8	7.6
30°-40°	552.8	8.6
40°-50°	528.7	8.2
50°-60°	432.8	6.7
60°-70°	291.8	4.5
70°-80°	146.4	2.3
80°-90°	40.9	0.6
90°-100°	81.3	1.3
100°-110°	246.1	3.8
110°-120°	419.0	6.5
120°-130°	551.2	8.5
130°-140°	619.6	9.6
140°-150°	609.2	9.4
150°-160°	512.8	8.0
160°-170°	341.4	5.3
170°-180°	119.6	1.9
0°-30°	954.3	14.8
0°-40°	1507.0	23.4
0°-60°	2468.6	38.3
0°-90°	2947.7	45.7
90°-120°	746.5	11.6
90°-150°	2526.5	39.2
90°-180°	3500.0	54.3
0°-180°	6448.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1243	1232	1202	1197	1189	350
25°	1131	1105	1056	1034	1022	520
35°	979	941	875	830	811	613
45°	805	757	676	615	590	621
55°	611	559	469	408	387	548
65°	418	360	277	225	214	413
75°	221	170	112	102	99	235
85°	56	33	30	28	28	61
90°	1	11	24	28	30	8
95°	58	66	73	77	77	65
105°	223	225	234	234	236	239
115°	422	425	423	424	423	417
125°	617	620	618	614	610	550
135°	801	807	806	802	800	617
145°	972	974	976	976	972	607
155°	1112	1112	1113	1117	1110	512
165°	1212	1209	1209	1215	1208	342
175°	1260	1256	1256	1262	1255	120
180°	1263	1263	1263	1263	1263	

TEST NUMBER: P1012714

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1303.6	1303.6	1303.6	1303.6	1303.6
2.5°	1308.9	1304.6	1291.9	1303.6	1301.5
5°	1303.6	1298.3	1285.6	1295.1	1293.0
7.5°	1294.1	1288.8	1272.9	1279.3	1276.1
10°	1281.4	1274.0	1254.9	1256.0	1250.7
12.5°	1263.4	1254.9	1230.6	1229.6	1223.2
15°	1243.3	1231.7	1202.1	1196.8	1189.4
17.5°	1219.0	1206.3	1169.3	1158.7	1148.2
20°	1191.5	1174.6	1134.4	1120.7	1108.0
22.5°	1160.8	1140.8	1097.4	1079.4	1067.8
25°	1131.2	1104.8	1056.2	1034.0	1022.3
27.5°	1095.3	1066.8	1013.9	984.3	966.3
30°	1058.3	1026.6	967.4	931.4	914.5
32.5°	1021.3	984.3	920.9	880.7	862.7
35°	979.0	940.9	875.4	829.9	810.9
37.5°	936.7	895.5	826.8	776.0	752.8
40°	896.5	850.0	775.0	720.0	695.7
42.5°	851.1	804.6	726.3	665.0	643.9
45°	804.6	757.0	675.6	615.3	589.9
47.5°	759.1	706.2	625.9	560.3	538.1
50°	708.3	658.7	573.0	507.5	483.2
52.5°	662.9	607.9	523.3	454.6	433.5
55°	611.1	559.3	469.4	408.1	386.9
57.5°	564.6	508.5	417.6	359.5	341.5
60°	515.9	457.8	370.0	312.9	295.0
62.5°	467.3	409.2	321.4	268.5	249.5
65°	417.6	359.5	277.0	225.2	213.6
67.5°	367.9	308.7	228.4	189.2	176.6
70°	319.3	262.2	188.2	151.2	139.6
72.5°	270.7	214.6	149.1	120.5	117.4
75°	221.0	170.2	112.1	101.5	99.4
77.5°	175.5	129.0	87.8	81.4	79.3
80°	132.2	88.8	66.6	63.4	61.3
82.5°	90.9	55.0	47.6	44.4	44.4
85°	56.0	32.8	29.6	27.5	27.5
87.5°	25.4	13.7	13.7	12.7	11.6
90°	1.0	10.9	23.8	27.8	29.8
92.5°	29.8	35.7	41.7	44.7	42.7
95°	58.5	65.5	73.4	77.4	77.4
97.5°	96.3	101.2	107.2	112.1	111.1
100°	135.0	140.9	145.9	148.9	150.8
102.5°	179.6	182.6	189.5	192.5	191.5
105°	223.3	225.3	234.2	234.2	236.2
107.5°	274.9	275.9	279.8	282.8	281.8
110°	322.5	324.5	326.5	330.5	328.5



TEST NUMBER: P1012714

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	372.1	373.1	373.1	378.1	378.1
115°	421.8	424.7	422.7	423.7	422.7
117.5°	472.4	473.4	471.4	471.4	468.4
120°	519.0	525.0	520.0	519.0	517.0
122.5°	567.6	571.6	569.6	566.6	563.7
125°	617.3	620.2	618.2	614.3	610.3
127.5°	662.9	668.9	666.9	660.9	656.9
130°	708.6	716.5	713.5	709.5	702.6
132.5°	754.2	762.1	760.2	755.2	750.2
135°	800.8	806.8	805.8	801.8	799.8
137.5°	843.5	848.5	851.5	846.5	843.5
140°	888.2	893.1	894.1	893.1	886.2
142.5°	928.9	933.8	935.8	934.8	929.8
145°	971.5	973.5	976.5	975.5	971.5
147.5°	1008.2	1012.2	1015.2	1015.2	1009.2
150°	1046.9	1048.9	1050.9	1050.9	1045.0
152.5°	1078.7	1081.7	1082.7	1084.7	1079.7
155°	1112.4	1112.4	1113.4	1117.4	1110.5
157.5°	1141.2	1140.2	1141.2	1145.2	1139.2
160°	1168.0	1166.0	1166.0	1171.0	1167.0
162.5°	1191.8	1188.9	1189.8	1194.8	1187.9
165°	1211.7	1208.7	1208.7	1214.7	1207.7
167.5°	1228.6	1224.6	1225.6	1231.5	1225.6
170°	1242.4	1238.5	1238.5	1245.4	1238.5
172.5°	1253.4	1249.4	1249.4	1255.3	1248.4
175°	1260.3	1256.3	1256.3	1262.3	1255.3
177.5°	1264.3	1260.3	1260.3	1266.3	1259.3
180°	1263.3	1263.3	1263.3	1263.3	1263.3

(END OF REPORT)