

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012715

Luminaire Tested: S123RDIP-B775D1025UB35-4F0-XX-W2A-F4

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012715
REPORT IS A COMBINATION OF REPORTS P993546 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB35-4F0-XX-W2A-F4
Description: Define 3 Regressed Direct/Indirect Pendant with 3500K BioUP LEDs {m-DER=0.721}
{m-EER=0.792}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6644.6 lumens
Efficiency: N/A
Efficacy: 103.2 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012715

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F4

Luminous Intensity Polar Plot



TEST NUMBER: P1012715

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F4

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51
1	97	93	89	86	89	85	82	79	71	68	66	58	56	55	45	44	44
2	88	81	75	70	81	75	70	65	62	59	55	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28
5	68	57	49	43	62	52	45	40	44	39	35	36	33	29	29	26	24
6	63	51	43	37	57	47	40	35	40	34	30	33	29	26	27	24	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	27	33	28	24	28	23	21	22	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	19	21	18	16
10	47	35	28	23	43	33	26	22	28	23	19	23	20	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14032	14032	14032
5°	14055	13535	13499
10°	13944	13026	12769
15°	13763	12397	11971
20°	13525	11713	11079
25°	13280	11002	10233
30°	12967	10246	9234
35°	12643	9503	8324
40°	12338	8697	7319
45°	11949	7908	6414
50°	11518	7065	5479
55°	11073	6164	4621
60°	10645	5239	3752
65°	10095	4290	2928
70°	9403	3244	2093
75°	8407	2197	1658
80°	7177	1527	1163
85°	5379	824	610

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11949 cd/sqm

TEST NUMBER: P1012715

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F4

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	1.8
10°-20°	340.9	5.1
20°-30°	490.8	7.4
30°-40°	552.8	8.3
40°-50°	528.7	8.0
50°-60°	432.8	6.5
60°-70°	291.8	4.4
70°-80°	146.4	2.2
80°-90°	41.0	0.6
90°-100°	278.6	4.2
100°-110°	778.8	11.7
110°-120°	759.4	11.4
120°-130°	604.7	9.1
130°-140°	477.3	7.2
140°-150°	356.1	5.4
150°-160°	248.4	3.7
160°-170°	145.9	2.2
170°-180°	47.5	0.7
0°-30°	954.3	14.4
0°-40°	1507.0	22.7
0°-60°	2468.6	37.2
0°-90°	2947.8	44.4
90°-120°	1816.8	27.3
90°-150°	3255.0	49.0
90°-180°	3697.0	55.6
0°-180°	6644.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1304	1304	1304	1304	1304	
5°	1304	1298	1286	1295	1293	124
15°	1243	1232	1202	1197	1189	350
25°	1131	1105	1056	1034	1022	520
35°	979	941	875	830	811	613
45°	805	757	676	615	590	621
55°	611	559	469	408	387	548
65°	418	360	277	225	214	413
75°	221	170	112	102	99	235
85°	56	33	30	28	28	61
90°	2	12	25	28	29	6
95°	34	110	589	172	115	36
105°	115	170	798	1396	1262	122
115°	204	254	610	1338	1536	201
125°	283	334	570	1032	1211	251
135°	332	396	562	850	982	256
145°	378	433	555	697	767	237
155°	430	464	537	610	636	198
165°	470	483	514	545	555	132
175°	489	490	493	500	499	46
180°	490	490	490	490	490	

TEST NUMBER: P1012715

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1303.6	1303.6	1303.6	1303.6	1303.6
2.5°	1308.9	1304.6	1291.9	1303.6	1301.5
5°	1303.6	1298.3	1285.6	1295.1	1293.0
7.5°	1294.1	1288.8	1272.9	1279.3	1276.1
10°	1281.4	1274.0	1254.9	1256.0	1250.7
12.5°	1263.4	1254.9	1230.6	1229.6	1223.2
15°	1243.3	1231.7	1202.1	1196.8	1189.4
17.5°	1219.0	1206.3	1169.3	1158.7	1148.2
20°	1191.5	1174.6	1134.4	1120.7	1108.0
22.5°	1160.8	1140.8	1097.4	1079.4	1067.8
25°	1131.2	1104.8	1056.2	1034.0	1022.3
27.5°	1095.3	1066.8	1013.9	984.3	966.3
30°	1058.3	1026.6	967.4	931.4	914.5
32.5°	1021.3	984.3	920.9	880.7	862.7
35°	979.0	940.9	875.4	829.9	810.9
37.5°	936.7	895.5	826.8	776.0	752.8
40°	896.5	850.0	775.0	720.0	695.7
42.5°	851.1	804.6	726.3	665.0	643.9
45°	804.6	757.0	675.6	615.3	589.9
47.5°	759.1	706.2	625.9	560.3	538.1
50°	708.3	658.7	573.0	507.5	483.2
52.5°	662.9	607.9	523.3	454.6	433.5
55°	611.1	559.3	469.4	408.1	386.9
57.5°	564.6	508.5	417.6	359.5	341.5
60°	515.9	457.8	370.0	312.9	295.0
62.5°	467.3	409.2	321.4	268.5	249.5
65°	417.6	359.5	277.0	225.2	213.6
67.5°	367.9	308.7	228.4	189.2	176.6
70°	319.3	262.2	188.2	151.2	139.6
72.5°	270.7	214.6	149.1	120.5	117.4
75°	221.0	170.2	112.1	101.5	99.4
77.5°	175.5	129.0	87.8	81.4	79.3
80°	132.2	88.8	66.6	63.4	61.3
82.5°	90.9	55.0	47.6	44.4	44.4
85°	56.0	32.8	29.6	27.5	27.5
87.5°	25.4	13.7	13.7	12.7	11.6
90°	2.0	11.9	24.8	27.8	28.8
92.5°	14.9	59.6	184.6	63.0	52.6
95°	33.7	109.6	588.6	171.7	115.1
97.5°	53.6	125.6	905.2	431.8	236.2
100°	73.4	138.4	940.0	903.2	622.3
102.5°	94.3	153.4	875.4	1209.4	985.6
105°	115.1	170.2	798.0	1395.5	1262.5
107.5°	137.0	190.1	729.5	1477.4	1443.2
110°	160.8	210.4	673.0	1480.0	1546.4

TEST NUMBER: P1012715

CATALOG NUMBER: S123RDIP-B775D1025UB35-4F0-XX-W2A-F4

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	182.6	231.8	635.2	1423.8	1567.3
115°	203.5	253.6	610.4	1338.5	1535.5
117.5°	224.3	274.4	593.6	1247.2	1466.0
120°	246.2	295.3	582.6	1160.8	1374.7
122.5°	265.0	315.1	575.7	1092.8	1289.3
125°	282.9	334.0	569.7	1032.3	1210.9
127.5°	296.8	351.9	566.8	982.6	1143.4
130°	309.7	367.7	563.8	937.0	1087.8
132.5°	319.6	382.1	562.8	894.3	1033.3
135°	331.5	395.5	561.8	850.1	981.6
137.5°	342.4	406.4	559.8	808.4	927.1
140°	353.4	416.4	558.8	767.8	869.5
142.5°	365.3	425.3	556.8	730.6	815.9
145°	378.2	433.2	554.8	697.3	767.3
147.5°	391.1	441.7	551.9	671.4	725.6
150°	404.0	448.6	547.9	648.7	689.8
152.5°	416.9	456.0	542.9	628.8	660.1
155°	429.8	463.6	537.0	610.4	636.2
157.5°	439.7	470.0	532.0	592.6	613.4
160°	451.6	475.4	526.1	576.2	591.6
162.5°	460.5	479.4	520.1	560.8	571.7
165°	469.5	482.9	514.1	545.4	554.8
167.5°	476.4	485.8	508.2	532.0	538.0
170°	482.4	487.4	502.2	520.1	523.1
172.5°	486.4	488.8	497.3	509.7	509.2
175°	489.3	489.8	493.3	500.3	499.3
177.5°	491.3	490.3	490.3	494.3	492.3
180°	490.3	490.3	490.3	490.3	490.3

(END OF REPORT)