

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013268

Luminaire Tested: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_3000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013268
REPORT IS A COMBINATION OF REPORTS P999071 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_3000K
Description: Define 4 Regressed Direct/Indirect Pendant with 3000K BioUP LEDs {m-DER=0.589}
{m-EER=0.647}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9636.0 lumens
Efficiency: N/A
Efficacy: 100.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013268

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013268

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	43	41
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	24	21
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	20	17
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17042	17042	17042
5°	17044	16536	16538
10°	16899	16014	15824
15°	16667	15365	14981
20°	16362	14624	14021
25°	15983	13825	13083
30°	15611	13009	12029
35°	15202	12183	11000
40°	14716	11293	9942
45°	14259	10411	8895
50°	13741	9447	7830
55°	13180	8459	6733
60°	12557	7410	5648
65°	11957	6207	4604
70°	11104	4941	3518
75°	10008	3594	2460
80°	8357	2207	1769
85°	6287	1271	973

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 14259 cd/sqm

TEST NUMBER: P1013268

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	196.5	2.0
10°-20°	547.9	5.7
20°-30°	791.1	8.2
30°-40°	896.6	9.3
40°-50°	865.7	9.0
50°-60°	719.7	7.5
60°-70°	496.8	5.2
70°-80°	251.0	2.6
80°-90°	66.9	0.7
90°-100°	51.5	0.5
100°-110°	339.4	3.5
110°-120°	648.0	6.7
120°-130°	822.7	8.5
130°-140°	880.1	9.1
140°-150°	823.0	8.5
150°-160°	663.6	6.9
160°-170°	428.0	4.4
170°-180°	147.5	1.5
0°-30°	1535.6	15.9
0°-40°	2432.1	25.2
0°-60°	4017.5	41.7
0°-90°	4832.2	50.1
90°-120°	1039.0	10.8
90°-150°	3564.7	37.0
90°-180°	4804.0	49.9
0°-180°	9636.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2090	2090	2090	2090	2090	
5°	2087	2080	2061	2077	2074	198
15°	1988	1973	1933	1930	1919	560
25°	1797	1768	1703	1676	1660	828
35°	1554	1503	1423	1368	1339	971
45°	1267	1208	1112	1034	1005	977
55°	960	896	792	709	678	859
65°	653	584	482	413	394	645
75°	347	288	213	176	166	366
85°	86	54	50	46	46	95
90°	4	16	26	32	35	8
95°	64	24	26	32	34	79
105°	350	356	362	373	331	366
115°	653	656	655	657	657	642
125°	917	922	920	923	924	819
135°	1138	1137	1141	1144	1146	877
145°	1312	1316	1316	1317	1319	820
155°	1439	1440	1436	1441	1438	663
165°	1518	1512	1512	1521	1511	429
175°	1552	1546	1547	1557	1543	148
180°	1552	1552	1552	1552	1552	

TEST NUMBER: P1013268

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2089.9	2089.9	2089.9	2089.9	2089.9
2.5°	2096.3	2089.9	2072.3	2089.9	2088.3
5°	2086.7	2080.3	2061.1	2077.1	2073.9
7.5°	2072.3	2065.9	2041.9	2053.1	2048.3
10°	2049.9	2041.9	2013.1	2019.5	2013.1
12.5°	2021.1	2011.5	1976.3	1979.5	1969.9
15°	1987.5	1973.1	1933.1	1929.9	1918.7
17.5°	1949.1	1928.3	1881.9	1873.9	1857.9
20°	1902.7	1881.9	1827.5	1814.7	1793.9
22.5°	1851.5	1827.5	1768.3	1747.5	1731.5
25°	1797.1	1768.3	1702.7	1675.5	1659.5
27.5°	1741.1	1705.9	1637.1	1605.1	1582.6
30°	1681.9	1641.9	1566.6	1526.6	1501.0
32.5°	1619.5	1573.0	1494.6	1446.6	1422.6
35°	1553.8	1502.6	1422.6	1368.2	1339.4
37.5°	1485.0	1432.2	1344.2	1285.0	1256.2
40°	1411.4	1358.6	1267.4	1200.2	1171.4
42.5°	1341.0	1285.0	1189.0	1120.2	1089.8
45°	1267.4	1208.2	1112.2	1033.8	1005.0
47.5°	1192.2	1131.4	1032.2	950.5	918.5
50°	1115.4	1053.0	950.5	870.5	840.1
52.5°	1037.0	976.2	870.5	788.9	756.9
55°	960.2	896.1	792.1	708.9	678.5
57.5°	884.9	817.7	715.3	630.5	608.1
60°	803.3	739.3	636.9	553.7	528.1
62.5°	729.7	662.5	556.9	481.7	462.5
65°	652.9	584.1	481.7	412.9	393.7
67.5°	572.9	507.3	411.3	350.5	328.1
70°	497.7	430.5	339.3	286.4	270.4
72.5°	417.7	358.5	273.6	230.4	216.0
75°	347.3	288.0	212.8	176.0	166.4
77.5°	273.6	222.4	158.4	132.8	129.6
80°	203.2	156.8	108.8	104.0	102.4
82.5°	142.4	100.8	78.4	75.2	73.6
85°	86.4	54.4	49.6	46.4	46.4
87.5°	36.8	24.0	22.4	20.8	22.4
90°	3.5	16.3	25.5	32.5	34.8
92.5°	17.4	15.1	24.4	31.4	31.4
95°	63.9	24.4	25.5	32.5	33.7
97.5°	121.9	147.5	25.5	31.4	32.5
100°	190.4	211.3	51.1	31.4	32.5
102.5°	267.1	281.0	294.9	33.7	33.7
105°	349.5	356.5	362.3	372.7	330.9
107.5°	425.0	428.5	436.6	442.4	447.0
110°	501.6	505.1	512.1	514.4	517.9

TEST NUMBER: P1013268

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_3000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	575.9	582.9	585.2	584.1	588.7
115°	652.6	656.0	654.9	657.2	657.2
117.5°	721.1	725.7	729.2	728.0	728.0
120°	790.7	795.4	794.2	796.5	794.2
122.5°	855.8	858.1	860.4	861.6	859.2
125°	917.3	921.9	919.6	923.1	924.3
127.5°	976.5	977.7	983.5	982.3	981.2
130°	1033.4	1034.6	1038.1	1039.2	1039.2
132.5°	1085.7	1088.0	1092.6	1093.8	1092.6
135°	1137.9	1136.8	1141.4	1143.7	1146.0
137.5°	1184.4	1184.4	1190.2	1192.5	1191.3
140°	1229.6	1232.0	1234.3	1237.8	1238.9
142.5°	1270.3	1274.9	1276.1	1278.4	1278.4
145°	1312.1	1315.6	1315.6	1316.7	1319.1
147.5°	1344.6	1351.6	1350.4	1351.6	1352.7
150°	1380.6	1385.2	1384.1	1384.1	1385.2
152.5°	1410.8	1414.3	1411.9	1414.3	1413.1
155°	1438.6	1439.8	1436.3	1441.0	1437.5
157.5°	1463.0	1463.0	1458.4	1464.2	1458.4
160°	1483.9	1480.4	1479.3	1486.3	1479.3
162.5°	1502.5	1497.9	1496.7	1503.7	1495.5
165°	1517.6	1511.8	1511.8	1521.1	1510.6
167.5°	1530.4	1524.6	1523.4	1533.9	1522.2
170°	1540.8	1533.9	1535.0	1544.3	1532.7
172.5°	1547.8	1540.8	1542.0	1551.3	1538.5
175°	1552.4	1545.5	1546.6	1557.1	1543.1
177.5°	1555.9	1547.8	1550.1	1559.4	1545.5
180°	1552.4	1552.4	1552.4	1552.4	1552.4

(END OF REPORT)