

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1012720

Luminaire Tested: S123RDIP-B775D1025UB40-4F0-XX-W2A-F1

Issue Date: 5/6/2025

Test Information

Test Method: LM-79-2019
Report Number: P1012720
REPORT IS A COMBINATION OF REPORTS P993551 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/6/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S123RDIP-B775D1025UB40-4F0-XX-W2A-F1
Description: Define 3 Regressed Direct/Indirect Pendant with 4000K BioUP LEDs {m-DER=0.865}
{m-EER=0.951}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6384.0 lumens
Efficiency: N/A
Efficacy: 99.1 lumens/watt
Spacing Criteria (0/90/45): 1.21 / 1.07 / 1.22
Luminous Opening: Rectangular w/ Sides (W: 0.25' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1012720

CATALOG NUMBER: S123RDIP-B775D1025UB40-4F0-XX-W2A-F1

Luminous Intensity Polar Plot



TEST NUMBER: P1012720

CATALOG NUMBER: S123RDIP-B775D1025UB40-4F0-XX-W2A-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46		
1	97	93	89	86	89	85	82	79	71	69	67	58	57	56	47	46	45	39		
2	89	81	76	71	81	75	70	66	63	59	56	52	49	47	41	40	38	33		
3	81	72	65	59	74	66	60	55	56	51	47	46	43	40	37	35	33	28		
4	74	64	56	50	68	59	52	47	50	45	41	41	37	34	33	31	28	25		
5	68	57	49	43	62	53	46	40	45	39	35	37	33	30	30	27	25	22		
6	63	51	43	37	58	47	40	35	40	35	31	34	29	26	27	24	22	19		
7	58	46	38	33	53	43	36	31	36	31	27	31	26	23	25	22	20	17		
8	54	42	34	29	50	39	32	27	33	28	24	28	24	21	23	20	18	15		
9	50	38	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14		
10	47	35	28	23	43	33	26	22	28	23	20	24	20	17	20	17	15	13		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13889	13889	13889
5°	13911	13397	13361
10°	13802	12894	12640
15°	13622	12271	11849
20°	13388	11594	10966
25°	13145	10890	10129
30°	12834	10141	9140
35°	12514	9407	8239
40°	12213	8608	7244
45°	11827	7827	6349
50°	11401	6993	5423
55°	10960	6101	4574
60°	10538	5186	3713
65°	9993	4247	2898
70°	9306	3212	2071
75°	8319	2174	1642
80°	7101	1511	1151
85°	5331	816	603

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11827 cd/sqm

TEST NUMBER: P1012720

CATALOG NUMBER: S123RDIP-B775D1025UB40-4F0-XX-W2A-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.3	1.9
10°-20°	337.4	5.3
20°-30°	485.8	7.6
30°-40°	547.1	8.6
40°-50°	523.3	8.2
50°-60°	428.4	6.7
60°-70°	288.8	4.5
70°-80°	144.9	2.3
80°-90°	40.5	0.6
90°-100°	80.5	1.3
100°-110°	243.7	3.8
110°-120°	415.0	6.5
120°-130°	545.9	8.6
130°-140°	613.6	9.6
140°-150°	603.2	9.4
150°-160°	507.9	8.0
160°-170°	338.1	5.3
170°-180°	118.4	1.9
0°-30°	944.5	14.8
0°-40°	1491.7	23.4
0°-60°	2443.4	38.3
0°-90°	2917.7	45.7
90°-120°	739.2	11.6
90°-150°	2502.0	39.2
90°-180°	3466.0	54.3
0°-180°	6384.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1290	1290	1290	1290	1290	
5°	1290	1285	1272	1282	1280	122
15°	1231	1219	1190	1185	1177	347
25°	1120	1094	1045	1023	1012	515
35°	969	931	866	822	803	607
45°	796	749	669	609	584	615
55°	605	554	465	404	383	542
65°	413	356	274	223	211	409
75°	219	168	111	100	98	233
85°	56	32	29	27	27	61
90°	1	11	24	28	30	8
95°	58	65	73	77	77	64
105°	221	223	232	232	234	237
115°	418	421	419	420	419	413
125°	611	614	612	608	604	545
135°	793	799	798	794	792	611
145°	962	964	967	966	962	601
155°	1102	1102	1103	1107	1100	507
165°	1200	1197	1197	1203	1196	338
175°	1248	1244	1244	1250	1243	119
180°	1251	1251	1251	1251	1251	

TEST NUMBER: P1012720

CATALOG NUMBER: S123RDIP-B775D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1290.3	1290.3	1290.3	1290.3	1290.3
2.5°	1295.5	1291.3	1278.8	1290.3	1288.2
5°	1290.3	1285.1	1272.5	1281.9	1279.8
7.5°	1280.9	1275.6	1259.9	1266.2	1263.1
10°	1268.3	1261.0	1242.2	1243.2	1238.0
12.5°	1250.5	1242.2	1218.1	1217.0	1210.8
15°	1230.6	1219.1	1189.8	1184.6	1177.3
17.5°	1206.6	1194.0	1157.4	1146.9	1136.5
20°	1179.4	1162.6	1122.9	1109.3	1096.7
22.5°	1149.0	1129.1	1086.2	1068.4	1056.9
25°	1119.7	1093.6	1045.4	1023.4	1011.9
27.5°	1084.1	1055.9	1003.6	974.3	956.5
30°	1047.5	1016.1	957.5	921.9	905.2
32.5°	1010.9	974.3	911.5	871.7	853.9
35°	969.0	931.4	866.5	821.5	802.6
37.5°	927.2	886.4	818.3	768.1	745.1
40°	887.4	841.4	767.1	712.6	688.6
42.5°	842.4	796.4	718.9	658.2	637.3
45°	796.4	749.3	668.7	609.0	583.9
47.5°	751.4	699.0	619.5	554.6	532.7
50°	701.1	651.9	567.2	502.3	478.2
52.5°	656.1	601.7	518.0	450.0	429.1
55°	604.9	553.6	464.6	403.9	383.0
57.5°	558.8	503.4	413.4	355.8	338.0
60°	510.7	453.1	366.3	309.8	292.0
62.5°	462.5	405.0	318.1	265.8	247.0
65°	413.4	355.8	274.2	222.9	211.4
67.5°	364.2	305.6	226.0	187.3	174.8
70°	316.0	259.5	186.3	149.6	138.1
72.5°	267.9	212.4	147.6	119.3	116.2
75°	218.7	168.5	110.9	100.5	98.4
77.5°	173.7	127.7	86.9	80.6	78.5
80°	130.8	87.9	65.9	62.8	60.7
82.5°	90.0	54.4	47.1	44.0	44.0
85°	55.5	32.4	29.3	27.2	27.2
87.5°	25.1	13.6	13.6	12.6	11.5
90°	1.0	10.8	23.6	27.5	29.5
92.5°	29.5	35.4	41.3	44.2	42.3
95°	58.0	64.9	72.7	76.7	76.7
97.5°	95.3	100.2	106.1	111.0	110.1
100°	133.7	139.5	144.5	147.4	149.4
102.5°	177.9	180.8	187.7	190.7	189.7
105°	221.1	223.1	231.9	231.9	233.9
107.5°	272.2	273.2	277.1	280.1	279.1
110°	319.4	321.4	323.3	327.3	325.3

TEST NUMBER: P1012720

CATALOG NUMBER: S123RDIP-B775D1025UB40-4F0-XX-W2A-F1

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	368.5	369.5	369.5	374.4	374.4
115°	417.7	420.6	418.6	419.6	418.6
117.5°	467.8	468.8	466.8	466.8	463.9
120°	514.0	519.9	515.0	514.0	512.0
122.5°	562.1	566.1	564.1	561.1	558.2
125°	611.3	614.2	612.2	608.3	604.4
127.5°	656.5	662.4	660.4	654.5	650.6
130°	701.7	709.5	706.6	702.7	695.8
132.5°	746.9	754.7	752.8	747.9	742.9
135°	793.1	799.0	798.0	794.1	792.1
137.5°	835.3	840.2	843.2	838.3	835.3
140°	879.5	884.5	885.4	884.5	877.6
142.5°	919.8	924.8	926.7	925.7	920.8
145°	962.1	964.1	967.0	966.0	962.1
147.5°	998.5	1002.4	1005.3	1005.3	999.4
150°	1036.8	1038.8	1040.7	1040.7	1034.8
152.5°	1068.2	1071.2	1072.2	1074.1	1069.2
155°	1101.6	1101.6	1102.6	1106.6	1099.7
157.5°	1130.1	1129.2	1130.1	1134.1	1128.2
160°	1156.7	1154.7	1154.7	1159.6	1155.7
162.5°	1180.3	1177.3	1178.3	1183.2	1176.3
165°	1199.9	1197.0	1197.0	1202.9	1196.0
167.5°	1216.6	1212.7	1213.7	1219.6	1213.7
170°	1230.4	1226.5	1226.5	1233.3	1226.5
172.5°	1241.2	1237.3	1237.3	1243.2	1236.3
175°	1248.1	1244.1	1244.1	1250.0	1243.2
177.5°	1252.0	1248.1	1248.1	1254.0	1247.1
180°	1251.0	1251.0	1251.0	1251.0	1251.0

(END OF REPORT)