

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P1013271

Luminaire Tested: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_5000K

Issue Date: 5/7/2025

Test Information

Test Method: LM-79-2019
Report Number: P1013271
REPORT IS A COMBINATION OF REPORTS P999074 AND P1007351
Test Lab: INNOVATION CENTER
Issue Date: 5/7/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_5000K
Description: Define 4 Regressed Direct/Indirect Pendant with 5000K BioUP LEDs {m-DER=1.015}
{m-EER=1.115}
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9266.0 lumens
Efficiency: N/A
Efficacy: 96.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.09 / 1.24
Luminous Opening: Rectangular w/ Sides (W: 0.33' x L: 4' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 96.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1013271

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1013271

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	48	48	43
2	90	82	76	71	82	76	71	67	65	61	58	54	51	49	44	43	41	41	41	36
3	82	73	65	60	75	67	61	56	57	53	49	48	45	42	40	37	35	35	35	31
4	75	64	57	51	69	60	53	48	51	46	42	43	39	36	36	33	30	30	30	27
5	69	57	49	44	63	53	46	41	46	40	36	39	35	31	32	29	27	27	27	23
6	64	52	44	38	58	48	41	36	41	36	32	35	31	28	29	26	24	24	24	21
7	59	47	39	33	54	44	36	31	38	32	28	32	28	24	27	24	21	21	21	18
8	55	42	35	29	50	40	33	28	34	29	25	29	25	22	25	21	19	19	19	17
9	51	39	31	26	47	36	30	25	31	26	22	27	23	20	23	20	17	17	17	15
10	48	36	28	24	44	33	27	23	29	24	20	25	21	18	21	18	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	16390	16390	16390
5°	16391	15903	15905
10°	16252	15401	15218
15°	16029	14776	14408
20°	15735	14064	13484
25°	15370	13295	12581
30°	15013	12511	11568
35°	14620	11716	10578
40°	14151	10860	9561
45°	13713	10012	8554
50°	13213	9085	7530
55°	12675	8135	6475
60°	12077	7126	5432
65°	11499	5969	4428
70°	10677	4752	3384
75°	9625	3457	2367
80°	8037	2121	1701
85°	6047	1222	935

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 13713 cd/sqm

TEST NUMBER: P1013271

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	189.0	2.0
10°-20°	527.0	5.7
20°-30°	760.8	8.2
30°-40°	862.2	9.3
40°-50°	832.5	9.0
50°-60°	692.1	7.5
60°-70°	477.7	5.2
70°-80°	241.4	2.6
80°-90°	64.4	0.7
90°-100°	49.5	0.5
100°-110°	326.3	3.5
110°-120°	623.1	6.7
120°-130°	791.0	8.5
130°-140°	846.2	9.1
140°-150°	791.3	8.5
150°-160°	638.1	6.9
160°-170°	411.5	4.4
170°-180°	141.8	1.5
0°-30°	1476.7	15.9
0°-40°	2339.0	25.2
0°-60°	3863.6	41.7
0°-90°	4647.1	50.2
90°-120°	999.0	10.8
90°-150°	3427.5	37.0
90°-180°	4619.0	49.8
0°-180°	9266.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2010	2010	2010	2010	2010	
5°	2007	2001	1982	1998	1994	190
15°	1911	1898	1859	1856	1845	539
25°	1728	1700	1637	1611	1596	796
35°	1494	1445	1368	1316	1288	934
45°	1219	1162	1070	994	966	940
55°	923	862	762	682	652	826
65°	628	562	463	397	379	620
75°	334	277	205	169	160	352
85°	83	52	48	45	45	91
90°	3	16	25	31	34	8
95°	61	23	25	31	32	76
105°	336	343	348	358	318	352
115°	627	631	630	632	632	618
125°	882	886	884	888	889	788
135°	1094	1093	1098	1100	1102	843
145°	1262	1265	1265	1266	1268	788
155°	1383	1384	1381	1386	1382	638
165°	1459	1454	1454	1462	1452	412
175°	1493	1486	1487	1497	1484	142
180°	1493	1493	1493	1493	1493	

TEST NUMBER: P1013271

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2009.9	2009.9	2009.9	2009.9	2009.9
2.5°	2016.0	2009.9	1992.9	2009.9	2008.3
5°	2006.8	2000.6	1982.2	1997.6	1994.5
7.5°	1992.9	1986.8	1963.7	1974.5	1969.8
10°	1971.4	1963.7	1936.0	1942.1	1936.0
12.5°	1943.7	1934.5	1900.6	1903.7	1894.4
15°	1911.4	1897.5	1859.0	1856.0	1845.2
17.5°	1874.4	1854.4	1809.8	1802.1	1786.7
20°	1829.8	1809.8	1757.5	1745.2	1725.2
22.5°	1780.6	1757.5	1700.5	1680.5	1665.1
25°	1728.2	1700.5	1637.4	1611.3	1595.9
27.5°	1674.4	1640.5	1574.3	1543.6	1522.0
30°	1617.4	1579.0	1506.6	1468.2	1443.5
32.5°	1557.4	1512.8	1437.4	1391.2	1368.1
35°	1494.3	1445.1	1368.1	1315.8	1288.1
37.5°	1428.1	1377.4	1292.7	1235.8	1208.1
40°	1357.3	1306.6	1218.8	1154.2	1126.5
42.5°	1289.6	1235.8	1143.4	1077.3	1048.0
45°	1218.8	1161.9	1069.6	994.2	966.5
47.5°	1146.5	1088.0	992.6	914.1	883.4
50°	1072.6	1012.6	914.1	837.2	807.9
52.5°	997.2	938.8	837.2	758.7	727.9
55°	923.4	861.8	761.8	681.8	652.5
57.5°	851.0	786.4	687.9	606.3	584.8
60°	772.6	711.0	612.5	532.5	507.9
62.5°	701.8	637.1	535.6	463.2	444.8
65°	627.9	561.7	463.2	397.0	378.6
67.5°	550.9	487.8	395.5	337.0	315.5
70°	478.6	414.0	326.3	275.5	260.1
72.5°	401.7	344.7	263.2	221.6	207.8
75°	334.0	277.0	204.7	169.3	160.1
77.5°	263.2	213.9	152.4	127.7	124.7
80°	195.4	150.8	104.6	100.0	98.5
82.5°	137.0	97.0	75.4	72.3	70.8
85°	83.1	52.3	47.7	44.6	44.6
87.5°	35.4	23.1	21.5	20.0	21.5
90°	3.3	15.6	24.6	31.3	33.5
92.5°	16.7	14.5	23.4	30.1	30.1
95°	61.4	23.4	24.6	31.3	32.4
97.5°	117.2	141.8	24.6	30.1	31.3
100°	183.1	203.2	49.1	30.1	31.3
102.5°	256.8	270.2	283.6	32.4	32.4
105°	336.1	342.7	348.3	358.4	318.2
107.5°	408.6	412.0	419.8	425.4	429.8
110°	482.3	485.7	492.4	494.6	497.9

TEST NUMBER: P1013271

CATALOG NUMBER: S124RDIP-B1195D1205UB2750-4F0-XX-W2A-F_5000K

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	553.8	560.5	562.7	561.6	566.0
115°	627.4	630.8	629.7	631.9	631.9
117.5°	693.3	697.8	701.1	700.0	700.0
120°	760.3	764.8	763.7	765.9	763.7
122.5°	822.8	825.1	827.3	828.4	826.2
125°	882.0	886.5	884.2	887.6	888.7
127.5°	938.9	940.1	945.6	944.5	943.4
130°	993.6	994.8	998.1	999.2	999.2
132.5°	1043.9	1046.1	1050.6	1051.7	1050.6
135°	1094.1	1093.0	1097.5	1099.7	1101.9
137.5°	1138.8	1138.8	1144.4	1146.6	1145.5
140°	1182.3	1184.6	1186.8	1190.1	1191.3
142.5°	1221.4	1225.9	1227.0	1229.2	1229.2
145°	1261.6	1264.9	1264.9	1266.1	1268.3
147.5°	1292.8	1299.5	1298.4	1299.5	1300.7
150°	1327.5	1331.9	1330.8	1330.8	1331.9
152.5°	1356.5	1359.8	1357.6	1359.8	1358.7
155°	1383.3	1384.4	1381.0	1385.5	1382.2
157.5°	1406.7	1406.7	1402.3	1407.8	1402.3
160°	1426.8	1423.5	1422.4	1429.1	1422.4
162.5°	1444.7	1440.2	1439.1	1445.8	1438.0
165°	1459.2	1453.6	1453.6	1462.5	1452.5
167.5°	1471.5	1465.9	1464.8	1474.8	1463.7
170°	1481.5	1474.8	1475.9	1484.9	1473.7
172.5°	1488.2	1481.5	1482.6	1491.6	1479.3
175°	1492.7	1486.0	1487.1	1497.2	1483.8
177.5°	1496.0	1488.2	1490.5	1499.4	1486.0
180°	1492.7	1492.7	1492.7	1492.7	1492.7

(END OF REPORT)